

LED Wall Bracket

 Wall mounted • Damp location listed 

Description:

Beam LED vanity and sconces feature a squared, tubular opal glass diffuser paired with a simple, modern metal canopy. An integrated LED source provides a variety of energy and cost savings benefits. Suitable for residential and commercial applications.

Specifications:

- Brushed Nickel (-009) (plated)
- Steel construction
- Etched Opal Glass Flat Square/Rectangular
- A tubular design pairs with a square back plate to create the Beam Collection, an LED fixture for bath and vanity areas
- 1-light 16-watt LED wall bracket
- Beam LED adds task lighting on either side or above a mirror to eliminate shadows on face when getting ready in the morning
- An integrated LED source provides a variety of energy, maintenance and cost savings benefits for the homeowner
- Measures 10 1/2"W x 4 3/4" H
- 1036 lumens 62 lumens/watt (delivered)
- Warm white 3000K lighting color and 90+CRI
- Adds task lighting on either side of mirror to eliminate shadows on face when getting ready in the morning
- Damp location listed
- Dimmable to 10% brightness (See Dimming Notes)
- Back plate covers a standard 4" octagonal recessed outlet box
- Mounting plate for outlet box included
- 6" of wire supplied
- Complies with "Americans with Disabilities Act" - ADA
- Meets California Title 24 JA8-2016

Performance:

Number of Modules	1
Input Power	16w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Delivered)	1036/62.8 (LM-79)
CCT	3000 K
CRI	90 CRI
Life (hours)	50,000 (L70/TM-21)
FCC	Meets FCC Title 47, Part 15 Class B
Min. Start Temp	-10 °C
Warranty	5 year limited warranty
Labels	cETLus Damp location listed Meets California Title 24 JA8-2016

P710049-009-30

Images:



Dimensions:

Width: 10-1/2"
Depth: 3-1/4"
Height: 4-3/4"
H/CTR: 8-3/8"

Glass
Width: 2-1/4"
Length: 2-1/4"
Height: 10-1/4"

P710049-009-30**Dimming Notes:**

P710049 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

Dimming Controls

Lutron - NTELV-300

Lutron - DVELV-300P

Lutron - DVCL-253P

Lutron - Caseta Wireless

Leviton – 6672

Leviton – 6674

Leviton - 6681

Lutron - AYCL-153P

Lutron - TGCL-153PH

Lutron - AYLV-600P

Lutron - NTLV-600

Lutron - MAELV-601

Lutron - N-600

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.