

Garant
Solid carbide drill for aramide, uncoated, Ø DC h6: 10mm

Order data

Order number	121230 10
GTIN	4045197472076
Item class	11Y

Description
Version:

Special geometry for reliable drilling of aramide plastics (polyaramides) and aramide fibres as well as thermoplastics and thermosetting plastics.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Technical description

Nominal Ø D_c	10 mm
Feed f in AFK	0.1 mm/rev.
Flute length L_c	48 mm
Number of cutting edges Z	2
Shank tolerance	h6
Tolerance nominal Ø	h6
Shank Ø D_s	10 mm
Overall length L	89 mm
Standard	Manufacturer's standard
recommended maximum drilling depth L_2	33 mm
Coating	uncoated
Tool material	Solid carbide
Version	4xD

Shank	Parallel shank to h6
Use for drilling	for aramides
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V _c	ISO code
PE-HD	suitable only under restricted conditions	140 m/min	N
PA 66	suitable only under restricted conditions	130 m/min	N
PEEK	suitable only under restricted conditions	120 m/min	N
PF 31	suitable only under restricted conditions	100 m/min	N
AFRP aramid	suitable	110 m/min	N
Honeycomb sandwich	suitable only under restricted conditions	120 m/min	N
dry	suitable		
Air	suitable		