

Safety Data Sheet



1. Identification

Product Name:	R-O 1-GL EGGSHELL DOVE GRAY	Revision Date:	10/29/2018
Product Identifier:	339521	Supersedes Date:	New SDS
Recommended Use:	Topcoat		
Supplier:	Rust-Oleum Corporation 11 Hawthorn Parkway Vernon Hills, IL 60061 USA	Manufacturer:	Rust-Oleum Corporation 11 Hawthorn Parkway Vernon Hills, IL 60061 USA
Preparer:	Regulatory Department		
Emergency Telephone:	24 Hour Hotline: 847-367-7700		

2. Hazard Identification

Classification

Symbol(s) of Product



Signal Word

Danger

Possible Hazards

19% of the mixture consists of ingredient(s) of unknown acute toxicity.

GHS HAZARD STATEMENTS

Carcinogenicity, category 1B H350 May cause cancer.

GHS LABEL PRECAUTIONARY STATEMENTS

P201	Obtain special instructions before use.
P280	Wear protective gloves/protective clothing/eye protection/face protection.
P308+P313	IF exposed or concerned: Get medical advice/attention.
P405	Store locked up.
P501	Dispose of contents/container in accordance with local, regional and national regulations.

3. Composition / Information On Ingredients

HAZARDOUS SUBSTANCES

<u>Chemical Name</u>	<u>CAS-No.</u>	<u>Wt.% Range</u>	<u>GHS Symbols</u>	<u>GHS Statements</u>
Titanium Dioxide	13463-67-7	10-25	Not Available	Not Available
Kaolin Clay	1332-58-7	2.5-10	Not Available	Not Available

2,4,7,9-Tetramethyl-5-Decyne-4,7-Diol	126-86-3	0.1-1.0	GHS05-GHS07	H302-312-317-318
Aliphatic Petroleum Distillates	64741-88-4	0.1-1.0	GHS08	H350
Propylene Glycol Phenyl Ether	770-35-4	0.1-1.0	GHS06	H331
Sodium Nitrite	7632-00-0	0.1-1.0	GHS03-GHS06	H272-301-319-331
Titanium Dioxide	1317-70-0	0.1-1.0	Not Available	Not Available
Oxirane, 2-Methyl-, Polymer with Oxirane, Monobutyl Ether	9038-95-3	0.1-1.0	GHS06	H330

4. First-Aid Measures

FIRST AID - EYE CONTACT: Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed.

FIRST AID - SKIN CONTACT: Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persists.

FIRST AID - INHALATION: Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately.

FIRST AID - INGESTION: Swallowing less than an ounce will not cause significant harm. For larger amounts, do not induce vomiting, but give one or two glasses of water to drink and get medical attention. If swallowed, rinse mouth with water. If feeling unwell, get medical attention.

5. Fire-Fighting Measures

EXTINGUISHING MEDIA: Alcohol Film Forming Foam, Carbon Dioxide, Dry Chemical, Dry Sand, Water Fog

UNUSUAL FIRE AND EXPLOSION HAZARDS: No unusual fire or explosion hazards noted. Keep containers tightly closed. FLASH POINT IS TESTED TO BE GREATER THAN 200 DEGREES F.

SPECIAL FIREFIGHTING PROCEDURES: Water may be used to cool closed containers to prevent buildup of steam. If water is used, fog nozzles are preferred.

Special Fire and Explosion Hazard (Combustible Dust): No Information

6. Accidental Release Measures

STEPS TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED: If spilled, contain spilled material and remove with inert absorbent. Dispose of contaminated absorbent, container, and unused contents in accordance with local, state, and federal regulations. Do not incinerate closed containers

7. Handling and Storage

HANDLING: Wash thoroughly after handling. Wash hands before eating. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Follow all SDS and label precautions even after container is emptied because it may retain product residues. Avoid breathing fumes, vapors, or mist. Avoid contact with eyes, skin and clothing.

STORAGE: Store in a dry, well ventilated place. Keep container tightly closed when not in use.

Advice on Safe Handling of Combustible Dust: No Information

8. Exposure Controls / Personal Protection

Chemical Name	CAS-No.	Weight % Less Than	ACGIH TLV- TWA	ACGIH TLV- STEL	OSHA PEL-TWA	OSHA PEL- CEILING
Titanium Dioxide	13463-67-7	15.0	10 mg/m3	N.E.	15 mg/m3	N.E.
Kaolin Clay	1332-58-7	10.0	2 mg/m3	N.E.	15 mg/m3	N.E.
2,4,7,9-Tetramethyl-5-Decyne-4,7-Diol	126-86-3	1.0	N.E.	N.E.	N.E.	N.E.
Aliphatic Petroleum Distillates	64741-88-4	1.0	N.E.	N.E.	N.E.	N.E.
Propylene Glycol Phenyl Ether	770-35-4	1.0	N.E.	N.E.	N.E.	N.E.

Sodium Nitrite	7632-00-0	1.0	N.E.	N.E.	N.E.	N.E.
Titanium Dioxide	1317-70-0	1.0	N.E.	N.E.	N.E.	N.E.
Oxirane, 2-Methyl-, Polymer with Oxirane, Monobutyl Ether	9038-95-3	1.0	N.E.	N.E.	N.E.	N.E.

PERSONAL PROTECTION

ENGINEERING CONTROLS: Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Prevent build-up of vapors by opening all doors and windows to achieve cross-ventilation.

RESPIRATORY PROTECTION: A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 requirements must be followed whenever workplace conditions warrant a respirator's use.

SKIN PROTECTION: Use gloves to prevent prolonged skin contact. Nitrile or Neoprene gloves may afford adequate skin protection.

EYE PROTECTION: Use safety eyewear designed to protect against splash of liquids.

OTHER PROTECTIVE EQUIPMENT: Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications.

HYGIENIC PRACTICES: Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

Engineering Measures for Combustible Dust: No Information

9. Physical and Chemical Properties

Appearance:	Liquid	Physical State:	Liquid
Odor:	Solvent Like	Odor Threshold:	N.E.
Relative Density:	1.296	pH:	N.A.
Freeze Point, °C:	N.D.	Viscosity:	N.D.
Solubility in Water:	Slight	Partition Coefficient, n-octanol/water:	N.D.
Decomposition Temp., °C:	N.D.	Explosive Limits, vol%:	N.A. - N.A.
Boiling Range, °C:	100 - 537	Flash Point, °C:	93
Flammability:	Does not Support Combustion	Auto-ignition Temp., °C:	N.D.
Evaporation Rate:	Slower than Ether	Vapor Pressure:	N.D.
Vapor Density:	Heavier than Air		

(See "Other information" Section for abbreviation legend)

10. Stability and Reactivity

CONDITIONS TO AVOID: No Information

INCOMPATIBILITY: Incompatible with strong oxidizing agents, strong acids and strong alkalis.

HAZARDOUS DECOMPOSITION: When heated to decomposition, it emits acrid smoke and irritating fumes.

HAZARDOUS POLYMERIZATION: Will not occur under normal conditions.

STABILITY: This product is stable under normal storage conditions.

11. Toxicological Information

EFFECTS OF OVEREXPOSURE - EYE CONTACT: Irritating, and may injure eye tissue if not removed promptly.

EFFECTS OF OVEREXPOSURE - SKIN CONTACT: Low hazard for usual industrial handling or commercial handling by trained personnel.

EFFECTS OF OVEREXPOSURE - INHALATION: High gas, vapor, mist or dust concentrations may be harmful if inhaled. Avoid breathing fumes, spray, vapors, or mist.

EFFECTS OF OVEREXPOSURE - INGESTION: Substance may be harmful if swallowed.

EFFECTS OF OVEREXPOSURE - CHRONIC HAZARDS: Contains Titanium Dioxide. Titanium Dioxide is listed as a Group 2B-"Possibly carcinogenic to humans" by IARC. No significant exposure to Titanium Dioxide is thought to occur during the use of products in which Titanium Dioxide is bound to other materials, such as in paints during brush application or drying. Risk of overexposure depends on duration and level of exposure to dust from repeated sanding of surfaces or spray mist and the actual concentration of Titanium Dioxide in the formula. (Ref: IARC Monograph, Vol. 93, 2010) Contains Petroleum Distillates-Heavy Paraffinic, which is listed as an IARC Group 1 Carcinogen.

PRIMARY ROUTE(S) OF ENTRY: Eye Contact, Ingestion, Inhalation, Skin Absorption, Skin Contact

ACUTE TOXICITY VALUES

The acute effects of this product have not been tested. Data on individual components are tabulated below:

<u>CAS-No.</u>	<u>Chemical Name</u>	<u>Oral LD50</u>	<u>Dermal LD50</u>	<u>Vapor LC50</u>
13463-67-7	Titanium Dioxide	>10000 mg/kg Rat	2500 mg/kg	N.E.
1332-58-7	Kaolin Clay	5500 mg/kg	>5000 mg/kg Rat	25
126-86-3	2,4,7,9-Tetramethyl-5-Decyne-4,7-Diol	>500 mg/kg Rat	>1000 mg/kg Rabbit	N.E.
64741-88-4	Aliphatic Petroleum Distillates	>5000 mg/kg Rat	>2000 mg/kg Rabbit	N.E.
770-35-4	Propylene Glycol Phenyl Ether	2830 mg/kg Rat	>2000 mg/kg Rabbit	>5.4 mg/L Rat
7632-00-0	Sodium Nitrite	85 mg/kg Rat	N.E.	5.5 mg/L Rat
9038-95-3	Oxirane, 2-Methyl-, Polymer with Oxirane, Monobutyl Ether	5000 mg/kg Rat	14904 mg/kg Rabbit	.1 mg/L Rat

N.E. - Not Established

12. Ecological Information

ECOLOGICAL INFORMATION: Product is a mixture of listed components.

13. Disposal Information

DISPOSAL INFORMATION: Dispose of material in accordance to local, state, and federal regulations and ordinances. Do not allow to enter waterways, wastewater, soil, storm drains or sewer systems.

14. Transport Information

	<u>Domestic (USDOT)</u>	<u>International (IMDG)</u>	<u>Air (IATA)</u>	<u>TDG (Canada)</u>
UN Number:	N.A.	N.A.	N.A.	N.A.
Proper Shipping Name:	Not Regulated	Not Regulated	Not Regulated	Not Regulated
Hazard Class:	N.A.	N.A.	N.A.	N.A.
Packing Group:	N.A.	N.A.	N.A.	N.A.
Limited Quantity:	No	No	No	No

15. Regulatory Information

U.S. Federal Regulations:

CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Carcinogenicity

Sara Section 313:

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

<u>Chemical Name</u>	<u>CAS-No.</u>
Sodium Nitrite	7632-00-0

Toxic Substances Control Act:

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from the United States:

<u>Chemical Name</u>	<u>CAS-No.</u>
Sodium Nitrite	7632-00-0

U.S. State Regulations:**California Proposition 65:****WARNING:** Cancer and Reproductive Harm - www.P65Warnings.ca.gov.**16. Other Information****HMIS RATINGS****Health:** 2* **Flammability:** 1 **Physical Hazard:** 0 **Personal Protection:** X**NFPA RATINGS****Health:** 2 **Flammability:** 1 **Instability:** 0**Volatile Organic Compounds** 49 g/L**SDS REVISION DATE:** 10/29/2018**REASON FOR REVISION:**

Legend: N.A. - Not Applicable, N.E. - Not Established, N.D. - Not Determined

Rust-Oleum Corporation believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. Rust-Oleum Corporation makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.