


2

1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	MAX. BUNDLE DIA.	PACKAGE QTY.	"L" LENGTH +/- .3" [7]
MLT2EH-LP	2" [51]	50	11.8" [300]
MLT4EH-LP	4" [102]	50	17.1" [434]
MLT6EH-LP	6" [152]	50	23.4" [594]
MLT8EH-LP	8" [203]	50	29.7" [754]
MLT10EH-LP	10" [254]	50	35.9" [912]
MLT12EH-Q	12" [305]	25	42.2" [1072]



NOTES:

1. APPLICATION TOOLS - ST2MT, RT2HT, RT2HTN & PBTMT
2. MINIMUM LOOP TENSILE STRENGTH - 600 LBS. (2670 NEWTONS) WHEN TESTED ON A 3" MANDREL.
3. BRACKETS [] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
4. TOLERANCES:
 .XXX = $\pm .010$ [.25] .XX = $\pm .02$ [.5]
 .X = $\pm .03$ [.8] ANGLES = $\pm 2^\circ$
5. MATERIAL: 304 STAINLESS STEEL

TITLE				METAL LOCKING TIE EXTRA HEAVY DUTY 304 STAINLESS STEEL			
				CUSTOMER DRAWING			
ITEM REVISION NAME							
N41155BS/04							
DATASET FILE NAME							
N41155BS_DC/04A							
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .03 [.8] .xxx ± .010 [.25] .xx ± .02 [.5] ANGLES ± 5 °  THIRD ANGLE PROJECTION				MATERIAL:			
				SEE NOTES			
				DRAWING NUMBER:			
				N41155BS_DC			
DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1		SIZE	
JAMB	01/04	DPN	2:1			A	

2

1