


Section 1 - Product Information

Product Name: ORIGENZ / ODOR OUT NEUTRALIZER CONCENTRATE		Supplier: PristineHD, LLC
Product Code Number: C015	Information Phone: 1-844-777-4784	Address: P.O. Box 302 Cedarhurst, NY 11516
Product use: Odor neutralizer	Emergency Contact: CHEMTREC 1-800-424-9300	

Section 2 - Hazard Identification

OSHA-GHS Hazard Classification: Eye Corrosive Category 1.

Section 2.1 - Label Elements

Signal Word: Danger	Hazard Pictograms 	Hazard Statements: H318 - Causes serious eye damage.
-----------------------------------	---	--

Precautionary Statements: Prevention

P280 - Wear eye protection / face protection.

Precautionary Statements: Response

P305+P351+P338 - IF IN EYES: Rinse eyes with water for several minutes. Remove contact lenses if present and easy to do.
P310 - Immediately call a POISON CENTER or doctor.

Precautionary Statements: Storage

NA

Precautionary Statements : Disposal

NA

Section 3 - Composition

Chemical Name	CAS #	Percent w/w
Alkyl Poly Glycosides	68515-73-1	5-10
Alkyl Poly Glycosides	110615-47-9	1-3
sodium carbonate	497-19-8	1-3

Section 4 - First Aid Measures

Eye may cause irritation. Rinse eyes cautiously with water for several minutes. If irritation persists contact a physician

Skin contact not likely to cause irritation. Rinse skin with water. If skin irritation does occur contact a physician

Ingestion is not likely to cause toxic effects. If large quantities are swallowed, minor gastrointestinal distress may occur. Drink plenty of water to dilute material.

Section 5 - Fire and Explosion Hazard Data

Flash Point:	Limits	Extinguishing Media:	Special Fire Fighting Procedures: Avoid exposure to fumes or vapors.
> 200°F	LEL: NA	Product does not burn. Use suitable extinguishing media for surrounding material	Wear self-contained positive pressurized breathing apparatus MSHA/NIOSH Approved or equivalent to maintain TLV. UNUSUAL FIRE & EXPLOSION HAZARD: Product does not burn.
	UEL: NA		

Section 6 - Accidental Release Measures

Rinse spills with plenty of water. Dispose of in accordance to local and national regulations.

Section 7 - Handling and Storage

Avoid contact with eyes. Store between 35°F and 120°F

Section 8 - Exposure Controls/PPE									
Ingredient	OSHA PEL:	ACGIH TLV	PPE				General Hygiene Considerations:		
No ingredient has established exposure limits			Respiratory:	Not required			Handle in accordance with good industrial hygiene and safety practices. Provide suitable facilities for quick drenching or flushing of the eyes and body in case of contact or splash hazard.		
			Eye:	safety glasses suggested					
			Skin:	not required					
			Ventilation:	no special requirements					
Section 9 - Physical and Chemical Properties									
Appearance	odor	odor threshold	pH	Melting Point	Boiling point	Evaporation rate	Flammability	Upper/lower flammability limits	Vapor pressure
Colorless liq.	Characteristic	none	10 - 11	32°F	212°F	1	none	none	Na
Vapor Density (air = 1)	Density (lbs/gal)	Specific Gravity	pH(use dil)	Solubility (in water)	Partition coefficient	Auto Ignition temp	Viscosity	Decomposition Temp	
3.2	8.55	1.02	NA	complete	NE	NE	Thin	NE	
Section 10 - Stability and Reactivity									
This product is chemically inert. No known reactive materials. It is stable under normal conditions. Avoid temperature extremes. No hazardous reactions have been observed. Do not freeze. Do not use above ambient temperature. No known incompatible materials. Decomposition produces trace amounts of carbon dioxide and other natural gases.									
Section 11- Toxicological Information									
Ingredient	LD50) rat	toxicity(derm.	Skin and Eye	Carcinogen	Mutagen	Toxicity	STOST -single Exposure	Repeated	
Ingredient	Acute toxicity(oral LD50) rat	Acute toxicity(derm. LD50)rabbit	Skin and Eye	Carcinogen	Mutagen	Reproduct. Toxicity	STOST -single Exposure	STOST Repeated exposure	
Alkyl Poly Glycosides	> 5000mg/kg	> 2000mg/kg	eye corrosive	not listed	not listed	no effect	no effect	no effect	
Sodium Carbonate	2800 mg/kg	> 2000mg/kg	eye irritant	not listed	not listed	no effect	no effect	no effect	
Section 12 - Ecological Information					Section 13 - Disposal Considerations				
Not expected to be harmful to aquatic or soil environments. Readily biodegradable organic liquid.					Dispose of in accordance with local, state and national legislation.				
Section 14 - Transport Information									
UN number	Basic Description(DOT)					Class	Packing Group	LTD QTY	
	Not regulated								
Section 15 - Regulatory Information									
SARA Title 3: Does not contain reportable chemicals under sections 302, 304, or 313 of Title III of the Superfund amendments and Reauthorization Act of 1986. CERCLA: Does not contain chemicals subject to reporting under CERCLA. For more information consult 40 CFR parts 302, 355, 370, 372, and 40 CFR part 68									
Section 16 - Other Information									
			HMIS: Health - 0			Flam. - 0	R - 0	PPE- X	
Date Prepared:	2-Jan-2019		Prepared by: Environmental, Health and Safety Administrator.						
The information provided in this Safety Data Sheet is correct to the best of our knowledge and belief at the date of its publication. The information given is designed only as guidance for safe handling, use, processing, storage, transportation, disposal, and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with materials or in any process, unless specified in the text.									
Legend for Abbreviations: NA - not applicable NE - Not Established									