



## Husqvarna DM 200

Husqvarna DM 200 is a powerful and sturdy handheld electric core drill for both dry and wet drilling. The ergonomically designed D-handle gives you good control whilst drilling and its versatility makes it an ideal partner for professionals as well as semi-professionals. DM 200 is prepared for connectivity with Husqvarna Fleet Services™ system for monitoring of runtime, location, inventory etc. Suitable for light applications such as ventilation, plumbing pipes, electrical sockets and cables.



### Two-speed gear selector

Enables easy adaptation of spindle speed and torque to any diameter between 25mm - 100mm.



### Prepared for connectivity

Built-in connectivity enables communication with Husqvarna Fleet Services™ for monitoring of runtime, utilisation rate, inventory and more.

### Durable and ergonomic design

Durable and shock-proof, designed to protect the electronics. Easy to carry and install thanks to low weight and ergonomic design.



### 360° adjustable front handle

For best ergonomic position



## PXM\_FEATURES

- Durable and shock-proof, designed to protect the electronics. Easy to carry and install thanks to low weight and ergonomic design.
- Prepared for connectivity
- Two-speed gear selector
- For best ergonomic position
- The machine uses pulsation to warn you of an approaching overload. If the load is not reduced the motor will shut off, to prevent overheating. Elgard™ increases productivity and extends product life.
- Easy to switch between dry and wet drilling
- Softstart™ lowers incoming current to reduce amperage when starting the motor.
- Drilling holes in steplless adjustable angles.
- Drilling horizontally.
- Drilling upwards and downwards.
- Drilling ventilation channels and holes for pipes and cables.

### Technical Specifications

MOTOR	
Electronic product	Yes
Frequency	50–60 Hz
Voltage	100–120 V
Rated input power	2.68 hp
DRILLING EQUIPMENT	
Drill bit diameter handheld, max	4 in
Recommended drill bit diameter, min	1 in
SPECIFICATIONS	
Water pressure, max	43.5 psi
Mounting collar	2.36 in
Spindle thread, inner	G 1/2"
Spindle thread, outer	1 1/4" 7 UNC
TRANSMISSION	
Number of gearbox speeds	2
DIMENSIONS	
Water connector	Gardena Male
Weight	11.5 lbs
Product size length	490 in
Product size width	4.73 in
Product size height	10.83 in
SOUND AND NOISE	
Sound power level, guaranteed (LWA)	99 dB(A)
Sound pressure level at operators ear	88 dB(A)
PACKAGING	
Packaging length	550 mm
Packaging width	190 mm
Packaging height	400 mm

## ACCESSORIES



HUSQVARNA WT2GO  
598 74 24-01



HUSQVARNA WT 15I  
599 58 23-04



HUSQVARNA WT 15I  
599 58 24-06



SLURRY RINGS WSR  
593 56 30-01



HUSQVARNA W 250 P  
967 70 21-04



HUSQVARNA W 70 P  
967 66 47-01



HUSQVARNA S 13  
967 66 40-01