



W75 IDTR

PRODUCT INFORMATION

- ✓ Up to 200,000 divisions up to 10,000 lbs
- ✓ Extra large 50mm digit size wide angle LCD display with LED backlight
- ✓ Heavy duty construction design withstand harsh industrial operation
- ✓ High speed 24 bits multiplexed delta-sigma A/D converter
- ✓ Dual weighing range
- ✓ Functions including: power on zero tracking, manual zero, full subtractive tare, auto tare, preset tare, automatic continuous tare, data accumulation, digital motion filtering, animal weighing, simple piece counting, check weighing and battery power level indicator
- ✓ Supporting Lb/Kg conversion and simple piece counting
- ✓ 3 color backlight and alarm for check weighing function
- ✓ Built-in rechargeable battery for 210 hours operating time
- ✓ RS-232 equipped standard

LCD

M

RS
232

LO
OK
HI