

**Section 1: Identification**

**Product identifier**

Genesis Glass Cleaner

**Relevant identified uses of the substance or mixture and uses advised against**

Automotive Detailing

**Details of the supplier of the safety data sheet**

Proje Premium Car Care  
15020 Desman Rd  
La Mirada, CA 90636

info@projeproducts.com  
www.projeproducts.com

**Emergency telephone number**

Emergency information service

USA 1.800.535.5053, INTL 1.352.323.3500  
24 hour emergency number

**Section 2: Hazard(s) Identification**

**Classification of the substance or mixture**

Classification acc. to OSHA "Hazard Communication Standard" (29 CFR 1910.1200)

Health Environmental	Category
Eye Irritation	Cat 2B (Mild Irritation)
Acute Toxicity	Cat 5 (Oral)

**Label elements**

Labelling acc. to OSHA "Hazard Communication Standard" (29 CFR 1910.1200)

- Signal word                warning
- Pictograms



- Hazard statements

H303 May be harmful if swallowed  
H320 Causes eye irritation

- Precautionary statements

P101 If medical advice is needed, have product or label at hand.  
P102 Keep out of reach of children  
P103 Read label before use.

**Section 3: Composition/information on ingredients**

Name of substance	Identifier	Wt%
Water	CAS No 7732-18-5	≤ 97
Sodium Xylenesulphonate	CAS No 1300-72-7	≤ 4
1,3-Bis(hydroxymethyl)-5, 5-dimethylimidazolidine-2,4-dione	CAS No 6440-58-0	≤ 0.001

**Genesis Glass Cleaner**

Mono(hydroxymethyl)-5,5-dimethylimidazolidine-2,4-dione	CAS No 27636-82-4	≤ 0.001
Fragrance	CAS No 8000-34-8	≤ 0.001
Colorant	CAS No 72243-90-4	< 0.001

Exact percentage of ingredients is withheld as a trade secret.

**Section 4: First-aid measures**

**Description of first- aid measures**

**Eye Contact:**

Flush immediately with large amounts of clean water for at least 15 minutes; Eyelids should be held away from the eyeball to ensure thorough rinsing. If any irritation persists, seek medical attention.

**Skin Contact:**

Rinse area with soap and water. Seek medical attention if any redness or irritation persists.

**Inhalation:**

If breathing is difficult or irritating, move to fresh air immediately. If symptoms persist, get medical attention.

**Ingestion:**

Rinse mouth. Get immediate medical attention. Do not induce vomiting unless directed by medical personnel

**Section 5: Fire Fighting Measures**

**Suitable Extinguishing Media:**

Use dry chemical, foam, or carbon dioxide to extinguish fire. Water may be ineffective but should be used to cool fire-exposed containers, structures and to protect personnel. Use water to dilute spills and to flush them away from sources of ignition.

**Fire Fighting Procedures:**

No special protective action for fire fighters are anticipated.

**Unusual Fire and Explosion:**

N/A

**Combustion Products:**

N/A

**Section 6: Accidental release measures**

Contain large spills with dikes to prevent entry to waterways and sanitary sewers and transfer the material to appropriate containers for reclamation or disposal. Absorb/trap remaining material or small spills with inert material (dirt, sand, industrial absorbent) and then place in chemical waste containers. Flush residual spill area with large amounts of water. Dispose of all clean up materials in accordance with all applicable federal, state, and local health and environmental regulations.

**Section 7: Handling and storage**

**Handling**

Do not get in eyes, on skin or on clothing. Do not breathe vapor or mists. Use good personal hygiene practices. Wash hands before eating, drinking, smoking. Remove contaminated clothing and clean before re-use. Keep operating temperatures below ignition temperatures at all times. Chemical resistant splash goggles and chemical resistant gloves are always recommended when using chemicals.

**Storage**

Keep container tightly closed in a cool, dry, well-ventilated area away from heat, source of ignition and incompatibles. Do not store below 32 degrees F or above 100 degrees F. Do not store in direct sunlight. Keep away from children.

**Section 8: Exposure controls/personal protection**

**Exposure Limits**

No occupational exposure limit values exist for any of the components list in section 3 of this SDS.

**Engineering Controls:**

None

**Personal Protective Equipment (PPE):**

**Eye Protection:**

Wear chemical safety goggles and face shield. Have eye-wash stations available where eye contact can occur.

**Skin Protection:**

Avoid prolonged skin contact. Wear gloves impervious to conditions of use. Additional protection may be necessary to prevent skin contact including use of apron. A safety shower should be located in the work area

**Respiratory Protection:**

N/A

**Section 9: Physical and chemical properties**

**Safety Parameters, information on basic physical, and chemical properties appearance**

Flash Point	None
Auto-Ignition Temperature	N/A
Boiling Point	≥ 95°C
Melting Point	N/A
Vapor Pressure	N/A
Vapor Density (Air=1)	N/A
Solubility	Complete
Pour Point	N/A
Molecular Formula	Mixture
Odor/Appearance	Liquid
Lower Flammability Limit	N/A
Upper Flammability Limit	N/A
Volatile Organic Compound	.1% weight [CARB]
Volatile Organic Compound	1 g/l [SCAQMD 443.1
Evaporation Rate (Water=1)	N/A
Viscosity	~ 0.6868 cSt @ 100 ° F
PH	7.5
Molecular Weight	Mixture
Spec. Grav. / Density	8.403 Lbs. / Ga/l.

**Section 10: Stability and reactivity**

**Reactivity:**

None

**Chemical Stability:**

Stable

**Possibility of hazardous reactions:**

Hazardous polymerization will not occur.

**Conditions to avoid:**

none

**Incompatible materials:**

Strong acids and oxidizers

**Hazardous Decomposition:**

None know.

**Section 11: Toxicological information**

**Signs and Systems of Exposure:**

Based on the test data and/or information on the components, this material may produce the following health effects:

**Inhalation Respiratory Tract Irritation:**

N/A

**Skin Contact: Mild Skin Irritation:**

Signs/symptoms may include localized redness, swelling, itching, and dryness. Allergic Skin Reaction (non-photo induced) in sensitive people: Signs/symptoms may include redness, swelling, blistering, and itching.

**Eye Contact: Moderate Eye Irritation:**

Moderate Eye Irritation: Signs/symptoms may include redness, swelling, pain, tearing, and blurred or hazy vision

**Ingestion: Gastrointestinal Irritation:**

Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

**Target Organ Effects:**

Allergic Skin Reaction (non-photo induced) in sensitive people. Signs/symptoms may include redness, swelling, blistering, and itching.

**Toxicological Data:**

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

**Acute Toxicity**

Name	Route	Species	Value
1,3-Bis(hydroxymethyl)-5, 5 - dimethylimidazolidine-2,4-dione	Oral	-	No data available
1,3-Bis(hydroxymethyl)-5, 5 - dimethylimidazolidine-2,4-dione	Inhalation	-	No data available
1,3-Bis(hydroxymethyl)-5, 5 - dimethylimidazolidine-2,4-dione	Dermal	Rabbit	Non- irritant, exposure time: 4 hr. Method: US-EPA

**Skin Corrosion/Irritation**

Name	Route	Species	Value

**Serious Eye Damage/Irritation**

Name	Route	Species	Value

**Skin Sensitization**

Name	Route	Species	Value

**Respiratory Sensitization**

Name	Route	Species	Value

**Germ Cell Mutagenicity**

Name	Route	Species	Value

**Carcinogenicity**

Name	Route	Species	Value

**Reproductive Toxicity**

**Reproductive and/or Development Effects**

Name	Route	Species	Value

**Target Organ(s)**

**Specific Target Organ Toxicity – repeated exposure**

Name	Route	Species	Value

**Aspiration Hazard**

Name	Route	Species	Value

**Section 12: Ecological information**

**Acute Toxicity**

Acute and Prolonged Toxicity to Fish:  
No Data

Acute Toxicity to Aquatic Invertebrates:  
No Data

**Environmental Fate and Pathways**

No Data

**Section 13: Disposal considerations**

**Disposal Methods:** Dispose of in accordance with local, state, and federal regulations. Always contact a permitted waste disposer TSD to assure compliance.

**Section 14: Transport Information**

**UN number**

not subject to transport regulations

**UN proper shipping name**

not assigned

**Transport hazard class(es)**

not assigned

**Packing group**

not assigned

**Environmental hazards**

non-environmentally hazardous acc. to the dangerous goods regulations

**Special precautions for user**

There is no additional information.

**Transport in bulk according to Annex II of MARPOL and the IBC Code**

The cargo is not intended to be carried in bulk.

**Information for each of the UN Model Regulations**

**Transport of dangerous goods by road or rail (49 CFR US DOT)**

Not subject to transport regulations.

**International Maritime Dangerous Goods Code (IMDG)**

Not subject to IMDG.

**International Civil Aviation Organization (ICAO-IATA/DGR)**

Not subject to ICAO-IATA.

**Section 15: Regulatory information**

**Amendments and Reauthorization Act of 1986 Title III (Emergency Planning and Community Right-to-Know Act of 1986) Sections 311 and 312**

No SARA Hazards

**Superfund Amendments and Reauthorization Act of 1986 Title III (Emergency Planning and Community Right-to-Know Act of 1986) Section 313**

This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313

**Comprehensive Environmental Response, Compensation, and Liability Act of 1980 (CERCLA) Section 103**

This material does not contain any components with a CERCLA RQ

**California Prop. 65**

This product does not contain any chemicals known to State of California to cause cancer, birth defects, or any other reproductive harm.

**United States TSCA Inventory (TSCA)**

All components of this product are in compliance with the inventory listing requirements of the U.S. Toxic Substances Control Act (TSCA) Chemical Substance Inventory

**Section 16: Other information, including date of preparation or last revision**

**NFPA Hazardous Classification**

Health: 1

Flammability: 0

Instability: 0

Special Hazard: None

**Revision Indicator:**

SDS Revision # 8 / Issued 2/24/2023

The information contained herein is based on data considered to be accurate. However, the information is provided without any warranty, expressed or implied, regarding its correctness. The conditions or methods of handling, storage, use and disposal of the product are beyond our control and may be beyond our knowledge. For this and other reasons, we do not assume responsibility and expressly disclaim liability for loss, damage or expense arising out of or in any way connected with handling, storage, use or disposal of the product.

