

High Velocity Drum Fans Belt Drive



Model Code:

DFC -24 B
A B C

A: Series

B: Fan Diameter
(36", 42", 48")

C: B = Belt Drive Motor



- 2-speed switch Belt drive motor
- Incredibly quiet for its size & performance levels
- 4 aerodynamically balanced blades
- Convenient handles & Rugged wheels
- Meets OSHA 1910.212(A)(5) requirements
- 9 Ft, 120V grounded cord & plug
- Scratch resistant, powder- coated finish
- Built-In cord wrap
- Heavy duty 20 gauge steel drum
- Reinforced with tubular cross braces
- Standard color: King Green
- 1-year limited warranty

The King High Velocity Drum Fans - Belt Drive

King High Velocity Industrial Belt Drive Drum Fans were specifically designed for industrial applications where quality, performance, and durability are required. Rugged and reliable, they make less noise and use a lower power load, which gives the fan's motor a longer life. The 2-speed, belt drive fan has 4 aerodynamically balanced aluminum blades for even, steady airflow and to provide maximum airflow and motor efficiency. The scratch-resistant King green finish looks sharp and is easy to clean. Rugged flat-free wheels with metal hubs last for years and roll easily over uneven surfaces. Cord wrap for convenient storage. UL listed.

Ordering Information

MODEL NUMBER	UPC #093319	DESCRIPTION	CFM	WT. (lbs.)
DFC-42B	32711	Drum Fan, 42" Belt Drive, Fixed	15800	96.01
DFC-48B	32712	Drum Fan, 48" Belt Drive, Fixed	17800	118.5

Accessories

MODEL	UPC	DESCRIPTION	SHIP WEIGHT lbs
FAN-SPEED-CONTROLLER	55378	Fan Motor Variable Speed Control Plug-In, 120V 2.5A Max	.05



FAN-SPEED-CONTROLLER

High Velocity Drum Fans Direct Drive



Model Code:

DFC -24 D -S
A B C D

A: Series
B: Fan Diameter
(36", 42", 48")
C: D = Direct Drive Motor
D: -S = Swivel Base (Optional)



- 2-speed switch Belt drive motor
- 3 aerodynamically balanced blades
- Convenient handles & Rugged wheels
- Meets OSHA 1910.212(A)(5) requirements
- 9 Ft, 120V grounded cord & plug
- Scratch resistant, powder- coated finish
- Built-in cord wrap
- Heavy duty 20 gauge steel drum
- Reinforced with tubular cross braces
- Standard color: King Green
- Optional swivel base available
- 1-year limited warranty

The King High Velocity Drum Fans - Direct Drive

King High Velocity Direct Drive Drum Fans are great for heavy duty air circulation in light duty commercial applications where an economical solution is needed. They are dependable, running on less power and require less maintenance compared to other motors. The 2-speed, direct drive fan has 3 aerodynamically balanced aluminum blades for even, steady airflow and to provide maximum airflow and motor efficiency. The scratch resistant King green finish looks sharp and is easy to clean. Rugged flat-free wheels with metal hubs last for years and roll easily over uneven surfaces. Cord wrap for convenient storage. UL listed.

Ordering Information

MODEL NUMBER	UPC #093319	DESCRIPTION	CFM	WT. (lbs.)
DFC-24D-S	32705	Drum Fan, 24" Direct Drive, Swivel	7300	39.04
DFC-30D-S	32707	Drum Fan, 30" Direct Drive, Swivel	8800	54.96
DFC-36D	32709	Drum Fan, 36" Direct Drive, Fixed	11630	65.74

Accessories

MODEL	UPC	DESCRIPTION	SHIP WEIGHT lbs
FAN-SPEED-CONTROLLER	55378	Fan Motor Variable Speed Control Plug-In, 120V 2.5A Max	0.5



FAN-SPEED-CONTROLLER