



SAFETY DATA SHEET

1. Identification

Product identifier	Coated Abrasive Product
Other means of identification	
Product code	T000795
Recommended use	Abrasive Product
Recommended restrictions	None known.
Manufacturer/Importer/Supplier/Distributor information	
United States	
Address:	Saint-Gobain Abrasives One New Bond Street Worcester, MA 01615
General Phone Number:	800-551-4413
Website:	www.Nortonabrasives.com
Canada	
Company name:	Saint-Gobain Canada, Inc.
Address:	28 Albert Street, W. Plattsville, ON NOJ 1S0
General Phone Number:	519-684-7441
Website:	www.Nortonabrasives.com
Emergency phone number:	508-795-5000
CHEMTREC:	For emergencies in the US or Canada, call CHEMTREC: 800-424-9300

2. Hazard(s) identification

Physical hazards	Not classified.
Health hazards	Not classified.
Environmental hazards	Not classified.
OSHA defined hazards	Not classified.
Label elements	
Hazard symbol	None.
Signal word	None.
Hazard statement	The mixture does not meet the criteria for classification.
Precautionary statement	
Prevention	Not available.
Response	Not available.
Storage	Not available.
Disposal	Not available.
Hazard(s) not otherwise classified (HNOC)	None known.

Supplemental information

60% of the mixture consists of component(s) of unknown acute oral toxicity. 100% of the mixture consists of component(s) of unknown acute dermal toxicity. 100% of the mixture consists of component(s) of unknown acute hazards to the aquatic environment. 100% of the mixture consists of component(s) of unknown long-term hazards to the aquatic environment.

3. Composition/information on ingredients**Mixtures**

Chemical name	Common name and synonyms	CAS number	%
Aluminum Oxide, Non-fibrous		1344-28-1	30 - 60
Nylon		No Data	10 - 30
Resin		9003-35-4	10 - 20
Polymer/solids		No Data	1 - 10

4. First-aid measures**Inhalation**

Move to fresh air. Call a physician if symptoms develop or persist.

Skin contact

Wash off with soap and water. Get medical attention if irritation develops and persists.

Eye contact

Rinse with water. Get medical attention if irritation develops and persists.

Ingestion

Rinse mouth. Get medical attention if symptoms occur.

Most important symptoms/effects, acute and delayed

Direct contact with eyes may cause temporary irritation.

Indication of immediate medical attention and special treatment needed

Treat symptomatically.

General information

Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures**Suitable extinguishing media**

Water fog. Foam. Dry chemical powder. Carbon dioxide (CO₂).

Unsuitable extinguishing media

Do not use water jet as an extinguisher, as this will spread the fire.

Specific hazards arising from the chemical

During fire, gases hazardous to health may be formed.

Special protective equipment and precautions for firefighters

Self-contained breathing apparatus and full protective clothing must be worn in case of fire.

Fire fighting equipment/instructions

Move containers from fire area if you can do so without risk.

Specific methods

Use standard firefighting procedures and consider the hazards of other involved materials.

General fire hazards

No unusual fire or explosion hazards noted.

6. Accidental release measures**Personal precautions, protective equipment and emergency procedures**

Keep unnecessary personnel away. For personal protection, see section 8 of the SDS.

Methods and materials for containment and cleaning up

Stop the flow of material, if this is without risk. Following product recovery, flush area with water. For waste disposal, see section 13 of the SDS.

Environmental precautions

Avoid discharge into drains, water courses or onto the ground.

7. Handling and storage**Precautions for safe handling**

Avoid prolonged exposure. For industrial or professional use only. Always read, understand and follow the Safety Guide insert as well as the Safety Data Sheet before use. Use care when handling and storing abrasive wheels and products. Always inspect products for cracks, chips, nicks and for possible damage before mounting and ring test vitrified wheels. Damaged product can break apart during use and cause serious injury. Always use a guard, never exceed maximum operating speed, mount and operate according to ANSI B7.1 for Bonded Abrasive products and ANSI B7.7 for Coated Abrasive products.

Conditions for safe storage, including any incompatibilities

Store in tightly closed container. Store away from incompatible materials (see Section 10 of the SDS).

Protective measures

Wear appropriate personal protective equipment (see Section 8). Use only with adequate ventilation. Avoid breathing dust. Read the Safety Data Sheet of the material you are grinding, polishing, cutting, sanding, etc. for appropriate respiratory protection.
Wash hands after handling

Storage conditions

Bonded Abrasive products should be stored according to ANSI B7.1 and not be exposed to extreme temperatures or conditions that cause condensation. Coated Abrasive products should be stored according to ANSI B7.7 and between 35-50% relative humidity and between 60-80 degrees Fahrenheit.

8. Exposure controls/personal protection

Occupational exposure limits

The following constituents are the only constituents of the product which have a PEL, TLV or other recommended exposure limit. At this time, the other constituents have no known exposure limits.

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Components	Type	Value	Form
Aluminum Oxide, Non-fibrous (CAS 1344-28-1)	PEL	5 mg/m3	Respirable fraction.
		15 mg/m3	Total dust.

US. OSHA Table Z-3 (29 CFR 1910.1000)

Components	Type	Value	Form
Aluminum Oxide, Non-fibrous (CAS 1344-28-1)	TWA	5 mg/m3	Respirable fraction.
		15 mg/m3	Total dust.
		50 mppcf	Total dust.
		15 mppcf	Respirable fraction.

US. ACGIH Threshold Limit Values

Components	Type	Value	Form
Aluminum Oxide, Non-fibrous (CAS 1344-28-1)	TWA	1 mg/m3	Respirable fraction.

Biological limit values

No biological exposure limits noted for the ingredient(s).

Appropriate engineering controls

Good general ventilation should be used. Ventilation rates should be matched to conditions. If applicable, use process enclosures, local exhaust ventilation, or other engineering controls to maintain airborne levels below recommended exposure limits. If exposure limits have not been established, maintain airborne levels to an acceptable level.

Individual protection measures, such as personal protective equipment

Eye/face protection Wear safety glasses with side shields (or goggles).

Skin protection

Hand protection Wear appropriate chemical resistant gloves.

Other Wear appropriate chemical resistant clothing.

Respiratory protection In case of insufficient ventilation, wear suitable respiratory equipment.

Thermal hazards Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations

Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants.

9. Physical and chemical properties

Appearance

Physical state Solid.

Form Solid.

Color Not available.

Odor Not available.

Odor threshold Not available.

pH	Not available.
Melting point/freezing point	3632 °F (2000 °C) estimated
Initial boiling point and boiling range	5390.6 °F (2977 °C) estimated
Flash point	Not available.
Evaporation rate	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	
Explosive limit - lower (%)	Not available.
Explosive limit - upper (%)	Not available.
Vapor pressure	-0.01 hPa estimated
Vapor density	Not available.
Relative density	Not available.
Solubility(ies)	
Solubility (water)	Not available.
Partition coefficient (n-octanol/water)	Not available.
Auto-ignition temperature	Not available.
Decomposition temperature	Not available.
Viscosity	Not available.
Other information	
Density	3.40 g/cm3 estimated
Explosive properties	Not explosive.
Oxidizing properties	Not oxidizing.
Specific gravity	3.4 estimated

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Material is stable under normal conditions.
Possibility of hazardous reactions	No dangerous reaction known under conditions of normal use.
Conditions to avoid	Contact with incompatible materials.
Incompatible materials	Acids. Chlorine.
Hazardous decomposition products	No hazardous decomposition products are known.

11. Toxicological information

Information on likely routes of exposure

Inhalation	Prolonged inhalation may be harmful.
Skin contact	No adverse effects due to skin contact are expected.
Eye contact	Direct contact with eyes may cause temporary irritation.
Ingestion	Expected to be a low ingestion hazard.

Symptoms related to the physical, chemical and toxicological characteristics Direct contact with eyes may cause temporary irritation.

Information on toxicological effects

Acute toxicity Not known.

Components	Species	Test Results
Aluminum Oxide, Non-fibrous (CAS 1344-28-1)		
Acute		
Oral		
LD50	Rat	> 5000 mg/kg

Skin corrosion/irritation	Due to partial or complete lack of data the classification is not possible.
Serious eye damage/eye irritation	Due to partial or complete lack of data the classification is not possible.
Respiratory or skin sensitization	
Respiratory sensitization	Due to partial or complete lack of data the classification is not possible.
Skin sensitization	Due to partial or complete lack of data the classification is not possible.
Germ cell mutagenicity	Due to partial or complete lack of data the classification is not possible.
Carcinogenicity	Due to partial or complete lack of data the classification is not possible.
IARC Monographs. Overall Evaluation of Carcinogenicity	
Not listed.	
OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)	
Not listed.	
US. National Toxicology Program (NTP) Report on Carcinogens	
Not listed.	
Reproductive toxicity	Due to partial or complete lack of data the classification is not possible.
Specific target organ toxicity - single exposure	Due to partial or complete lack of data the classification is not possible.
Specific target organ toxicity - repeated exposure	Due to partial or complete lack of data the classification is not possible.
Aspiration hazard	Due to partial or complete lack of data the classification is not possible.
Chronic effects	Prolonged inhalation may be harmful.
Further information	This product has no known adverse effect on human health.

12. Ecological information

Ecotoxicity	The product is not classified as environmentally hazardous. However, this does not exclude the possibility that large or frequent spills can have a harmful or damaging effect on the environment.
Persistence and degradability	No data is available on the degradability of any ingredients in the mixture.
Bioaccumulative potential	No data available.
Mobility in soil	No data available.
Other adverse effects	No other adverse environmental effects (e.g. ozone depletion, photochemical ozone creation potential, endocrine disruption, global warming potential) are expected from this component.

13. Disposal considerations

Disposal instructions	Collect and reclaim or dispose in sealed containers at licensed waste disposal site.
Local disposal regulations	Dispose in accordance with all applicable regulations.
Hazardous waste code	The waste code should be assigned in discussion between the user, the producer and the waste disposal company.
Waste from residues / unused products	Dispose of in accordance with local regulations. Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe manner (see: Disposal instructions).
Contaminated packaging	Since emptied containers may retain product residue, follow label warnings even after container is emptied. Empty containers should be taken to an approved waste handling site for recycling or disposal.

14. Transport information

DOT	Not regulated as dangerous goods.
IATA	Not regulated as dangerous goods.
IMDG	Not regulated as dangerous goods.
Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	Not applicable.

15. Regulatory information

US federal regulations

This product is not known to be a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

Toxic Substances Control Act (TSCA)

One or more components of the mixture are not on the TSCA 8(b) inventory or are designated "inactive".

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Not listed.

SARA 304 Emergency release notification

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1053)

Not listed.

Superfund Amendments and Reauthorization Act of 1986 (SARA)

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical

No

SARA 313 (TRI reporting)

Chemical name	CAS number	% by wt.
Aluminum Oxide, Non-fibrous	1344-28-1	30 - 60

Other federal regulations

Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Not regulated.

Safe Drinking Water Act (SDWA)

Not regulated.

US state regulations

California Proposition 65

California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins. For more information go to www.P65Warnings.ca.gov. According to the Superior Court of California Consent Judgement 995893 issued on September 29, 2000 abrasive products from Saint-Gobain Abrasives are exempt from the Proposition 65 warning requirements.

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Industrial Chemicals (AICIS)	No
Canada	Domestic Substances List (DSL)	No
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	No
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	No
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	No
Korea	Existing Chemicals List (ECL)	No
New Zealand	New Zealand Inventory	No
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	No
Taiwan	Taiwan Chemical Substance Inventory (TCSI)	No
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	No

*A "Yes" indicates that all components of this product comply with the inventory requirements administered by the governing country(s)

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date 01-31-2023

Version # 01

Disclaimer Saint Gobain Abrasives, Inc. cannot anticipate all conditions under which this information and its product, or the products of other manufacturers in combination with its product, may be used. It is the user's responsibility to ensure safe conditions for handling, storage and disposal of the product, and to assume liability for loss, injury, damage or expense due to improper use. The information in the sheet was written based on the best knowledge and experience currently available. Information for this material safety data sheet was obtained from sources considered technically accurate and reliable. While every effort has been made to ensure full disclosure of product hazards, in some cases data is not available and is so stated. Since conditions of actual product use are beyond control of the supplier, it is assumed that users of this material have been fully trained according to the mandatory requirements of WHMIS. No warranty, expressed or implied, is made and supplier will not be liable for any losses, injuries or consequential damages which may result from the use of or reliance on any information contained in this form. If user requires independent information on ingredients in this or any other material, we recommend contact with the Canadian Centre for Occupational Health and Safety (CCOHS) in Hamilton, Ontario (1-800-263-8466) or CSST in Montreal, Quebec (514-873-3990).