

NOBLELIFT

INDUSTRIAL EQUIPMENT

AC55






PREMIUM PALLET JACK

Best Seller Worldwide

NOBLELIFT

INDUSTRIAL EQUIPMENT

**Weight Capacity:
5500 lbs.**



AC55

WHY CHOOSE BETWEEN PRICE AND QUALITY WHEN YOU CAN HAVE BOTH

PREMIUM PALLET JACK

- Top class range of pallet trucks with excellent ergonomic designs .
- Professional and ideal storage aid for all variety of manual transport tasks over short distances in stores, warehouses and factory plants .
- Reliable, sturdy, torsion-resistant due to its extremely strong high quality steel profile . German WAGNER paint system ensures best powder coating and painting quality .
- All pivots points are greased for excellent maneuverability and effortless steering. Chromed bearing bushes and joints ensure quiet running application and particularly long service life .
- High quality galvanized whole casting hydraulic pump, robust and durable, with fine control of lowering speed, overload valve, and low maintenance .

AUTHORIZED DEALER

Item/Type		AC55-1836	AC55-1848
Capacity Q	lbs	5500	5500
Min. fork height h	Inch	2.75"	2.75"
Max. fork height h ₁	Inch	7.5	7.5
Steering wheel	Inch	φ 2"×7"	φ 2"×7"
Load roller Single	Inch	φ O.D:2.75 W:3.7	
Size of fork e*s	Inch	6.3×2.4	6.3×2.4
Width overall forks B	Inch	18"	18"
Fork length l	Inch	36"	48"
Special sizes under request			
Optional fork length	Inch	42" (Special Order)	