

Project: _____

Fixture Type: _____

Location: _____

Contact: _____

P500167-109 Carriage Hill

Featuring artful angles and soft metal tones, the Carriage Hill Collection offers a sophisticated six-light pendant design for Traditional interiors. A crisp fabric shade forms a hexagonal shape to surround an interior candelabra cluster in Brushed Bronze.

- This debonair six-light pendant is all about angles and curves, adding a jaunty look to your interiors
- A crisp, hexagonal linen shade gives studious accent to the sinuous brushed-metal frame
- These pendants make the best impact when displayed in libraries, home offices, sitting rooms, entryways and foyers, or breakfast areas
- Traditional interiors get a boost with the Carriage Hill pendants
- Elegant Brushed Bronze finish
- Measures 28 7/8in diameter x 28 7/8in ht.
- Uses six 60-watt max. candelabra bulbs including LED equivalent (sold separately)
- Compatible with standard wall dimmer
- Progress Lighting products are designed for exceptional quality, reliability, and functionality
- Includes installation instructions and mounting hardware
- Coordinating fixtures available

Category: Chandeliers

Finish: Brushed Bronze (plated)

Construction: Steel Construction

Glass/Shade: Ecru linen Shade



Diameter: 28-7/8 in
Height: 28-7/8 in
Overall Ht. W/Chain: 104 in

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
Ceiling mounted	Prewired	Quantity:	CULus Dry Location Listed
Mounting strap for outlet box included	15 feet of wire supplied	Six 60 W max. Candelabra Base or LED equivalent	1-year Limited Warranty
6 feet of 9 gauge chain supplied	120 V	E12 base phenolic sockets	
Canopy covers a standard 4" recessed outlet box: 5.25" W., 1.25" ht., 5.25" depth			