

ELECTRIC CHAIN HOIST



Removeable top hook with safety latch for optional motorized trolley.

Durable canvas chain container.


Paddle type limit switches for easy adjustment and consistent stopping points.

Japanese FEC 80 Chain.

European 24v pendant control with emergency power isolation switch.

CAPACITY
½ Ton – 5 Ton

LIFT SPEED
½ Ton: 26 FPM
1 Ton: 26 FPM
2 Ton: 26 FPM
3 Ton: 21 FPM
5 Ton: 11 FPM




Variable Speed Controls Available

Load tested to 125% of the rated capacity

360° swivel hook with safety hook latch.

KEY COMPONENTS

⚙️ Cooling fan to prevent motor from overheating during continuous usage.



⚙️ Electromagnetic braking system tested to hold 125% of rated capacity.

⚙️ Overload clutch will slip under excessive load to prevent damage.

⚙️ Schneider Electric AC Contactor