

1. IDENTIFICATION

Product identifier

Product Name Fast Dry Stain Special Walnut

Other means of identification

Product Code 61104
SKU(s) 61101, 61104, 61116

Recommended use of the chemical and restrictions on use

Recommended Use No information available.
Uses advised against No information available

Details of the supplier of the safety data sheet

Supplier Address
Old Masters
303 19th St. SE
Orange City, IA 51041
Phone: 712-737-4993
Fax: 712-737-4997

Emergency telephone number

Emergency Telephone Chemtrec 1-800-424-9300

2. HAZARDS IDENTIFICATION

Classification

OSHA Regulatory Status

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Skin sensitization	Category 1
Germ cell mutagenicity	Category 1B
Carcinogenicity	Category 1A
Aspiration toxicity	Category 1
Flammable liquids	Category 3

Emergency Overview

Danger

Hazard statements

May cause an allergic skin reaction
May cause genetic defects
May cause cancer
May be fatal if swallowed and enters airways
Flammable liquid and vapor



	Consult a physician.
Skin Contact	Call a physician immediately.
Inhalation	Move victim to fresh air. If breathing is irregular or stopped, administer artificial respiration. Call a physician immediately.
Ingestion	Do NOT induce vomiting. Drink 1 or 2 glasses of water. Never give anything by mouth to an unconscious person. Get medical attention.

Most important symptoms and effects, both acute and delayed

Symptoms No information available.

Indication of any immediate medical attention and special treatment needed

Note to physicians Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media CAUTION: Use of water spray when fighting fire may be inefficient.

Specific hazards arising from the chemical

Flammable. WARNING: Spontaneous combustion (fire) may result from materials such as rags, steel wool, paper, clothing, and other waste soaked in linseed oil. Place in a sealed, water filled, metal container to prevent this.

Explosion data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge None.

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Remove all sources of ignition. Use personal protective equipment as required.

Environmental precautions

Environmental precautions Do not flush into surface water or sanitary sewer system. See Section 12 for additional Ecological Information.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Cover liquid spill with sand, earth or other non-combustible absorbent material. Soak up with inert absorbent material.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Avoid contact with skin, eyes or clothing.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep away from heat, sparks, flame and other sources of ignition (i.e., pilot lights, electric motors and static electricity).

Incompatible materials Chlorinated compounds.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical name	ACGIH TLV	OSHA PEL	NIOSH
Xylene 1330-20-7	STEL: 150 ppm TWA: 100 ppm	TWA: 100 ppm TWA: 435 mg/m ³ (vacated) TWA: 100 ppm (vacated) TWA: 435 mg/m ³ (vacated) STEL: 150 ppm (vacated) STEL: 655 mg/m ³	-
Ethyl Benzene 100-41-4	TWA: 20 ppm	TWA: 100 ppm TWA: 435 mg/m ³ (vacated) TWA: 100 ppm (vacated) TWA: 435 mg/m ³ (vacated) STEL: 125 ppm (vacated) STEL: 545 mg/m ³	IDLH: 800 ppm TWA: 100 ppm TWA: 435 mg/m ³ STEL: 125 ppm STEL: 545 mg/m ³
Crystalline Silica 14808-60-7	TWA: 0.025 mg/m ³ respirable particulate matter	TWA: 50 µg/m ³ TWA: 50 µg/m ³ excludes construction work, agricultural operations, and exposures that result from the processing of sorptive clays (vacated) TWA: 0.1 mg/m ³ respirable dust : (250)/(%SiO ₂ + 5) mppcf TWA respirable fraction : (10)/(%SiO ₂ + 2) mg/m ³ TWA respirable fraction	IDLH: 50 mg/m ³ respirable dust TWA: 0.05 mg/m ³ respirable dust
Carbon Black 1333-86-4	TWA: 3 mg/m ³ inhalable particulate matter	TWA: 3.5 mg/m ³ (vacated) TWA: 3.5 mg/m ³	IDLH: 1750 mg/m ³ TWA: 3.5 mg/m ³ TWA: 0.1 mg/m ³ Carbon black in presence of Polycyclic aromatic hydrocarbons PAH

NIOSH Immediately Dangerous to Life or Health

Other Information Vacated limits revoked by the Court of Appeals decision in AFL-CIO v. OSHA, 965 F.2d 962 (11th Cir., 1992).

Appropriate engineering controls

Engineering Controls Showers
Eyewash stations
Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/face protection No special technical protective measures are necessary.

Skin and body protection No special technical protective measures are necessary.

Respiratory protection If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

General Hygiene Considerations Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical state	Liquid	Odor	No information available
Appearance	No information available	Odor threshold	No information available
Color	No information available		

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	No information available	
Melting point / freezing point	No information available	
Boiling point / boiling range	>= 80 °C / 176 °F	
Flash point	39 °C / 102 °F	
Evaporation rate	No information available	
Flammability (solid, gas)	No information available	
Flammability Limit in Air		
Upper flammability limit:	No information available	
Lower flammability limit:	No information available	
Vapor pressure	No information available	
Vapor density	No information available	
Specific Gravity	0.88	
Water solubility	No information available	
Solubility in other solvents	No information available	
Partition coefficient	No information available	
Autoignition temperature	No information available	
Decomposition temperature	No information available	
Kinematic viscosity	No information available	
Dynamic viscosity	No information available	
Explosive properties	No information available	
Oxidizing properties	No information available	

Other Information

Softening point	No information available
Molecular weight	No information available
Liquid Density	7.30 lbs/gal
Bulk density	No information available
Percent solids by weight	37.7%
Percent volatile by weight	62.3%
Percent solids by volume	30.1%
Actual VOC (lbs/gal)	4.5
Actual VOC (grams/liter)	545.2
EPA VOC (lbs/gal)	4.5
EPA VOC (grams/liter)	545.2
EPA VOC (lb/gal solids)	15.1

10. STABILITY AND REACTIVITY**Reactivity**

No data available

Chemical stability

Stable under recommended storage conditions.

Possibility of hazardous reactions

None under normal processing.

Conditions to avoid

Heat, flames and sparks.

Incompatible materials

Chlorinated compounds.

Hazardous decomposition products

Carbon oxides.

11. TOXICOLOGICAL INFORMATION**Information on likely routes of exposure**

Product Information	No data available
Inhalation	No data available.
Eye contact	No data available.
Skin Contact	No data available.
Ingestion	No data available.

Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
Solvent Naphtha, Medium Aliphatic 64742-88-7	> 25 mL/kg (Rat)	> 3000 mg/kg (Rabbit)	> 13 mg/L (Rat) 4 h
Linseed Oil 8001-26-1	> 15,000 mg/kg	-	-
Xylene 1330-20-7	= 3500 mg/kg (Rat)	> 1700 mg/kg (Rabbit) > 4350 mg/kg (Rabbit)	= 29.08 mg/L (Rat) 4 h = 5000 ppm (Rat) 4 h
Methyl Ethyl Ketoxime 96-29-7	= 930 mg/kg (Rat)	1000 - 1800 mg/kg (Rabbit)	> 4.83 mg/L (Rat) 4 h
Ethyl Benzene 100-41-4	= 3500 mg/kg (Rat)	= 15400 mg/kg (Rabbit)	= 17.4 mg/L (Rat) 4 h
Mineral Spirits 64742-48-9	> 6000 mg/kg (Rat)	> 3160 mg/kg (Rabbit)	> 8500 mg/m ³ (Rat) 4 h
Crystalline Silica 14808-60-7	> 22,500 mg/kg (Rat)	-	-
Carbon Black 1333-86-4	> 15400 mg/kg (Rat)	> 3 g/kg (Rabbit)	-

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms No information available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Sensitization No information available.

Germ cell mutagenicity No information available.

Carcinogenicity No information available.

Chemical name	ACGIH	IARC	NTP	OSHA
Xylene 1330-20-7	-	Group 3	-	-
Ethyl Benzene 100-41-4	A3	Group 2B	-	X
Crystalline Silica 14808-60-7	A2	Group 1	Known	X
Carbon Black 1333-86-4	A3	Group 2B	-	X

ACGIH (American Conference of Governmental Industrial Hygienists)

A2 - Suspected Human Carcinogen

A3 - Animal Carcinogen

IARC (International Agency for Research on Cancer)

Group 1 - Carcinogenic to Humans

Group 2B - Possibly Carcinogenic to Humans

Group 3 - Not classifiable as a human carcinogen

NTP (National Toxicology Program)

Known - Known Carcinogen

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present

Reproductive toxicity	No information available.
STOT - single exposure	No information available.
STOT - repeated exposure	No information available.
Chronic toxicity	Ethylbenzene has been classified by the International Agency for Research on Cancer (IARC) as possibly carcinogenic to humans (Group 2B). Prolonged or repeated overexposure to ethylbenzene may result in adverse effects to the kidneys, liver, respiratory system, thyroid, testicles, and pituitary glands.
Aspiration hazard	No information available.

Numerical measures of toxicity - Product Information

The following values are calculated based on chapter 3.1 of the GHS document mg/kg mg/l

12. ECOLOGICAL INFORMATION

Ecotoxicity

Harmful to aquatic life with long lasting effects

2.64% of the mixture consists of component(s) of unknown hazards to the aquatic environment

Chemical name	Algae/aquatic plants	Fish	Crustacea
Solvent Naphtha, Medium Aliphatic 64742-88-7	450: 96 h Pseudokirchneriella subcapitata mg/L EC50	800: 96 h Pimephales promelas mg/L LC50 static	100: 48 h Daphnia magna mg/L EC50
Xylene 1330-20-7	-	13.4: 96 h Pimephales promelas mg/L LC50 flow-through 13.1 - 16.5: 96 h Lepomis macrochirus mg/L LC50 flow-through 13.5 - 17.3: 96 h Oncorhynchus mykiss mg/L LC50 30.26 - 40.75: 96 h Poecilia reticulata mg/L LC50 static 2.661 - 4.093: 96 h Oncorhynchus mykiss mg/L LC50 static 23.53 - 29.97: 96 h Pimephales promelas mg/L LC50 static 780: 96 h Cyprinus carpio mg/L LC50 semi-static 780: 96 h Cyprinus carpio mg/L LC50 7.711 - 9.591: 96 h Lepomis macrochirus mg/L LC50 static 19: 96 h Lepomis macrochirus mg/L LC50	3.82: 48 h water flea mg/L EC50 0.6: 48 h Gammarus lacustris mg/L LC50
Methyl Ethyl Ketoxime 96-29-7	83: 72 h Desmodesmus subspicatus mg/L EC50	760: 96 h Poecilia reticulata mg/L LC50 static 320 - 1000: 96 h Leuciscus idus mg/L LC50 static 777 - 914: 96 h Pimephales promelas mg/L LC50 flow-through	750: 48 h Daphnia magna mg/L EC50
Ethyl Benzene 100-41-4	438: 96 h Pseudokirchneriella subcapitata mg/L EC50 2.6 - 11.3: 72 h Pseudokirchneriella subcapitata mg/L EC50 static 4.6: 72 h Pseudokirchneriella subcapitata mg/L EC50 1.7 - 7.6: 96 h Pseudokirchneriella subcapitata mg/L EC50 static	11.0 - 18.0: 96 h Oncorhynchus mykiss mg/L LC50 static 4.2: 96 h Oncorhynchus mykiss mg/L LC50 semi-static 7.55 - 11: 96 h Pimephales promelas mg/L LC50 flow-through 9.1 - 15.6: 96 h Pimephales promelas mg/L LC50 static 32: 96 h Lepomis macrochirus mg/L LC50 static 9.6: 96 h Poecilia reticulata mg/L LC50 static	1.8 - 2.4: 48 h Daphnia magna mg/L EC50
Mineral Spirits 64742-48-9	-	2200: 96 h Pimephales promelas mg/L LC50	2.6: 96 h Chaetogammarus marinus mg/L LC50
Carbon Black 1333-86-4	-	-	5600: 24 h Daphnia magna mg/L EC50

Persistence and degradability

No information available.

Bioaccumulation

No information available.

Chemical name	Partition coefficient
---------------	-----------------------

Xylene 1330-20-7	2.77 - 3.15
Methyl Ethyl Ketoxime 96-29-7	0.65
Ethyl Benzene 100-41-4	3.2

Other adverse effects No information available

13. DISPOSAL CONSIDERATIONS

Waste treatment methods

Disposal of wastes Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated packaging Do not reuse container.

US EPA Waste Number D001 U019 U055 U073 U220 U239

Chemical name	RCRA	RCRA - Basis for Listing	RCRA - D Series Wastes	RCRA - U Series Wastes
Xylene 1330-20-7	-	Included in waste stream: F039	-	U239
Ethyl Benzene 100-41-4	-	Included in waste stream: F039	-	-

This product contains one or more substances that are listed with the State of California as a hazardous waste.

Chemical name	California Hazardous Waste Status
Xylene 1330-20-7	Toxic Ignitable
Ethyl Benzene 100-41-4	Toxic Ignitable

14. TRANSPORT INFORMATION

DOT Not regulated

TDG Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA Complies
DSL/NDL Complies *

* This product contains an unknown chemical, therefore, this product's compliance to the inventory list is NOT DETERMINED

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

Chemical name	SARA 313 - Threshold Values %
Xylene	1.0
Ethyl Benzene	0.1

SARA 311/312 Hazard Categories

Acute health hazard	Yes
Chronic Health Hazard	No
Fire hazard	Yes
Sudden release of pressure hazard	No
Reactive Hazard	No

CWA (Clean Water Act)

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

Chemical name	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Xylene 1330-20-7	100 lb	-	-	X
Ethyl Benzene 100-41-4	1000 lb	X	X	X

CERCLA

This material, as supplied, contains one or more substances regulated as a hazardous substance under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302)

Chemical name	Hazardous Substances RQs	CERCLA/SARA RQ	Reportable Quantity (RQ)
Xylene 1330-20-7	100 lb	-	RQ 100 lb final RQ RQ 45.4 kg final RQ
Ethyl Benzene 100-41-4	1000 lb	-	RQ 1000 lb final RQ RQ 454 kg final RQ

US State Regulations**California Proposition 65**

This product contains the following Proposition 65 chemicals

Chemical name	California Proposition 65
Ethyl Benzene - 100-41-4	Carcinogen
Crystalline Silica - 14808-60-7	Carcinogen
Carbon Black - 1333-86-4	Carcinogen
Toluene - 108-88-3	Developmental
Benzene(including benzene from gasoline) - 71-43-2	Carcinogen Developmental Male Reproductive
Cumene - 98-82-8	Carcinogen
3,3'-Dichlorobenzidine - 91-94-1	Carcinogen
Ethylene Glycol - 107-21-1	Developmental

U.S. State Right-to-Know Regulations

Chemical name	New Jersey	Massachusetts
Xylene 1330-20-7	X	X
Ethyl Benzene 100-41-4	X	X
Crystalline Silica 14808-60-7	X	X
Carbon Black 1333-86-4	X	X

Chemical name	Pennsylvania
Linseed Oil 8001-26-1	X

Xylene 1330-20-7	X
---------------------	---

U.S. EPA Label Information

EPA Pesticide Registration Number Not applicable

Hazardous air pollutants (HAPS) content

LIST OF HAZARDOUS AIR POLLUTANTS SUBJECT TO THE PROVISIONS OF THE CLEAN AIR ACT, TITLE I SECTION 112 'National Emission Standards for Hazardous Air Pollutants' (present individually at 1% by weight, or greater):

Chemical name	Weight % of HAPS in Product	Pounds HAPS / Gal Product
Xylene 1330-20-7	1.33%	0.10

16. OTHER INFORMATION, INCLUDING DATE OF PREPARATION OF THE LAST REVISION

NFPA	Health hazards 2	Flammability 2	Instability 0	Physical and chemical properties -
HMIS	Health hazards 2 *	Flammability 2	Physical hazards 0	Personal protection X
<i>Chronic Hazard Star Legend</i>	<i>* = Chronic Health Hazard</i>			

Revision Date 19-May-2020

Revision Note

No information available

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text. Shipping information may vary based upon container size and shipping destination. Each user of this material needs to evaluate the conditions of use and design the appropriate protective mechanisms to prevent employee exposures, property damage, or release to the environment. The manufacturer assumes no responsibility for injury to the recipient or third persons, or for any damages to any property resulting from misuse of the product.

End of Safety Data Sheet