

Technical drawing of a probe with dimensions A through K and reference dimensions F, G, and J. The drawing includes a side view and a detail view of the probe tip.

Dimensions and Tolerances:

- A $\pm .01 (.25)$
- B $\pm .01 (.25)$
- C REF.
- D
- E
- F REF.
- G REF.
- H REF. NOMINAL HOLE DIAMETER $\pm .016 (.41)$
- J REF.
- K REF.

PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	G in (mm)	H in (mm)	J in (mm)	K in (mm)	MAX. PANEL THICKNESS in (mm)	MIN. LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT 100 pcs lbs (g)
	MIN. in (mm)	MAX. in (mm)														
PLWP30SC	.12 (3)	1.18 (30)	.05 (1.3)	.19 (4.8)	.46 (11.7)	.22 (5.6)	.32 (8.1)	5.8 (147.3)	.74 (18.8)	.266 (6.8)	1.3 (33)	.30 (7.6)	.118 (3.0)	50 (222)	STANDARD	.32 (145)
PLWP40SC	.12 (3)	1.58 (40)	.05 (1.3)	.19 (4.8)	.46 (11.7)	.22 (5.6)	.32 (8.1)	7.0 (178)	.74 (18.8)	.266 (6.8)	1.3 (33)	.30 (7.6)	.118 (3.0)	50 (222)	STANDARD	.37 (168)
PLWP50SC	.12 (3)	1.97 (50)	.05 (1.3)	.19 (4.8)	.46 (11.7)	.22 (5.6)	.32 (8.1)	8.2 (208.3)	.74 (18.8)	.266 (6.8)	1.3 (33)	.30 (7.6)	.118 (3.0)	50 (222)	STANDARD	.42 (191)

1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

										CAD FILENAME/LAYERS	
										DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS	
										PANDUIT CORP. TINLEY PARK, ILLINOIS	
										WINGED PUSH MOUNT CABLE TIE PLWP30, 40, 50SC	
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .1(2.5) (.XXX) ± .020(.51) (.XX) ± .02(.5) ANGLES ± ----	
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
										DRAWN BY	SO
										MAT'L:	
										SCALE	NONE
10	10/28/04	JABO		CHANGED FORMAT FOR CONSISTENCY SEE ECN FOR DETAILS		26267	10			DATE	12/14/90
REV	DATE	BY	CHK	DESCRIPTION		ECN	-	R	CUST	SUP	CHK'D
											HVP
											HEAT STABILIZED NYLON 6.6 BLACK (-30)
											DRAWING NO.
											SS-26267
											DWG A SIZE