

# Safety Data Sheet



## 1. Identification

<b>Product Name:</b>	UNVRSL SSPR 6PK HAMMERED CLEAR	<b>Revision Date:</b>	10/18/2023
<b>Product Identifier:</b>	302153	<b>Supersedes Date:</b>	1/8/2016
<b>Recommended Use:</b>	Aerosol Topcoat		
<b>Supplier:</b>	Rust-Oleum Corporation 11 Hawthorn Parkway Vernon Hills, IL 60061 USA	<b>Manufacturer:</b>	Rust-Oleum Corporation 11 Hawthorn Parkway Vernon Hills, IL 60061 USA
<b>Preparer:</b>	Regulatory Department		
<b>Emergency Telephone:</b>	24 Hour Hotline: 847-367-7700		

## 2. Hazards Identification

### Classification

#### Symbol(s) of Product



#### Signal Word

Danger

#### Possible Hazards

22% of the mixture consists of ingredient(s) of unknown acute toxicity.

#### GHS HAZARD STATEMENTS

Flammable Aerosol, category 1	H222	Extremely flammable aerosol.
Eye Irritation, category 2A	H319	Causes serious eye irritation.
STOT, Single Exposure, category 3, NE	H336	May cause drowsiness or dizziness.
Carcinogenicity, category 2	H351	Suspected of causing cancer.
Reproductive Toxicity, category 2	H361	Suspected of damaging fertility or the unborn child.
Gases under Pressure; Compressed Gas	H280	Contains gas under pressure; may explode if heated.

#### GHS LABEL PRECAUTIONARY STATEMENTS

P201	Obtain special instructions before use.
P210	Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211	Do not spray on an open flame or other ignition source.
P251	Do not pierce or burn, even after use.
P264	Wash thoroughly after handling.
P280	Wear protective gloves / protective clothing / eye protection / face protection.
P405	Store locked up.
P501	Dispose of contents and container in accordance with local, regional and national regulations.

P304+P340	IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P305+P351+P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P308+P313	IF exposed or concerned: Get medical advice/attention.
P403+P233	Store in a well-ventilated place. Keep container tightly closed.
P410+P403	Protect from sunlight. Store in a well-ventilated place.
P410+P412	Protect from sunlight. Do not expose to temperatures exceeding 50°C / 122°F.
P203	Obtain, read, and follow all safety instructions before use.
P317	Get medical help.
P308+P316	IF exposed or concerned: Get emergency medical help immediately.
P337+P317	If eye irritation persists: Get medical help.

### 3. Composition / Information on Ingredients

#### HAZARDOUS SUBSTANCES

<u>Chemical Name</u>	<u>CAS-No.</u>	<u>Wt.% Range</u>	<u>GHS Symbols</u>	<u>GHS Statements</u>
Acetone	67-64-1	25-50	GHS02-GHS07	H225-319-332-336
Propane	74-98-6	10-25	GHS04	H280
n-Butyl Acetate	123-86-4	10-25	GHS02-GHS07	H226-336
n-Butane	106-97-8	2.5-10	GHS04	H280
Ethyl Acetate	141-78-6	2.5-10	GHS02-GHS07	H225-319-332-336
Xylenes (o-, m-, p- Isomers)	1330-20-7	2.5-10	GHS02-GHS07	H226-315-319-332
Ethylbenzene	100-41-4	0.1-1.0	GHS02-GHS07-GHS08	H225-304-332-351-373
Toluene	108-88-3	0.1-1.0	GHS02-GHS07-GHS08	H225-304-315-332-336-361-373

### 4. First-Aid Measures

**FIRST AID - EYE CONTACT:** Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed. Remove contact lenses, if present and easy to do. Continue rinsing.

**FIRST AID - SKIN CONTACT:** Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persists.

**FIRST AID - INHALATION:** Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately.

**FIRST AID - INGESTION:** If swallowed, do not induce vomiting. If victim is conscious and alert, give 2 to 4 cupfuls of water or milk. Call a physician or poison control center immediately. Never give anything by mouth to an unconscious person. Treat symptomatically and supportively.

### 5. Fire-Fighting Measures

**EXTINGUISHING MEDIA:** Aqueous Film Forming Foam, Carbon Dioxide, Dry Chemical, Dry Sand, Water Fog

**UNUSUAL FIRE AND EXPLOSION HAZARDS:** Water spray may be ineffective. Closed containers may explode when exposed to extreme heat. Vapors may form explosive mixtures with air. Vapors can travel to a source of ignition and flash back. Isolate from heat, electrical equipment, sparks and open flame. Perforation of the pressurized container may cause bursting of the can. FLASH POINT IS LESS THAN -7°C (20°F). EXTREMELY FLAMMABLE LIQUID AND VAPOR!

**SPECIAL FIREFIGHTING PROCEDURES:** Water may be used to cool closed containers to prevent buildup of steam. Full protective equipment including self-contained breathing apparatus should be used. If water is used, fog nozzles are preferred. Evacuate area and fight fire from a safe distance. Use water spray to keep fire-exposed containers cool. Containers may explode when heated.

**Special Fire and Explosion Hazard (Combustible Dust):** Not a combustible dust.

## 6. Accidental Release Measures

**STEPS TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED:** Remove all sources of ignition, ventilate area and remove with inert absorbent and non-sparking tools. Dispose of according to local, state (provincial) and federal regulations. Do not incinerate closed containers. If spilled, contain spilled material and remove with inert absorbent. Dispose of contaminated absorbent, container, and unused contents in accordance with local, state, and federal regulations. Do not incinerate closed containers

## 7. Handling and Storage

**HANDLING:** Wash thoroughly after handling. Wash hands before eating. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Follow all SDS and label precautions even after container is emptied because it may retain product residues. Avoid breathing fumes, vapors, or mist. Do not get in eyes, on skin or clothing. Do not puncture or incinerate (burn) container, even after use.

**STORAGE:** Contents under pressure. Do not store above 120°F (49°C). Store large quantities in buildings designed and protected for storage of flammable aerosols. Keep away from heat, sparks, flame and sources of ignition.

**Advice on Safe Handling of Combustible Dust:** No Information

## 8. Exposure Controls / Personal Protection

Chemical Name	CAS-No.	Weight % Less Than	ACGIH TLV- TWA	ACGIH TLV- STEL	OSHA PEL-TWA	OSHA PEL- CEILING
Acetone	67-64-1	45.0	250 ppm	500 ppm	1000 ppm	N.E.
Propane	74-98-6	15.0	N.E.	N.E.	1000 ppm	N.E.
n-Butyl Acetate	123-86-4	15.0	50 ppm	150 ppm	150 ppm	N.E.
n-Butane	106-97-8	10.0	N.E.	1000 ppm	N.E.	N.E.
Ethyl Acetate	141-78-6	5.0	400 ppm	N.E.	400 ppm	N.E.
Xylenes (o-, m-, p- Isomers)	1330-20-7	5.0	20 ppm	N.E.	100 ppm	N.E.
Ethylbenzene	100-41-4	1.0	20 ppm	N.E.	100 ppm	N.E.
Toluene	108-88-3	1.0	20 ppm	N.E.	200 ppm	300 ppm

### PERSONAL PROTECTION

**ENGINEERING CONTROLS:** Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Use explosion-proof ventilation equipment. Facilities storing or utilizing this material should be equipped with an eyewash facility and a safety shower. Prevent build-up of vapors by opening all doors and windows to achieve cross-ventilation.

**RESPIRATORY PROTECTION:** A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 requirements must be followed whenever workplace conditions warrant a respirator's use. A NIOSH/MSHA approved air purifying respirator with organic vapor cartridge or canister may be permissible under certain circumstances where airborne concentrations are expected to exceed exposure limits.

**SKIN PROTECTION:** Use gloves to prevent prolonged skin contact. Nitrile or Neoprene gloves may afford adequate skin protection.

**EYE PROTECTION:** Use safety eyewear designed to protect against splash of liquids.

**OTHER PROTECTIVE EQUIPMENT:** Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications.

**HYGIENIC PRACTICES:** Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

**Engineering Measures for Combustible Dust:** No Information

## 9. Physical and Chemical Properties

<b>Appearance:</b>	Aerosolized Mist	<b>Physical State:</b>	Liquid
<b>Odor:</b>	Solvent Like	<b>Odor Threshold:</b>	N.E.
<b>Specific Gravity:</b>	0.755	<b>pH:</b>	N.A.
<b>Freeze Point, °C:</b>	N.D.	<b>Viscosity:</b>	N.D.
<b>Solubility in Water:</b>	Slight	<b>Partition Coefficient, n-octanol/ water:</b>	N.D.
<b>Decomposition Temp., °C:</b>	N.D.	<b>Explosive Limits, vol%:</b>	1.2 - 13.0
<b>Boiling Range, °C:</b>	-37 - 537	<b>Flash Point, °C:</b>	-96
<b>Flammability:</b>	Supports Combustion	<b>Auto-Ignition Temp., °C:</b>	N.D.
<b>Evaporation Rate:</b>	Faster than Ether	<b>Vapor Pressure:</b>	N.D.
<b>Vapor Density:</b>	Heavier than Air		

(See "Other information" Section for abbreviation legend)

## 10. Stability and Reactivity

**Conditions to Avoid:** Avoid temperatures above 120°F (49°C). Avoid all possible sources of ignition. Avoid excess heat. Keep from freezing.

**Incompatibility:** Incompatible with strong oxidizing agents, strong acids and strong alkalies.

**Hazardous Decomposition:** When heated to decomposition, it emits acrid smoke and irritating fumes. Contains solvents which may form carbon monoxide, carbon dioxide, and formaldehyde.

**Hazardous Polymerization:** Will not occur under normal conditions.

**Stability:** This product is stable under normal storage conditions.

## 11. Toxicological Information

**EFFECTS OF OVEREXPOSURE - EYE CONTACT:** Can cause severe eye irritation. Causes eye and skin irritation which may lead to dermatitis with repeated exposures. Irritating, and may injure eye tissue if not removed promptly.

**EFFECTS OF OVEREXPOSURE - SKIN CONTACT:** May be absorbed through the skin in harmful amounts. Low hazard for usual industrial handling or commercial handling by trained personnel.

**EFFECTS OF OVEREXPOSURE - INHALATION:** High gas, vapor, mist or dust concentrations may be harmful if inhaled. Avoid breathing fumes, spray, vapors, or mist.

**EFFECTS OF OVEREXPOSURE - INGESTION:** Substance may be harmful if swallowed.

**EFFECTS OF OVEREXPOSURE - CHRONIC HAZARDS:** High concentrations may lead to central nervous system effects (drowsiness, dizziness, nausea, headaches, paralysis, and blurred vision) and/or damage. Reports have associated repeated and prolonged occupational overexposure to solvents with permanent brain and nervous system damage. Overexposure to xylene in laboratory animals has been associated with liver abnormalities, kidney, lung, spleen, eye and blood damage as well as reproductive disorders. Effects in humans, due to chronic overexposure, have included liver, cardiac abnormalities and nervous system damage. IARC lists Ethylbenzene as a possible human carcinogen (group 2B). May cause genetic defects. May damage fertility or the unborn child.

**PRIMARY ROUTE(S) OF ENTRY:** Eye Contact, Ingestion, Inhalation, Skin Absorption, Skin Contact

### ACUTE TOXICITY VALUES

The acute effects of this product have not been tested. Data on individual components are tabulated below:

<u>CAS-No.</u>	<u>Chemical Name</u>	<u>Oral LD50</u>	<u>Dermal LD50</u>	<u>Vapor LC50</u>
67-64-1	Acetone	5800 mg/kg Rat	>15700 mg/kg Rabbit	50.1 mg/L Rat
123-86-4	n-Butyl Acetate	10768 mg/kg Rat	>17600 mg/kg Rabbit	> 21 mg/L Rat
106-97-8	n-Butane	N.E.	N.E.	658 mg/L Rat
141-78-6	Ethyl Acetate	5620 mg/kg Rat	>18000 mg/kg Rabbit	N.E.
1330-20-7	Xylenes (o-, m-, p- Isomers)	3500 mg/kg Rat	>4350 mg/kg Rabbit	29.08 mg/L Rat
100-41-4	Ethylbenzene	3500 mg/kg Rat	15400 mg/kg Rabbit	17.4 mg/L Rat
108-88-3	Toluene	2600 mg/kg Rat	12000 mg/kg Rabbit	12.5 mg/L Rat

N.E. - Not Established

## 12. Ecological Information

**ECOLOGICAL INFORMATION:** No ecotoxicity data was found for this product.

### 13. Disposal Information

**DISPOSAL:** Dispose of material in accordance to local, state, and federal regulations and ordinances. Do not incinerate closed containers. This product as supplied is a US EPA defined ignitable hazardous waste. Dispose of unusable product as a hazardous waste (D001) in accordance with local, state, and federal regulation.

### 14. Transport Information

	<u>Domestic (USDOT)</u>	<u>International (IMDG)</u>	<u>Air (IATA)</u>	<u>TDG (Canada)</u>
<b>UN Number:</b>	N.A.	1950	1950	N.A.
<b>Proper Shipping Name:</b>	Paint and Related Spray Products in Ltd Qty	Aerosols	Aerosols, flammable	Aerosols
<b>Hazard Class:</b>	N.A.	2	2.1	N.A.
<b>Packing Group:</b>	N.A.	N.A.	N.A.	N.A.
<b>Limited Quantity:</b>	Yes	Yes	Yes	Yes

### 15. Regulatory Information

#### U.S. Federal Regulations:

##### CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Gas under pressure, Carcinogenicity, Reproductive toxicity, Serious eye damage or eye irritation, Specific target organ toxicity (single or repeated exposure)

##### SARA Section 313

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

<u>Chemical Name</u>	<u>CAS-No.</u>
Xylenes (o-, m-, p- Isomers)	1330-20-7
Ethylbenzene	100-41-4
Toluene	108-88-3

##### Toxic Substances Control Act

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from the United States:

No TSCA 12(b) components exist in this product.

#### U.S. State Regulations:

##### California Proposition 65

#### WARNING:

Cancer and Reproductive Harm - [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov).

**16. Other Information****HMIS RATINGS**

Health: 2\*      Flammability: 4      Physical Hazard: 0      Personal Protection: X

**NFPA RATINGS**

Health: 2      Flammability: 4      Instability: 0

**Volatile Organic Compounds:** 530 g/L

**SDS REVISION DATE:** 10/18/2023

**REASON FOR REVISION:**

Revision Description Changed  
Product Composition Changed  
Substance Chemical Name Changed  
Substance Hazard Threshold % Changed  
Substance and/or Product Properties Changed in  
Section(s):  
01 - Identification  
02 - Hazard Identification  
03 - Composition / Information on Ingredients  
05 - Fire-Fighting Measures  
08 - Exposure Controls / Personal Protection  
09 - Physical & Chemical Properties  
11 - Toxicological Information  
14 - Transport Information  
15 - Regulatory Information  
16 - Other Information  
Substance Hazardous Flag Changed  
Revision Statement(s) Changed

**Legend:** N.A. - Not Applicable, N.D. - Not Determined, N.E. - Not Established

Rust-Oleum Corporation believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. Rust-Oleum Corporation makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.