Date Printed: 5/22/2019 Page 1 / 5

Safety Data Sheet



www.rustoleum.com

Revision Date:

Supercedes Date:

1. Identification

Product Name: KK 24OZ 6PK TRIGR LATEX PAINT

REMOVER

Product Identifier: 336249

Recommended Use: Paint Remover

Supplier: Rust-Oleum Corporation

11 Hawthorn Parkway Vernon Hills, IL 60061

USA

Manufacturer: Rust-Oleum Corporation

11 Hawthorn Parkway Vernon Hills. IL 60061

USA

5/22/2019

1/2/2019

Preparer: Regulatory Department

Emergency Telephone: 24 Hour Hotline: 847-367-7700

2. Hazard Identification

Classification

Symbol(s) of Product





Signal Word Warning

Possible Hazards

19% of the mixture consists of ingredient(s) of unknown acute toxicity.

GHS HAZARD STATEMENTS

Eye Irritation, category 2A H319 Causes serious eye irritation. Flammable Liquid, category 3 H226 Flammable liquid and vapour.

GHS LABEL PRECAUTIONARY STATEMENTS

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P233 Keep container tightly closed.

P264 Wash hands thoroughly after handling.

P280 Wear protective gloves/protective clothing/eye protection/face protection.

P303+P361+P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/

shower.

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present

and easy to do. Continue rinsing.

P337+P313 If eye irritation persists: Get medical advice/attention.

P370+P378 In case of fire: Use alcohol film forming foam, carbon dioxide, dry chemical, dry sand to extinguish.

P403+P235 Store in a well-ventilated place. Keep cool.

P501 Dispose of contents/container in accordance with local, regional and national regulations.

GHS SDS PRECAUTIONARY STATEMENTS

Date Printed: 5/22/2019 Page 2 / 5

P240 Ground/bond container and receiving equipment.

P241 Use explosion-proof electrical/ventilating/lighting/equipment.

P242 Use only non-sparking tools.

P243 Take precautionary measures against static discharge.

3. Composition / Information On Ingredients

HAZARDOUS SUBSTANCES

<u>Chemical Name</u>	CAS-No.	Wt.% Range	GHS Symbols	GHS Statements
Dipropylene Glycol n-Propyl Ether	29911-27-1	10-25	GHS07	H319
Acetone	67-64-1	2.5-10	GHS02-GHS07	H225-319-332-336

4. First-Aid Measures

FIRST AID - EYE CONTACT: Immediately flush eyes with plenty of water for at least 15 minutes holding eyelids open. Get medical attention. Do NOT allow rubbing of eyes or keeping eyes closed.

FIRST AID - SKIN CONTACT: Wash skin with soap and water. Remove contaminated clothing. Get medical attention if irritation develops or persists.

FIRST AID - INHALATION: Remove to fresh air. If not breathing, give artificial respiration. If breathing is difficult, give oxygen. Get immediate medical attention. Do NOT use mouth-to-mouth resuscitation. If you experience difficulty in breathing, leave the area to obtain fresh air. If continued difficulty is experienced, get medical assistance immediately.

FIRST AID - INGESTION: Aspiration hazard: Do not induce vomiting or give anything by mouth because this material can enter the lungs and cause severe lung damage. Get immediate medical attention. If swallowed, get medical attention.

5. Fire-Fighting Measures

EXTINGUISHING MEDIA: Alcohol Film Forming Foam, Carbon Dioxide, Dry Chemical, Dry Sand, Water Fog

UNUSUAL FIRE AND EXPLOSION HAZARDS: Closed containers may explode when exposed to extreme heat due to buildup of steam. Keep containers tightly closed. Isolate from heat, electrical equipment, sparks and open flame. No unusual fire or explosion hazards noted.

SPECIAL FIREFIGHTING PROCEDURES: Water may be used to cool closed containers to prevent pressure buildup and possible autoignition or explosion. Evacuate area and fight fire from a safe distance. Use water spray to keep fire-exposed containers cool. Containers may explode when heated.

Special Fire and Explosion Hazard (Combustible Dust): No Information

6. Accidental Release Measures

STEPS TO BE TAKEN IF MATERIAL IS RELEASED OR SPILLED: Remove all sources of ignition, ventilate area and remove with inert absorbent and non-sparking tools. Dispose of according to local, state (provincial) and federal regulations. Do not incinerate closed containers. Ventilate area, isolate spilled material, and remove with inert absorbent. Dispose of contaminated absorbent, container, and unused contents in accordance with local, state, and federal regulations.

7. Handling and Storage

HANDLING: Wash thoroughly after handling. Wash hands before eating. Remove contaminated clothing and launder before reuse. Use only with adequate ventilation. Follow all SDS and label precautions even after container is emptied because it may retain product residues. Avoid breathing fumes, vapors, or mist. Avoid contact with eyes, skin and clothing.

STORAGE: Store in a dry, well ventilated place. Keep container tightly closed when not in use. Keep containers tightly closed. Isolate from heat, electrical equipment, sparks and open flame. Do not store above 120 ° F. Store large quantities in buildings designed and protected for storage of NFPA Class II combustible liquids. Keep away from heat, sparks, flame and sources of ignition. Avoid excess heat. Product should be stored in tightly sealed containers and protected from heat, moisture, and foreign materials.

Advice on Safe Handling of Combustible Dust: No Information

Date Printed: 5/22/2019 Page 3 / 5

8. Exposure Controls / Personal Protection

Chemical Name	CAS-No.	Weight % Less Than	ACGIH TLV- TWA	ACGIH TLV- STEL	OSHA PEL-TWA	OSHA PEL- CEILING
Dipropylene Glycol n-Propyl Ether	29911-27-1	20.0	N.E.	N.E.	N.E.	N.E.
Acetone	67-64-1	10.0	250 ppm	500 ppm	1000 ppm	N.E.

PERSONAL PROTECTION

ENGINEERING CONTROLS: Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits. Prevent build-up of vapors by opening all doors and windows to achieve crossventilation.

RESPIRATORY PROTECTION: A respiratory protection program that meets OSHA 1910.134 and ANSI Z88.2 requirements must be followed whenever workplace conditions warrant a respirator's use. A NIOSH/MSHA approved air purifying respirator with an organic vapor cartridge or canister may be permissible under certain circumstances where airborne concentrations are expected to exceed exposure limits.

Protection provided by air purifying respirators is limited. Use a positive pressure air supplied respirator if there is any potential for an uncontrolled release, exposure levels are not known, or in any other circumstances where air purifying respirators may not provide adequate protection.

SKIN PROTECTION: Use gloves to prevent prolonged skin contact. Nitrile or Neoprene gloves may afford adequate skin protection.

EYE PROTECTION: Use safety eyewear designed to protect against splash of liquids.

OTHER PROTECTIVE EQUIPMENT: Refer to safety supervisor or industrial hygienist for further guidance regarding types of personal protective equipment and their applications.

HYGIENIC PRACTICES: Wash thoroughly with soap and water before eating, drinking or smoking. Remove contaminated clothing immediately and launder before reuse.

Engineering Measures for Combustible Dust: No Information

9. Physical and Chemical Properties

Appearance: **Physical State:** Liquid Liquid Odor: Solvent Like **Odor Threshold:** N.E.

Specific Gravity: pH: 0.979 Not Determined

Viscosity:

Partition Coefficient, n-octanol/

N.D.

Freeze Point. °C: N.D. Solubility in Water: Soluble Decompostion Temp., °C: N.D. Boiling Range, °C: 56 - 212

N.D. Explosive Limits, vol%: 0.7 - 13.0

Flammability: Flash Point, °C: Supports Combustion 27 Evaporation Rate: Auto-ignition Temp., °C: N.D. Slower than Ether Vapor Pressure: Vapor Density: Heavier than Air N.D.

(See "Other information" Section for abbreviation legend)

10. Stability and Reactivity

CONDITIONS TO AVOID: Avoid temperatures above 120°F (49°C). Avoid all possible sources of ignition.

INCOMPATIBILITY: Incompatible with strong oxidizing agents, strong acids and strong alkalies.

HAZARDOUS DECOMPOSITION: By open flame, carbon monoxide and carbon dioxide. When heated to decomposition, it emits acrid smoke and irritating fumes. Contains solvents which may form carbon monoxide, carbon dioxide, and formaldehyde.

HAZARDOUS POLYMERIZATION: Will not occur under normal conditions.

STABILITY: This product is stable under normal storage conditions.

11. Toxicological Information

EFFECTS OF OVEREXPOSURE - EYE CONTACT: Causes Serious Eye Irritation

EFFECTS OF OVEREXPOSURE - SKIN CONTACT: Causes skin irritation. Allergic reactions are possible.

EFFECTS OF OVEREXPOSURE - INHALATION: Harmful if inhaled. High gas, vapor, mist or dust concentrations may be harmful if inhaled. Avoid breathing fumes, spray, vapors, or mist. High vapor concentrations are irritating to the eyes, nose, throat and lungs. Prolonged or excessive inhalation may cause respiratory tract irritation.

Date Printed: 5/22/2019 Page 4 / 5

EFFECTS OF OVEREXPOSURE - INGESTION: Harmful if swallowed.

EFFECTS OF OVEREXPOSURE - CHRONIC HAZARDS: High concentrations may lead to central nervous system effects (drowsiness, dizziness, nausea, headaches, paralysis, and blurred vision) and/or damage. Reports have associated repeated and prolonged occupational overexposure to solvents with permanent brain and nervous system damage.

PRIMARY ROUTE(S) OF ENTRY: Eye Contact, Ingestion, Inhalation, Skin Absorption, Skin Contact

ACUTE TOXICITY VALUES

The acute effects of this product have not been tested. Data on individual components are tabulated below:

CAS-No.	Chemical Name	Oral LD50	Dermal LD50	Vapor LC50
29911-27-1	Dipropylene Glycol n-Propyl Ether	2032 mg/kg (rat)	>2000 mg/kg (rat)	N.E.
67-64-1	Acetone	5800 mg/kg Rat	>15700 mg/kg Rabbit	50.1 mg/L Rat

N.E. - Not Established

12. Ecological Information

ECOLOGICAL INFORMATION: Product is a mixture of listed components.

13. Disposal Information

DISPOSAL INFORMATION: Do not incinerate closed containers. Dispose of material in accordance to local, state, and federal regulations and ordinances. Do not allow to enter waterways, wastewater, soil, storm drains or sewer systems.

14. Transport Information

	Domestic (USDOT)	International (IMDG)	<u>Air (IATA)</u>	TDG (Canada)	
UN Number:	N.A.	1263	1263	N.A.	
Proper Shipping Name:	Paint and related products in Limited Quantities	Paint Related Material	Paint Related Material	Paint and related products in Limited Quantities	
Hazard Class:	N.A.	3	3	N.A.	
Packing Group:	N.A.	III	III	N.A.	
Limited Quantity:	Yes	Yes	Yes	Yes	

15. Regulatory Information

U.S. Federal Regulations:

CERCLA - SARA Hazard Category

This product has been reviewed according to the EPA 'Hazard Categories' promulgated under Sections 311 and 312 of the Superfund Amendment and Reauthorization Act of 1986 (SARA Title III) and is considered, under applicable definitions, to meet the following categories:

Flammable (gases, aerosols, liquids, or solids), Serious eye damage or eye irritation

Sara Section 313:

This product contains the following substances subject to the reporting requirements of Section 313 of Title III of the Superfund Amendment and Reauthorization Act of 1986 and 40 CFR part 372:

No Sara 313 components exist in this product.

Toxic Substances Control Act:

This product contains the following chemical substances subject to the reporting requirements of TSCA 12(b) if exported from the United States:

No TSCA 12(b) components exist in this product.

U.S. State Regulations:

Date Printed: 5/22/2019 Page 5 / 5

California Proposition 65:

WARNING: No Prop. 65 warning is required.

16. Other Information

HMIS RATINGS

Health: 2* Flammability: 3 Physical Hazard: 0 Personal Protection: X

NFPA RATINGS

Health: 2 Flammability: 3 Instability 0

Volatile Organic Compounds 34.00% SDS REVISION DATE: 5/22/2019

REASON FOR REVISION: Substance and/or Product Properties Changed in Section(s):

11 - Toxicological Information

Legend: N.A. - Not Applicable, N.E. - Not Established, N.D. - Not Determined

The manufacturer believes, to the best of its knowledge, information and belief, the information contained herein to be accurate and reliable as of the date of this safety data sheet. However, because the conditions of handling, use, and storage of these materials are beyond our control, we assume no responsibility or liability for personal injury or property damage incurred by the use of these materials. The manufacturer makes no warranty, expressed or implied, regarding the accuracy or reliability of the data or results obtained from their use. All materials may present unknown hazards and should be used with caution. The information and recommendations in this material safety data sheet are offered for the users' consideration and examination. It is the responsibility of the user to determine the final suitability of this information and to comply with all applicable international, federal, state, and local laws and regulations.