PAGE #:1 OF 6	PRODUCT MATERIAL SAFETY DATA SHEET RESEARCH PRODUCTS INTERNATIONAL	ISSUE DATE: 12/15/14	REV.:2 REV Date : 02/05/19
DOCUMENT #: F/RPI/QC 7.7.3-02-00	PRODUCT NAME: IMIDAZOLE		RPI ITEM NO: 152000

SECTION 1 - CHEMICAL IDENTIFICATION

PRODUCT NAME: IMIDAZOLE [Glyoxaline] [1, 3-Diaza-2-, 4-Cyclopentadiene]

RPI CATALOG #: I52000

SUPPLIER'S NAME: Research Products International Corp.

SUPPLIERS ADDRESS: 410 N Business Center Drive Mount Prospect, Il 60056

EMERGENCY CONTACT: 1-800-424-9300 OTHER INFORMATION: 847-635-7330

SECTION 2 - HAZARDS IDENTIFICATION

2.1 Classification of the substance or mixture

GHS Classification in accordance with 29 CFR 1910 (OSHA HCS)

H302	Acute Toxicity, Oral	Category 4
H314	Skin Corrosion/Irritation	Category 1
H318	Serious Eye Damage	Category 1
H360	Reproductive Toxicity	Category 1

2.2 GHS Label elements, including Hazard and Precautionary Statement(s)

Pictogram







Signal word: Danger
Hazard statement(s)

H302	Harmful if swallowed
H314	Causes Severe Skin Burns And Eye Damage.
H318	Causes Serious Eye Damage
H360	May Damage Fertility Or The Unborn Child

Prevention, Response, Storage and Disposal Precautionary Statement(s)

P201	Obtain special instructions before use
P202	Do not handle until all safety precautions have been read and understood
P260	Do not breathe dust or mist.
P264	Wash skin thoroughly after handling
P280	Wear protective gloves/ protective clothing/ eye protection/ face protection.
P301 + P312	IF SWALLOWED: Call a poison center or doctor/physician if you feel unwell.

PAGE #:2 OF 6	PRODUCT MATERIAL SAFETY DATA SHEET RESEARCH PRODUCTS INTERNATIONAL	ISSUE DATE: 12/15/14	REV.:2 REV Date : 02/05/19
DOCUMENT #: F/RPI/QC 7.7.3-02-00	PRODUCT NAME: IMIDAZOLE		RPI ITEM NO: 152000

P301 + P330 + P331	IF SWALLOWED: rinse mouth. Do NOT induce vomiting.
P303 + P361 + P353	IF ON SKIN (or hair): Remove/ Take off immediately all contaminated clothing. Rinse skin with water/ shower.
P304 + P340	IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.
P305 + P351 + P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P310	Immediately call a POISON CENTER or doctor/ physician.
P321	Specific treatment (see supplemental first aid instructions on this label).
P363	Wash contaminated clothing before reuse.
P405	Store locked up.
P501	Dispose of contents/ container to an approved waste disposal plant.

SECTION 3 - COMPOSITION/INFORMATION ON INGREDIENTS

 $\begin{array}{lll} \text{CAS Number:} & 288\text{-}32\text{-}4 \\ \text{EINECS Number:} & 206\text{-}019\text{-}2 \\ \text{Molecular Weight:} & 68.08 \text{ g/mol} \\ \text{Formula:} & C_3H_4N_2 \\ \end{array}$

SECTION 4 - FIRST-AID MEASURES

4.1 Description of first aid measures

General advice: Consult a doctor and show this safety data sheet.

- If inhaled: Remove to fresh air and monitor breathing. If breathing becomes difficult, give oxygen. If breathing stops, give artificial respiration. Consult a doctor.
- ii. **In case of skin contact:** Immediately wash skin with copious amounts of soap and water for at least 15 minutes. Remove contaminated clothing and shoes and wash before reuse. Consult a doctor.
- iii. In case of eye contact: Flush with copious amounts of water for at least 15 minutes. Consult a doctor.
- iv. **If swallowed:** Rinse mouth with water. Do not induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Consult a doctor.
- **4.2 Most important symptoms and effects, both acute and delayed:** To the best of our knowledge, the chemical, physical and toxicological properties have not been thoroughly investigated.
- **4.3 Indication of immediate medical attention and special treatment needed:** Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

SECTION 5 - FIRE FIGHTING MEASURES

5.1 Extinguishing media

Suitable extinguishing media: Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide

5.2 Special hazards arising from the substance or mixture: Carbon oxides, nitrogen oxides (NOx), Sulfur oxides, Hydrogen chloride gas, Hydrogen fluoride

PAGE #:3 OF 6	PRODUCT MATERIAL SAFETY DATA SHEET RESEARCH PRODUCTS INTERNATIONAL	ISSUE DATE: 12/15/14	REV.:2 REV Date : 02/05/19
DOCUMENT #: F/RPI/QC 7.7.3-02-00	PRODUCT NAME: IMIDAZOLE		RPI ITEM NO: 152000

- **5.3 Precautions for fire-fighters:** Wear suitable protective clothing to prevent contact with skin and eyes and self-contained breathing apparatus.
- **5.4 Further information:** no data available

SECTION 6 - ACCIDENTAL RELEASE MEASURES

- **6.1 Personal precautions, protective equipment and emergency procedures:** Do not take action without suitable protective clothing see section 8 of SDS. Evacuate personnel to safe areas. Ensure adequate ventilation. Avoid breathing vapors, mist, dust or gas.
- **6.2 Environmental precautions:** Do not let product enter drains.
- **6.3 Methods and materials for containment and cleaning up:** Cover spillage with suitable absorbent material. Using non-spark tools, sweep up material and place in an appropriate container. Decontaminate spill site with 10% caustic solution and ventilate area until after disposal is complete. Hold all material for appropriate disposal as described under section 13 of SDS.
- **6.4 Reference to other sections:** For required PPE see section 8. For disposal see section 13.

SECTION 7 - HANDLING AND STORAGE

7.1 Precautions for safe handling:

Use in a chemical fume hood, with air supplied by an independent system. Avoid inhalation, contact with eyes, skin and clothing. Avoid the formation of dust and aerosols. Use in a well-ventilated area. Keep away from sources of ignition. Avoid prolonged or repeated exposure.

- **7.2 Conditions for safe storage, including any incompatibilities:** Store in cool, well-ventilated area. Keep away from direct sunlight. Keep container tightly sealed until ready for use. Recommended storage temperature: Moisture sensitive
- 7.3 Specific end use(s): Use in a laboratory fume hood where possible. Refer to employer's COSHH risk assessment.

SECTION 8 - EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 Control parameters

Components with workplace control parameters: Contains no substances with occupational exposure limit values.

8.2 Exposure Controls

i. **Appropriate engineering controls:** Use in a fume hood where applicable. Ensure all engineering measures described under section 7 of SDS are in place. Ensure laboratory is equipped with a safety shower and eye wash station.

8.3 Personal protective equipment

- i. **Eye/face protection:** Face shield and safety glasses Use equipment for eye protection tested and approved under appropriate government standards such as NIOSH (US) or EN 166(EU).
- ii. **Skin protection:** Wear appropriate protective eyeglasses or chemical safety goggles as described by OSHA's eye and face protection regulations in 29 CFR 1910.133 or European Standard EN166
- iii. **Body Protection:** Wear appropriate protective clothing. Complete suit protecting against chemicals, The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.

PAGE #:4 OF 6	PRODUCT MATERIAL SAFETY DATA SHEET RESEARCH PRODUCTS INTERNATIONAL	ISSUE DATE: 12/15/14	REV.:2 REV Date : 02/05/19
DOCUMENT #: F/RPI/QC 7.7.3-02-00	PRODUCT NAME: IMIDAZOLE		RPI ITEM NO: 152000

- iv. **Respiratory Protection:** Follow the OSHA respirator regulations found in 29 CFR 1910.134 or European Standard EN 149. Use a NIOSH/MSHA or European Standard EN149 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.
- v. Control of environmental exposure: Do not let product enter drains

SECTION 9 - PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Appearance	White Powder	Vapor Pressure	No Data Available
Odor	No Data Available	Vapor Density	No Data Available
Odor Threshold	No Data Available	Relative Density	1.030 g/cm ³
pH	No Data Available	Water Solubility	6.33 g/l at 20 °C
Melting / Freezing Point	88-91° C	Partition Coefficient	No Data Available
Initial Boiling Point Range	256° C (493 °F)	Auto-Ignition Temperature	No Data Available
Flash Point	145° C (293 °F)	Decomposition Temperature	No Data Available
Evaporation Rate	No Data Available	Viscosity	No Data Available
Flammability (Solid, Gas)	No Data Available	Explosive Properties	No Data Available
Upper / Lower Flammability Or Explosive Limits	No Data Available	Oxidizing Properties	No Data Available

SECTION 10 - STABILITY AND REACTIVITY

Stability: Stable under recommended transport or storage conditions. **Conditions to Avoid:** Heat, moisture air or water, incompatibles

Incompatible Materials: Strong oxidizing agents

SECTION 11 - TOXICOLOGICAL INFORMATION

Acute Toxicity

LD50 Oral	LD50 Dermal	LD50 Inhalation
25,800 mg/kg (Rat)	Not Listed	Not Listed

SECTION 12 - ECOLOGICAL INFORMATION

Ecotoxicity: Do not empty into drains

Component	Freshwater Algae	Freshwater Fish	Microtox	Water Flea
1-Imidazole	EC50 =30 mg/L- 72 h EC50 =82 mg/L- 96 h	LC50=280 mg/L- 48 h	EC50 Pseudomonas putida = 1200 mg/L -17 h EC50 Photobacteriumphosphoreum=	EC50 =341.5 mg/L -48 h
			231 mg/- 30 min	

Persistence and degradability/ Bioaccumlative potential: Readily biodegradable

DOCUMENT #: F/RPI/QC 7.7.3-02-00	RESEARCH PRODUCTS INTERNATIONAL PRODUCT NAME: IMIDAZOLE	12/13/14	RPI ITEM NO: 152000
PAGE #:5 OF 6	PRODUCT MATERIAL SAFETY DATA SHEET	ISSUE DATE: 12/15/14	REV.:2 REV Date : 02/05/19

Results of PBT and vPvB assessment: No data available

Other adverse effects: No data available

Chronic Toxicity: There are no known carcinogenic chemicals in this product

Mobility in Soil

Component	log Pow
1-Imidazole	-0.02

SECTION 13 - DISPOSAL CONSIDERATIONS

Whatever cannot be saved for recovery or recycling should be managed in an appropriate and approved waste disposal facility. Processing, use or contamination of this product may change the waste management options. State and local disposal regulations may differ from federal disposal regulations. Dispose of container and unused contents in accordance with federal, state and local requirements.

SECTION 14 - TRANSPORT INFORMATION

	UN#	Proper Shipping Name	Hazard Class	Packaging Group
DOT	3263	CORROSIVE SOLID, BASIC, ORGANIC, N.O.S	8	II
TDG	3263	CORROSIVE SOLID, BASIC, ORGANIC, N.O.S	8	II
IATA	3263	CORROSIVE SOLID, BASIC, ORGANIC, N.O.S	8	II
IMDG/IMO	3263	CORROSIVE SOLID, BASIC, ORGANIC, N.O.S	8	II

SECTION 15 - REGULATORY INFORMATION

INTERNATIONAL INVENTORIES

TSCA	DSL	NDSL	ELINCS	NLP	PICCS	ENCS	AICS	CHINA	KECL
Listed	Listed	-	-		Listed	Listed	Listed	Listed	Listed

USA FEDERAL REGULATION

SARA 311/312 HAZARDOUS CATEGORIZATION

Acute Health	Chronic Health	Fire Hazard	Sudden Release Of	Reactive
Hazard	Hazard		Pressure Hazard	Hazard
Yes	Yes	No	No	No

PAGE #:6 OF 6	PRODUCT MATERIAL SAFETY DATA SHEET RESEARCH PRODUCTS INTERNATIONAL	ISSUE DATE: 12/15/14	REV.:2 REV Date : 02/05/19
DOCUMENT #: F/RPI/QC 7.7.3-02-00 PRODUCT NAME: IMIDAZOLE			RPI ITEM NO: 152000

TSCA 12(b)/ OSHA/ CERCLA/ SARA 313: Not Applicable

Clean Water Act/ Clean Air Act: Not Applicable

California Proposition 65: This product does not contain any Proposition 65 chemicals.

STATE RIGHT TO KNOW

Massachusetts	New Jersey	Pennsylvania	Illinois	Rhode Island
-	Listed	Listed	-	-

HMIS Rating

Health hazard	Chronic Health Hazard	Flammability	Physical Hazard
3	*		0

NFPA Rating

Health Hazard	Fire Hazard	Reactivity Hazard
3		0

US DEPARTMENT OF TRANSPORTATION

REPORTABLE QUANTITY (RQ)	DOT MARINE POLLUTANT	DOT SEVER MARINE POLLUTANT
No	No	No

U.S. DEPARTMENT OF HOMELAND SECURITY: This product does not contain any DHS chemicals.

Canada: This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations (CPR) and the SDS contains all the information required by the CPR.

This SDS complies with the requirements of Regulation (EC).

SECTION 16 - OTHER INFORMATION

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. Research Products International Corp. shall not be held liable for any damage resulting from handling or from contact with the above product. See reverse side of invoice or packing slip for additional terms and conditions of sale. This product is sold for laboratory research and development purposes use only.