

PAGE #:1 OF 5	PRODUCT SAFETY DATA SHEET RESEARCH PRODUCTS INTERNATIONAL	ISSUE DATE: 12/15/14	REV.:1 REV Date :01/16/17
DOCUMENT #: F/RPI/QC 7.7.3-02	PRODUCT NAME: Trypto Soy Agar	RPI ITEM NO: T48800	

SECTION 1 - CHEMICAL IDENTIFICATION

PRODUCT NAME: Trypto Soy Agar
 RPI CATALOG #: T48800
 SUPPLIER'S NAME: Research Products International Corp.
 SUPPLIERS ADDRESS: 410 N Business Center Drive Mount Prospect, IL 60056
 EMERGENCY CONTACT: 1-800-424-9300
 OTHER INFORMATION: 847-635-7330

SECTION 2 - HAZARDS IDENTIFICATION

2.1 Classification of the substance or mixture

GHS Classification in accordance with 29 CFR 1910 (OSHA HCS)

Not hazardous

Signal word: None

Hazard statement(s): Not hazardous

Precautionary statements:

P101	If medical advice is needed, have product container or label at hand
P102	Keep out of reach of children.
P501	Dispose of contents/ container to an approved waste disposal plant.

SECTION 3- COMPOSITION/INFORMATION ON INGREDIENTS

Component	CAS Number	Weight g/l
Peptone, Casein	91079-40-2	15.0
Papaic Digest of Soybean Meal	91079-46-8	5.0
Sodium Chloride	7647-14-5	5.0
Agar	9002-18-0	15.0

SECTION 4 - FIRST-AID MEASURES

4.1 Description of first aid measures

General advice: Consult a doctor and show this safety data sheet.

- If inhaled:** Remove to fresh air and monitor breathing. If breathing becomes difficult, give oxygen. If breathing stops, give artificial respiration. Consult a doctor.
- In case of skin contact:** Immediately wash skin with copious amounts of soap and water for at least 15 minutes. Remove contaminated clothing and shoes and wash before reuse. Consult a doctor.
- In case of eye contact:** Flush with copious amounts of water for at least 15 minutes. Consult a doctor.
- If swallowed:** Rinse mouth with water. Do not induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Consult a doctor.

PAGE #:2 OF 5	PRODUCT SAFETY DATA SHEET RESEARCH PRODUCTS INTERNATIONAL	ISSUE DATE: 12/15/14	REV.:1 REV Date :01/16/17
DOCUMENT #: F/RPI/QC 7.7.3-02	PRODUCT NAME: Trypto Soy Agar	RPI ITEM NO: T48800	

4.2 Most important symptoms and effects, both acute and delayed: To the best of our knowledge, the chemical, physical and toxicological properties have not been thoroughly investigated.

4.3 Indication of immediate medical attention and special treatment needed: Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

SECTION 5 - FIRE FIGHTING MEASURES

5.1 Extinguishing media

Suitable extinguishing media: Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide

5.2 Special hazards arising from the substance or mixture: No data available.

5.3 Precautions for fire-fighters: Wear suitable protective clothing to prevent contact with skin and eyes and self-contained breathing apparatus.

5.4 Further information: No data available

SECTION 6 - ACCIDENTAL RELEASE MEASURES

6.1 Personal precautions, protective equipment and emergency procedures: Do not take action without suitable protective clothing - see section 8 of SDS. Evacuate personnel to safe areas. Ensure adequate ventilation. Avoid breathing vapors, mist, dust or gas.

6.2 Environmental precautions: Do not let product enter drains.

6.3 Methods and materials for containment and cleaning up: Cover spillage with suitable absorbent material. Using non-spark tools, sweep up material and place in an appropriate container. Decontaminate spill site with 10% caustic solution and ventilate area until after disposal is complete. Hold all material for appropriate disposal as described under section 13 of SDS.

6.4 Reference to other sections: For required PPE see section 8. For disposal see section 13.

SECTION 7 - HANDLING AND STORAGE

7.1 Precautions for safe handling: Use in a chemical fume hood, with air supplied by an independent system. Avoid inhalation, contact with eyes, skin and clothing. Avoid the formation of dust and aerosols. Use in a well-ventilated area. Keep away from sources of ignition. Avoid prolonged or repeated exposure.

7.2 Conditions for safe storage, including any incompatibilities: Store in cool, well-ventilated area. Keep away from direct sunlight. Keep container tightly sealed until ready for use. Keep in a dry place. Store the sealed bottle containing the dehydrated medium at 2 - 30 °C. Once opened and recapped, place the container in a low humidity environment the same storage temperature. Protect it from moisture and light. The dehydrated medium should be discarded if it is not free flowing or if the color has changed from the original light beige color.

7.3 Specific end use(s): Use in a laboratory fume hood where possible. Refer to employer's COSHH risk assessment.

SECTION 8 - EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 Control parameters

Components with workplace control parameters: Contains no substances with occupational exposure limit values.

8.2 Exposure Controls

- i. **Appropriate engineering controls:** Use in a fume hood where applicable. Ensure all engineering measures described under section 7 of SDS are in place. Ensure laboratory is equipped with a safety shower and eye wash station.

PAGE #:3 OF 5	PRODUCT SAFETY DATA SHEET RESEARCH PRODUCTS INTERNATIONAL	ISSUE DATE: 12/15/14	REV.:1 REV Date :01/16/17
DOCUMENT #: F/RPI/QC 7.7.3-02	PRODUCT NAME: Trypto Soy Agar	RPI ITEM NO: T48800	

8.3 Personal protective equipment

- Eye/face protection:** Face shield and safety glasses Use equipment for eye protection tested and approved under appropriate government standards such as NIOSH (US) or EN 166(EU).
- Skin protection:** Wear appropriate protective eyeglasses or chemical safety goggles as described by OSHA's eye and face protection regulations in 29 CFR 1910.133 or European Standard EN166
- Body Protection:** Wear appropriate protective clothing. Complete suit protecting against chemicals, The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.
- Respiratory Protection:** Follow the OSHA respirator regulations found in 29 CFR 1910.134 or European Standard EN 149. Use a NIOSH/MSHA or European Standard EN149 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.
- Control of environmental exposure:** Do not let product enter drains

SECTION 9 - PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Appearance	Solid	Vapor Pressure	No Data Available
Odor	No Data Available	Vapor Density	No Data Available
Odor Threshold	No Data Available	Relative Density	No Data Available
pH @25 °C	7.1 - 7.5	Water Solubility	No Data Available
Melting / Freezing Point	No Data Available	Partition Coefficient	No Data Available
Initial Boiling Point Range	No Data Available	Auto-Ignition Temperature	No Data Available
Flash Point	No Data Available	Decomposition Temperature	No Data Available
Evaporation Rate	No Data Available	Viscosity	No Data Available
Flammability (Solid, Gas)	No Data Available	Explosive Properties	No Data Available
Upper / Lower Flammability Or Explosive Limits	No Data Available	Oxidizing Properties	No Data Available

SECTION 10 - STABILITY AND REACTIVITY

Stability: Stable under recommended storage conditions.

Hazardous Decomposition Products: Carbon monoxide (CO), Carbon dioxide (CO₂).

Incompatibilities: Strong Oxidizing Agent.

SECTION 11 - TOXICOLOGICAL INFORMATION

Acute Toxicity

Component	LD50 Oral	LC50 inhalation
Sodium chloride	3 g/kg (Rat)	42 g/m ³ (Rat) 1 h
Agar	11 g/kg (Rat)	Not Listed

PAGE #:4 OF 5	PRODUCT SAFETY DATA SHEET RESEARCH PRODUCTS INTERNATIONAL	ISSUE DATE: 12/15/14	REV.:1 REV Date :01/16/17
DOCUMENT #: F/RPI/QC 7.7.3-02	PRODUCT NAME: Trypto Soy Agar		RPI ITEM NO: T48800

SECTION 12 - ECOLOGICAL INFORMATION

Eco Toxicity: This product contains the following substance(s) which are hazardous for the environment.

Component	Freshwater Fish	Water Flea
Sodium Chloride	Pimephals prome: LC50:7650 mg-L/96h	EC50: 1000 mg-L/48h

Persistence and degradability/ Bioaccumulative potential/ Mobility in soil: No data available

Results of PBT and vPvB assessment: No data available

Other adverse effects: No data available

Chronic Toxicity: There are no known carcinogenic chemicals in this product

SECTION 13 - DISPOSAL CONSIDERATIONS

Whatever cannot be saved for recovery or recycling should be managed in an appropriate and approved waste disposal facility. Processing, use or contamination of this product may change the waste management options. State and local disposal regulations may differ from federal disposal regulations. Dispose of container and unused contents in accordance with federal, state and local requirements.

SECTION 14 - TRANSPORT INFORMATION

DOT	TDG	IATA	IMDG/IMO
Not regulated	Not regulated	Not regulated	Not regulated

SECTION 15 - REGULATORY INFORMATION

INTERNATIONAL INVENTORIES

INGREDIENT: Peptone, Casein					CAS #:91079-40-2			EINECS: 293-428-4	
TSCA	DSL	NDSL	ELINCS	NLP	PICCS	ENCS	AICS	CHINA	KECL
-	-	-	-	-	Listed	-	Listed	Listed	Listed

INGREDIENT: Sodium Chloride					CAS #:7647-14-5			EINECS: 231-598-3	
TSCA	DSL	NDSL	ELINCS	NLP	PICCS	ENCS	AICS	CHINA	KECL
Listed	Listed	-	-	-	Listed	Listed	Listed	Listed	Listed

INGREDIENT: Agar					CAS #:9002-18-0			EINECS: 232-658-1	
TSCA	DSL	NDSL	ELINCS	NLP	PICCS	ENCS	AICS	CHINA	KECL
Listed	-	-	-	-	Listed	-	Listed	Listed	Listed

PAGE #:5 OF 5	PRODUCT SAFETY DATA SHEET RESEARCH PRODUCTS INTERNATIONAL	ISSUE DATE: 12/15/14	REV.:1 REV Date :01/16/17
DOCUMENT #: F/RPI/QC 7.7.3-02	PRODUCT NAME: Trypto Soy Agar		RPI ITEM NO: T48800

USA FEDERAL REGULATION

TSCA 12(b) : Not Applicable

OSHA: Not Applicable

CERCLA: Not Applicable

Clean Water Act: Not Applicable

Clean Air Act: Not Applicable

SARA 311/312 HAZARDOUS CATEGORIZATION: Not Applicable

SARA 313: Not Applicable

California Proposition 65: This product does not contain any Proposition 65 chemicals.

HMIS Rating

Health hazard	Chronic Health Hazard	Flammability	Physical Hazard
0		0	0

NFPA Rating

Health hazard	Fire Hazard	Reactivity Hazard
0	0	0

STATE RIGHT TO KNOW

Massachusetts	New Jersey	Pennsylvania	Illinois	Rhode Island
-	Listed	Listed	-	-

US DEPARTMENT OF TRANSPORTATION

REPORTABLE QUANTITY (RQ)	DOT MARINE POLLUTANT	DOT SEVER MARINE POLLUTANT
No	No	No

U.S. DEPARTMENT OF HOMELAND SECURITY: This product does not contain any DHS chemicals.

Canada: This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations (CPR) and the SDS contains all the information required by the CPR.

This SDS complies with the requirements of Regulation (EC).

SECTION 16 - OTHER INFORMATION

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. Research Products International Corp. shall not be held liable for any damage resulting from handling or from contact with the above product. See reverse side of invoice or packing slip for additional terms and conditions of sale. This product is sold for laboratory research and development purposes use only.