

PAGE #:1 OF 6	PRODUCT SAFETY DATA SHEET RESEARCH PRODUCTS INTERNATIONAL	ISSUE DATE: 12/15/14	REV.:1 REV Date : 11/09/15
DOCUMENT #: F/RPI/QC 7.7.3-02	PRODUCT NAME: Thimerosal		RPI ITEM NO: T21040

SECTION 1 - CHEMICAL IDENTIFICATION

PRODUCT NAME: Thimerosal
 RPI CATALOG #: T21040
 SUPPLIER'S NAME: Research Products International Corp.
 SUPPLIERS ADDRESS: 410 N Business Center Drive Mount Prospect, IL 60056
 EMERGENCY CONTACT: 1-800-424-9300
 OTHER INFORMATION: 847-635-7330

SECTION 2 - HAZARDS IDENTIFICATION


2.1 Classification of the substance or mixture

GHS Classification in accordance with 29 CFR 1910 (OSHA HCS)

H301	Acute toxicity, oral	Category 3
H310	Acute toxicity.	Category 1
H330	Acute toxicity, Inhalation.	Category 2
H373	Specific target organ toxicity, repeated exposure	Category 2

2.2 GHS Label elements, including Hazard and Precautionary Statement(s)

Pictogram



Signal word: Danger

Hazard statement(s)

H373	May cause damage to organs prolonged or repeated exposure
H301	Toxic if swallowed
H310	Fatal in contact with skin.
H330	Fatal if inhaled.

Prevention, Response, Storage and Disposal Precautionary Statement(s)

P260	Do not breathe dust/fume/gas/mist/vapors/spray.
P262	Do not get in eyes, on skin, or on clothing.
P264	Wash skin thoroughly after handling
P270	Do not eat, drink or smoke when using this product.
P271	Use only outdoors or in a well-ventilated area.
P280	Wear protective gloves/ protective clothing/ eye protection/ face protection.

PAGE #:2 OF 6	PRODUCT SAFETY DATA SHEET RESEARCH PRODUCTS INTERNATIONAL	ISSUE DATE: 12/15/14	REV.:1 REV Date : 11/09/15
DOCUMENT #: F/RPI/QC 7.7.3-02	PRODUCT NAME: Thimerosal		RPI ITEM NO: T21040

P284	Wear respiratory protection
P301 + P310	IF SWALLOWED: Call a POISON CENTER or doctor/physician.
P302 + P352	IF ON SKIN: Wash with plenty of soap and water.
P304 + P340	IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.
P310	Immediately call a POISON CENTER or doctor/physician.
P314	Get medical advice/attention if you feel unwell.
P321	Specific treatment (see. on this label).
P330	Rinse mouth.
P361 + P364	Take off contaminated clothing and wash before reuse.
P403 + P233	Store in a well-ventilated place. Keep container tightly closed.
P405	Store locked up.
P501	Dispose of contents/ container to an approved waste disposal plant.

SECTION 3- COMPOSITION/INFORMATION ON INGREDIENTS

CAS Number: 54-64-8
EINECS Number: 200-210-4
Molecular Weight: 404.8 g/mol
Formula: C₉H₉HgNaO₂S

SECTION 4 - FIRST-AID MEASURES

4.1 Description of first aid measures

General advice: Consult a doctor and show this safety data sheet.

- i. **If inhaled:** Remove to fresh air and monitor breathing. If breathing becomes difficult, give oxygen. If breathing stops, give artificial respiration. Consult a doctor.
- ii. **In case of skin contact:** Immediately wash skin with copious amounts of soap and water for at least 15 minutes. Remove contaminated clothing and shoes and wash before reuse. Consult a doctor.
- iii. **In case of eye contact:** Flush with copious amounts of water for at least 15 minutes. Consult a doctor.
- iv. **If swallowed:** Rinse mouth with water. Do not induce vomiting unless directed to do so by medical personnel. Never give anything by mouth to an unconscious person. Consult a doctor.

4.2 Most important symptoms and effects, both acute and delayed: To the best of our knowledge, the chemical, physical and toxicological properties have not been thoroughly investigated.

4.3 Indication of immediate medical attention and special treatment needed: Show this safety data sheet to the doctor in attendance. Immediate medical attention is required.

SECTION 5 - FIRE FIGHTING MEASURES

5.1 Extinguishing media

Suitable extinguishing media: Use water spray, alcohol-resistant foam, dry chemical or carbon dioxide

PAGE #:3 OF 6	PRODUCT SAFETY DATA SHEET RESEARCH PRODUCTS INTERNATIONAL	ISSUE DATE: 12/15/14	REV.:1 REV Date : 11/09/15
DOCUMENT #: F/RPI/QC 7.7.3-02	PRODUCT NAME: Thimerosal		RPI ITEM NO: T21040

5.2 Special hazards arising from the substance or mixture: Carbon oxides, Sulfur oxides, Sodium oxides, Mercury/mercury oxides.

5.3 Precautions for fire-fighters: Wear suitable protective clothing to prevent contact with skin and eyes and self-contained breathing apparatus.

5.4 Further information: No data available

SECTION 6 - ACCIDENTAL RELEASE MEASURES

6.1 Personal precautions, protective equipment and emergency procedures: Do not take action without suitable protective clothing - see section 8 of SDS. Evacuate personnel to safe areas. Ensure adequate ventilation. Avoid breathing vapors, mist, dust or gas.

6.2 Environmental precautions: Do not let product enter drains.

6.3 Methods and materials for containment and cleaning up: Cover spillage with suitable absorbent material. Using non-spark tools, sweep up material and place in an appropriate container. Decontaminate spill site with 10% caustic solution and ventilate area until after disposal is complete. Hold all material for appropriate disposal as described under section 13 of SDS.

6.4 Reference to other sections: For required PPE see section 8. For disposal see section 13.

SECTION 7 - HANDLING AND STORAGE

7.1 Precautions for safe handling: Use in a chemical fume hood, with air supplied by an independent system. Avoid inhalation, contact with eyes, skin and clothing. Avoid the formation of dust and aerosols. Use in a well-ventilated area. Keep away from sources of ignition. Avoid prolonged or repeated exposure.

7.2 Conditions for safe storage, including any incompatibilities: Store in cool, well-ventilated area. Keep away from direct sunlight. Keep container tightly sealed until ready for use. Keep in a dry place. Protect from light.

7.3 Specific end use(s): Use in a laboratory fume hood where possible. Refer to employer's COSHH risk assessment.

SECTION 8 - EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 Control parameters

Components with workplace control parameters: Contains no substances with occupational exposure limit values

8.2 Exposure Controls

- i. **Appropriate engineering controls:** Use in a fume hood where applicable. Ensure all engineering measures described under section 7 of SDS are in place. Ensure laboratory is equipped with a safety shower and eye wash station.

8.3 Personal protective equipment

- i. **Eye/face protection:** Face shield and safety glasses Use equipment for eye protection tested and approved under appropriate government standards such as NIOSH (US) or EN 166(EU).
- ii. **Skin protection:** Wear appropriate protective eyeglasses or chemical safety goggles as described by OSHA's eye and face protection regulations in 29 CFR 1910.133 or European Standard EN166
- iii. **Body Protection:** Wear appropriate protective clothing. Complete suit protecting against chemicals, The type of protective equipment must be selected according to the concentration and amount of the dangerous substance at the specific workplace.

PAGE #:4 OF 6	PRODUCT SAFETY DATA SHEET RESEARCH PRODUCTS INTERNATIONAL	ISSUE DATE: 12/15/14	REV.:1 REV Date : 11/09/15
DOCUMENT #: F/RPI/QC 7.7.3-02	PRODUCT NAME: Thimerosal		RPI ITEM NO: T21040

iv. **Respiratory Protection:** Follow the OSHA respirator regulations found in 29 CFR 1910.134 or European Standard EN 149. Use a NIOSH/MSHA or European Standard EN149 approved respirator if exposure limits are exceeded or if irritation or other symptoms are experienced.

v. **Control of environmental exposure:** Do not let product enter drains

SECTION 9 - PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Appearance	White or Off-White Powder	Vapor Pressure	No Data Available
Odor	No Data Available	Vapor Density	No Data Available
Odor Threshold	No Data Available	Relative Density	No Data Available
pH	No Data Available	Water Solubility	No Data Available
Melting / Freezing Point	232 - 233°C	Partition Coefficient	No Data Available
Initial Boiling Point Range	No Data Available	Auto-Ignition Temperature	No Data Available
Flash Point	No Data Available	Decomposition Temperature	No Data Available
Evaporation Rate	No Data Available	Viscosity	No Data Available
Flammability (Solid, Gas)	No Data Available	Explosive Properties	No Data Available
Upper / Lower Flammability Or Explosive Limits	No Data Available	Oxidizing Properties	No Data Available

SECTION 10 - STABILITY AND REACTIVITY

Stability: Stable under recommended storage conditions.

Hazardous Decomposition Products: Carbon oxides. Sulfur oxides. Mercury/Mercury Oxides.

Conditions to Avoid: Protect from light.

Incompatibilities: Strong Oxidizing Agents. Strong Acids. Strong Bases.

SECTION 11 - TOXICOLOGICAL INFORMATION

Acute Toxicity

LD50 Oral	LD50 Dermal	LD50 Subcutaneous
75 mg/kg (Rat)	Not Listed	98 mg/kg (Rat)

SECTION 12 - ECOLOGICAL INFORMATION

Ecotoxicity

Component	Freshwater Fish
Thimerosal	LC50: 7.5 mg-L/24h (Ictalurus catus)

Persistence and degradability/ Bioaccumulative potential: No data available

Mobility in soil/ Results of PBT and vPvB assessment: No data available

PAGE #:5 OF 6	PRODUCT SAFETY DATA SHEET RESEARCH PRODUCTS INTERNATIONAL	ISSUE DATE: 12/15/14	REV.:1 REV Date : 11/09/15
DOCUMENT #: F/RPI/QC 7.7.3-02	PRODUCT NAME: Thimerosal		RPI ITEM NO: T21040

Other adverse effects: No data available

Chronic Toxicity: There are no known carcinogenic chemicals in this product

SECTION 13 - DISPOSAL CONSIDERATIONS

Whatever cannot be saved for recovery or recycling should be managed in an appropriate and approved waste disposal facility. Processing, use or contamination of this product may change the waste management options. State and local disposal regulations may differ from federal disposal regulations. Dispose of container and unused contents in accordance with federal, state and local requirements.

Component	CAS Number	California Hazardous Waste Status
Thimerosal	54-64-8	Toxic

SECTION 14 - TRANSPORT INFORMATION

	UN#	Proper Shipping Name	Hazard Class	Packaging Group
DOT	2025	MERCURY COMPOUND, SOLID, N.O.S. (THIMEROSAL)	6.1	II
TDG	2025	MERCURY COMPOUND, SOLID, N.O.S. (THIMEROSAL)	6.1	II
IATA	2025	MERCURY COMPOUND, SOLID, N.O.S. (THIMEROSAL)	6.1	II
IMDG/IMO	2025	MERCURY COMPOUND, SOLID, N.O.S. (THIMEROSAL)	6.1	II

SECTION 15 - REGULATORY INFORMATION

INTERNATIONAL INVENTORIES

TSCA	DSL	NDSL	ELINCS	NLP	PICCS	ENCS	AICS	CHINA	KECL
Listed	Listed	-	-	-	Listed	-	Listed	Listed	Listed

USA FEDERAL REGULATION

SARA 311/312 HAZARDOUS CATEGORIZATION

Acute Health Hazard	Chronic Health Hazard	Fire Hazard	Sudden Release Of Pressure Hazard	Reactive Hazard
Yes	Yes	No	No	No

SARA 313

Component	CAS#	Weight %	SARA 313 – Threshold Values %
Thimerosal	54-64-8	95-100	1.0

Clean Water Act

Component	CWA - Toxic Pollutant	CWA – Reportable Quantities
Thimerosal	Listed	-

PAGE #:6 OF 6	PRODUCT SAFETY DATA SHEET RESEARCH PRODUCTS INTERNATIONAL	ISSUE DATE: 12/15/14	REV.:1 REV Date : 11/09/15
DOCUMENT #: F/RPI/QC 7.7.3-02	PRODUCT NAME: Thimerosal		RPI ITEM NO: T21040

Clean Air Act

Component	HAPS Data	Class 1 Ozone Depletors	Class 2 Ozone Depletors
Thimerosal	Listed	-	-

TSCA 12(b)/ OSHA/ CERCLA: Not Applicable

California Proposition 65: This product contains Proposition 65 chemicals.

Component	CAS#	California Prop. 65	Prop 65 NSRL
Thimerosal	54-64-8	Developmental	-

HMIS Rating

Health hazard	Chronic Health Hazard	Flammability	Physical Hazard
4	*	1	0

NFPA Rating

Health Hazard	Fire Hazard	Reactivity Hazard
4	1	0

STATE RIGHT TO KNOW

Massachusetts	New Jersey	Pennsylvania	Illinois	Rhode Island
-	Listed	Listed	-	-

US DEPARTMENT OF TRANSPORTATION

REPORTABLE QUANTITY (RQ)	DOT MARINE POLLUTANT	DOT SEVER MARINE POLLUTANT
No	No	No

U.S. DEPARTMENT OF HOMELAND SECURITY: This product does not contain any DHS chemicals.

Canada: This product has been classified in accordance with the hazard criteria of the Controlled Products Regulations (CPR) and the MSDS contains all the information required by the CPR.

This SDS complies with the requirements of Regulation (EC).

SECTION 16 - OTHER INFORMATION

The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. Research Products International Corp. shall not be held liable for any damage resulting from handling or from contact with the above product. See reverse side of invoice or packing slip for additional terms and conditions of sale. This product is sold for laboratory research and development purposes use only.