


6' DUAL-LEG EXTERNAL SHOCK-ABSORBING LANYARD WITH REBAR HOOKS



Part Number: FAP30199(6)/6-SK

Our **Dingo Core™** series of single and dual-leg lanyards provide an economical solution for Non-SRL applications and are available in multiple hook and shock pack configurations.



SPECIFICATIONS

Design	<ul style="list-style-type: none"> ▶ Double, Y-shaped lanyard ▶ Webbing lanyard incorporated with energy absorber (PN 500) ▶ One side of lanyard is equipped with steel snap hook (PN 146) and other side of lanyard equipped with two steel rebar hooks (PN 167)
Webbing	<ul style="list-style-type: none"> ▶ Material: polyester ▶ Width: 1.18 in. ± 0.04 in. (30mm ± 1mm) ▶ Breaking strength: 6,000 lbs. (Minimum)
Stitching Thread	▶ Material: high-tenacity polyester
Metal Components	<ul style="list-style-type: none"> ▶ Material: alloy steel ▶ Plating: zinc plated ▶ Finish: shot-blasted ▶ Breaking strength: 5,000 lbs.
Weight	▶ 5.67 lbs. ± 0.02 lbs.
Applicable Standards	▶ Meets or exceeds ANSI Z359.13-2013

Safe Keeper Fall Protection is committed to providing high-quality fall protection equipment and systems to create a safer work environment and ultimately save lives in the workforce. We use today's cutting-edge manufacturing processes and experts, applying real-world practical knowledge to engineer effective yet affordable solution-focused products.

