

20" RETRACTABLE NOZZLE VACUUM SEALER

AVS-20

sealersales

Popular Best Seller - Fastest Speed at 6CFM



- 100% Maintenance Free Venturi Vacuum Pump
- Intuitive Design
- Extensive Safety Features
- Rust Treated Powder Coated Steel Chassis
- Clean Room Compatible
- Two Year Warranty

**MADE
IN THE USA**

Our **AVS-20 Vacuum Sealer** is powered by a compressed air (not included), eliminating any concern regarding noise, vibration, magnetic fields, or heat generation. Unlike electromechanically driven vacuum sealers, our design prevents particle generation and oil contamination that often leads to costly maintenance and downtime.

The AVS-20 is defined by retractable nozzle vacuum sealing functionality. At the push of a foot pedal the AVS-20 draws a vacuum around your products; its automated stainless-steel nozzle subsequently retracts before the 1/4" wide-sealing element delivers a leak proof seal a variety of flexible bags including clear, foil (Mylar), mil spec and ESD bags. In a matter of seconds your product is sealed and protected.

The AVS leads the industry in seal speed while delivering clean wrinkle-free seals without any bag distortion. The AVS-20 will not fire an impulse until the upper and lower jaw completely meet, further ensuring operator safety and uncompromised seal integrity.

SPECIFICATIONS

SEALING LENGTH	20"
SEAL WIDTH	1/4"
AIR REQUIREMENTS	6CFM@100PSI
VACUUM FLOW (CFM)	6
MAX VACUUM PRESSURE (inHG)	27
AMPS@120 VOLTS AC	8
DIMENSIONS (LxWxH)	28" x 10" x 7"
WEIGHT (LB)	NET: 34 / GROSS: 40



Optional
Work Tray

ADDITIONAL OPTIONS

- **Gas Flush (Model: AVN-20)**
Flush your package with inert gas to ensure oxygen free package
- **Bi-Active Seal**
- **Stainless Steel Upgrade**
- **CE Certification**
- **Vacuum Filter**
- **Vacuum Regulator**
- **Dual Nozzle**
- **Digital Temperature Controller**
- **Working Tray - 20" x 12"**