

W-SERIES DIRECT HEAT

FOOT OPERATED SEALERS

sealersales



Seals thicker materials like coffee bags

- Easy to operate
- Protector bars around sealing jaws
- Seals a variety of thermoplastic materials
- German manufactured temperature controller
- PTFE coated jaws
- Seal length: 8" (200mm), 12" (300mm), 16" (400mm)
- Seal width: 3/5" (15mm)
- Seal style: meshed ++ or serrated ==
- Option: stand up operation



Introducing our top-of-the-line **W-Series Direct Heat Sealers**, designed to seal a wide range of thermoplastic materials with precision and efficiency. These sealers handle various materials, including coated aluminum foil, Kraft paper, cellophane, polypropylene, poly-nylon, and even thicker options. Please note that while these sealers can tackle a multitude of materials, they are not suitable for sealing polyethylene.

With the capacity to seal materials up to an impressive 18 inches in width and 20 mils in total thickness, our W-Series sealers boast a German-manufactured thermostat, ensuring precise temperature control from 30° to 550° F (0° to 300° C). The simultaneous heating of both jaws ensures excellent heat penetration, especially when sealing thicker materials. Choose from two seal types: units ending in DT come equipped with meshed (++) seal bars, while the DTS models come equipped with serrated (==) seal bars.

We understand the need for adaptability, which is why our direct heat sealers feature an adjustable work table to accommodate various sealing projects. Moreover, the standard 26" pedestal stand offers a sturdy and ergonomic setup, while an optional 36" stand is available for stand up operations. Safety is paramount which is why our W-Series direct heat sealers come equipped with protector bars around the jaws, ensuring maximum protection.

Operating our W-Series sealers is simple! Simply set the desired temperature on the temperature controller based on your material's requirements. Just insert the material between the two sealing bars, press down on the foot pedal to activate sealing. Join countless satisfied customers who have already experienced the efficiency, precision, and ease-of-use of our W-Series Direct Heat Sealers.

MODEL #	SEAL LENGTH	SEAL TYPE	POWER	DIMENSIONS	WEIGHT
W-220DT	8"	MESHED	110V / 250W	13" X 13" X 35"	30
W-220DTS	8"	SERRATED	110V / 250W	13" X 13" X 35"	30
W-300DT	12"	MESHED	110V / 350W	13" X 13" X 35"	41
W-300DTS	12"	SERRATED	110V / 350W	13" X 13" X 35"	41
W-450DT	18"	MESHED	110V / 400W	19" X 13" X 35"	45
W-450DTS	18"	SERRATED	110V / 400W	19" X 13" X 35"	45