



LAB-CLEAN INC.

LAB CLEAN INC

Safety Data Sheet

Truth Antibacterial Unscented Foaming Hand Soap

SECTION 1: Identification

1.1 Product identifier

Product name	Truth Antibacterial Unscented Foaming Hand Soap
Product number	CHW1201
Brand	truth

1.4 Supplier's details

Name	LAB CLEAN INC
Address	3627 Briggeman Dr Los Alamitos CA 90720 USA
Telephone	714 689 0063
email	info@lab-clean.com

1.5 Emergency phone number(s)

CHEMTREC: 1-800-424-9300/ 1-703-527-3887

SECTION 2: Hazard identification

GHS Signal Word: None

GHS Hazard Phrases: May be harmful if swallowed.
Cause eye irritation

GHS Precautionary Phrases: Keep out of reach of children.
Read label before use.

GHS Response Phrases: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing for 15 minutes.
If eye irritation persists, get medical advice/attention.
IF SWALLOWED: Rinse mouth. Do NOT induce vomiting. Get immediate medical advice/attention.

Safety Data Sheet

Truth Antibacterial Unscented Foaming Hand Soap

GHS Storage and Disposal Dispose of contents/container to ...

Phrases:

Inhalation: None.

Skin Contact: Non-irritating to the skin.

Eye Contact: may cause irritation.

Ingestion: May be harmful if swallowed. May cause gastrointestinal irritation.

SECTION 3: Composition/information on ingredients

CAS #	Hazardous Components (Chemical Name)	Concentration
61789-40-0	Cocamidopropyl betaine	< 5.0 %

SECTION 4: First-aid measures

General advice	Treat symptomatically and supportively. Show this safety data sheet to the doctor in attendance.
In case of eye contact	Flush eyes with plenty of water for at least 15 minutes, occasionally lifting the upper and lower eyelids. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists, get medical advice/attention.
If swallowed	Do NOT induce vomiting. Never give anything by mouth to an unconscious person. Rinse mouth with water. If victim is conscious and alert, give 2-4 cupfuls of water. Get medical attention immediately.

SECTION 5: Fire-fighting measures

Flash Pt: NA

Explosive Limits: LEL: No data UEL : No data

Autoignition Pt: NA

5.1 Suitable extinguishing media

Use water fog, dry chemical, carbon dioxide, or alcohol-resistant foam.

5.2 Specific hazards arising from the chemical

High temperatures and fire conditions can result in the formation of carbon monoxide and carbon dioxide.

5.3 Special protective actions for fire-fighters

Safety Data Sheet

Truth Antibacterial Unscented Foaming Hand Soap

As in any fire, wear a self-contained breathing apparatus in pressure-demand, MSHA/NIOSH (approved or equivalent), and full protective gear.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment, and emergency procedures

Use proper personal protective equipment as indicated in Section 8.

6.2 Environmental precautions

Observe all federal, state, and local environmental regulations.

6.3 Methods and materials for containment and cleaning up.

Absorb spill with inert material (e.g., vermiculite, sand, or earth), then place in suitable container.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Avoid contact with eyes.

7.2 Conditions for safe storage, including any incompatibilities.

Do not store in direct sunlight. Protect containers against damage. Keep container tightly closed in a dry and well-ventilated place.

Specific end use(s)

Handle in accordance with good industrial hygiene and safety practice.

SECTION 8: Exposure controls/personal protection

CAS #	Partial Chemical Name	OSHA TWA	ACGIH TWA	Other Limits
61789-40-0	Cocamidopropyl betaine	No data.	No data.	No data.

Respiratory Equipment : No special respiratory protection equipment is required with normal use

Eyes Protection : Safety Glasses

Protective Gloves: No data available

Other Protective Clothing: No data available

Engineering Controls: No data available

Work / Hygienic /Maintenance : Handle in accordance with good industrial hygiene and safety practice.

SECTION 9: Physical and chemical properties

Information on basic physical and chemical properties

Safety Data Sheet

Truth Antibacterial Unscented Foaming Hand Soap

Appearance/form (physical state, color, etc.)	Clear Colorless , Liquid.
Odor	Characteristic
pH	5.5 - 6.5
Melting point/freezing point	N/A
Initial boiling point and boiling range	N/A
Flash point	N/A
Evaporation rate	N/A
Flammability (solid, gas)	No data available.
Explosive Limits	LEL: No data UEL: No data
Vapor pressure	NA
Vapor density (vs. Air or mm Hg)	N/A
Specific Gravity (Water = 1)	1.005-1.015
Relative density	NA
Solubility in water	No data
Saturated Vapor	NA
Partition coefficient: n-octanol/water	No data
Auto-ignition temperature	NA
Decomposition temperature	NA
Viscosity	No data

SECTION 10: Stability and reactivity

10.1 Reactivity

High temperatures and fire conditions can result in the formation of carbon monoxide. and carbon dioxide

10.2 Chemical stability

Unstable [] Stable [X]

10.3 Possibility of hazardous reactions

Will occur [] Will not occur [X]

10.4 Conditions to avoid.

No data Available.

10.5 Incompatible materials

No data available.

10.6 Hazardous decomposition products

Carbon oxides , oxides of nitrogen , oxides of sulfur , oxides of sodium , formed under fire conditions.

SECTION 11: Toxicological information

Information on toxicological effects

Epidemiology: No information found.

Teratogenicity: No information available.

Reproductive Effects: No information available.

Mutagenicity: No information available.

Neurotoxicity: Acute toxicity. No data available.

Safety Data Sheet

Truth Antibacterial Unscented Foaming Hand Soap

Carcinogenicity / Other information: Carcinogenicity

IARC: No component of this product present at levels greater than or equal to 0.1% is identified as probable, possible, or confirmed human carcinogen by IARC.

ACGIH: No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by ACGIH.

NTP: No component of this product present at levels greater than or equal to 0.1% is identified as a known or anticipated carcinogen by NTP.

OSHA: No component of this product present at levels greater than or equal to 0.1% is identified as a carcinogen or potential carcinogen by OSHA.

Carcinogenicity: NTP? No IARC Monographs? No OSHA Regulated? No

CAS #	Hazardous Components (Chemical Name)	NTP	IARC	ACGIH	OSHA
61789-40-0	Cocamidopropyl betaine	n.a.	n.a.	n.a.	n.a.

SECTION 12: Ecological information

Persistence and degradability

Environmental: No information available.

Physical: No information available.

Bio accumulative potential

No data available.

Mobility in soil

No data available.

Results of PBT and vPvB assessment.

No data available.

SECTION 13: Disposal considerations

Waste treatment

Chemical waste generators must determine whether a discarded chemical is classified as a hazardous waste. US EPA guidelines for the classification determination are listed in 40 CFR Parts 261. Additionally, waste generators must consult state and local hazardous waste regulations to ensure complete and accurate classification. Contact a licensed professional waste disposal service to dispose of this material.

SECTION 14: Transport information

DOT (US)

UN Number: None

Class: None

Packing Group: None

Proper Shipping Name: Not Regulated.

Safety Data Sheet

Truth Antibacterial Unscented Foaming Hand Soap

SECTION 15: Regulatory information

EPA SARA (Superfund Amendments and Reauthorization Act of 1986) Lists

CAS #	Hazardous Components (Chemical Name)	S. 302 (EHS)	S. 304 RQ	S. 313 (TRI)
61789-40-0	Cocamidopropyl betaine	No	No	No

This material meets the EPA 'Hazard Categories' defined for SARA Title III Sections 311/312 as indicated:

<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	Explosive	<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	Acute toxicity (any route of exposure)
<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	Flammable (gases, aerosols, liquid, or solid)	<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	Skin Corrosion or Irritation
<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	Oxidizer (liquid, solid or gas)	<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	Serious eye damage or eye irritation
<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	Self-reactive	<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	Respiratory or Skin Sensitization
<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	Pyrophoric (liquid or solid)	<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	Germ cell mutagenicity
<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	Pyrophoric gas	<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	Carcinogenicity
<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	Self-heating	<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	Reproductive toxicity
<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	Organic peroxide	<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	Specific target organ toxicity (single or repeated exposure)
<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	Corrosive to metal	<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	Aspiration Hazard
<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	Gas under pressure (compressed gas)	<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	Simple Asphyxiant
<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	In contact with water emits flammable gas	<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	(Health) Hazard Not Otherwise Classified (HNOC)
<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	Combustible Dust		
<input type="checkbox"/> Yes <input checked="" type="checkbox"/> No	(Physical) Hazard Not Otherwise Classified (HNOC)		

CAS #	Hazardous Components (Chemical Name)
61789-40-0	Cocamidopropyl betaine

Other US EPA or State Lists

CWA NPDES: No; TSCA: Yes - Inventory; CA PROP.65: No; CA TAC, Title 8: No; MA Oil/HazMat: No; MI CMR, Part 5: No; NJ EHS: No; NY Part 597: No; PA HSL: No

SECTION 16: Other information

16.1 Further information/disclaimer

While Lab Clean, Inc believes the statements set forth herein are accurate as of the date hereof, Lab Clean, Inc makes no warranty with respect thereto and expressly disclaims all liability for reliance thereon. Such data is offered solely for your consideration, investigation, and verification.

16.2 Preparation information

WORKED BY: Lab Clean Inc

DATE OF PRINTING: February 19, 2021