



Technical Sheet


Product

Premium Thin Aluminium Oxide Wheels

Type 27 Depressed Centre Premium Thin Aluminium Oxide Wheels Double Reinforced

1. Description of Product

Dimensions(in):	4 1/2" X .045" X 7/8"
Max RPM:	13,580
Abrasive:	STEEL STAINLESS STEEL
Line:	ULTICUT
Part Number:	AU4-10450352



1. Application

- For precise cutting of stainless steel.
- Good price-performance ratio.

2. Operating instructions

- Use on an angle grinder.
- Mount the disc and let it idle for one minute to check that it is not damaged.
- Keep the blade at 90 ° from the work surface.
- Do not press excessively, or hit against the backing material job.
- An adapter is required for the correct mounting of discs with depressed center.

3. Safety information

- Before mounting or dismounting the disc, check that the machine is disconnected.
- Never exceed the maximum peripheral speed marked on the label.
- Always use security guards.
- It is recommended to use full safety equipment (gloves, hearing protection, mask and safety glasses).
- Never try to make curved cuts.
- Never use a disc that has gotten wet.
- Do not use for roughing operations.



- Do not use the disc in machines for which it was not designed.
- Improper use can cause severe injury.
- Use as directed by ANSI B7.1.

4. Handling

- Handle discs with care to prevent bumps or drops. Yes a disc falls, fractures, detaches a section or is suspect that it may have damage, it should not be mounted.

5. Storage

- Store discs on a flat surface and do not hit or hit them. I dropped them.
- The discs must not be exposed to:
 - (a) Water or other solvents.
 - (b) Extreme temperatures or humid conditions.
- For more information, consult the ANSI B7.1 standard.

6. Packaging units

- Box Quantity: 50
- Case Quantity: 500



1021 N. Fuller St, Santa Ana, CA 92701
TEL 949.250.9060 FAX 949.250.8711

CALL TO PLACE ORDER

1.855.817.8390

www.continentalabrasives.com