

# SAFETY DATA SHEET



Breakthrough®

## Section 1. Identification

**GHS product identifier** : Breakthrough®  
**Product code** : BTS-3ml / BTS-15ml / BTS-2oz / BTS-6oz / BTS-16oz / BTS-32oz / BTS-1gl / BTS-5gl / BTS-55gl  
**Other means of identification** : Not available.  
**Product type** : Liquid.

### Relevant identified uses of the substance or mixture and uses advised against

**Identified uses** : Cleaner degreaser.

**Supplier's details** : Breakthrough Clean Technologies  
 1725 NW 97th Avenue, Doral, Florida, 33172  
 888-455-5499  
 305-717-5001  
 info@breakthroughclean.com  
 www.breakthroughclean.com

**Manufacturer** : Inland Technology

**Emergency telephone number (with hours of operation)** : Infotrac US: 1-800-535-5053  
 Infotrac International: 1-352-323-3500  
 (24 hours)

## Section 2. Hazards identification

**OSHA/HCS status** : This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

**Classification of the substance or mixture** : FLAMMABLE LIQUIDS - Category 4  
 ASPIRATION HAZARD - Category 1

### GHS label elements

**Hazard pictograms** :



**Signal word** : Danger

**Hazard statements** : H227 - Combustible liquid.  
 H304 - Harmful or fatal if swallowed and enters airways.

### Precautionary statements

**Prevention** : P280 - Wear protective gloves. Wear eye or face protection.  
 P210 - Keep away from flames and hot surfaces. - No smoking.

**Response** : P301 + P310 + P331 - IF SWALLOWED: Immediately call a POISON CENTER or physician. Do NOT induce vomiting.

**Storage** : P405 - Store locked up.  
 P403 - Store in a well-ventilated place.  
 P235 - Keep cool.

## Section 2. Hazards identification

**Disposal** : P501 - Dispose of contents and container in accordance with all local, regional, national and international regulations.

**Hazards not otherwise classified** : None known.

## Section 3. Composition/information on ingredients

**Substance/mixture** : Substance

**Other means of identification** : Not available.

### CAS number/other identifiers

**CAS number** : 64742-48-9

Ingredient name	%	CAS number
C12-C13 Paraffinic Hydrocarbons, Hydrotreated	Proprietary	64742-48-9

Any concentration shown as a range is to protect confidentiality or is due to batch variation.

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

Occupational exposure limits, if available, are listed in Section 8.

## Section 4. First aid measures

### Description of necessary first aid measures

**Eye contact** : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Continue to rinse for at least 20 minutes. Get medical attention if irritation occurs.

**Inhalation** : Remove victim to fresh air and keep at rest in a position comfortable for breathing. If not breathing, if breathing is irregular or if respiratory arrest occurs, provide artificial respiration or oxygen by trained personnel. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. Get medical attention if adverse health effects persist or are severe. If unconscious, place in recovery position and get medical attention immediately. Maintain an open airway. Loosen tight clothing such as a collar, tie, belt or waistband.

**Skin contact** : Flush contaminated skin with plenty of water. Get medical attention if symptoms occur. Wash clothing before reuse. Clean shoes thoroughly before reuse.

**Ingestion** : Get medical attention immediately. Call a poison center or physician. Wash out mouth with water. Remove dentures if any. Remove victim to fresh air and keep at rest in a position comfortable for breathing. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Stop if the exposed person feels sick as vomiting may be dangerous. Aspiration hazard if swallowed. Can enter lungs and cause damage. Do not induce vomiting. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Never give anything by mouth to an unconscious person. If unconscious, place in recovery position and get medical attention immediately. Maintain an open airway. Loosen tight clothing such as a collar, tie, belt or waistband.

### Most important symptoms/effects, acute and delayed

#### Potential acute health effects

**Eye contact** : No known significant effects or critical hazards.

**Inhalation** : No known significant effects or critical hazards.

**Skin contact** : No known significant effects or critical hazards.

## Section 4. First aid measures

**Ingestion** : Harmful or fatal if swallowed and enters airways.

### Over-exposure signs/symptoms

**Eye contact** : No known significant effects or critical hazards.

**Inhalation** : No known significant effects or critical hazards.

**Skin contact** : No known significant effects or critical hazards.

**Ingestion** : Adverse symptoms may include the following:  
nausea or vomiting

### Indication of immediate medical attention and special treatment needed, if necessary

**Notes to physician** : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.

**Specific treatments** : No specific treatment.

**Protection of first-aiders** : No action shall be taken involving any personal risk or without suitable training. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation.

See toxicological information (Section 11)

## Section 5. Fire-fighting measures

### Extinguishing media

**Suitable extinguishing media** : Use dry chemical, CO<sub>2</sub>, water spray (fog) or foam.

**Unsuitable extinguishing media** : Do not use water jet.

**Specific hazards arising from the chemical** : Combustible liquid. Runoff to sewer may create fire or explosion hazard. In a fire or if heated, a pressure increase will occur and the container may burst, with the risk of a subsequent explosion. The vapor/gas is heavier than air and will spread along the ground. Vapors may accumulate in low or confined areas or travel a considerable distance to a source of ignition and flash back.

**Hazardous thermal decomposition products** : No specific data.

**Special protective actions for fire-fighters** : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training. Move containers from fire area if this can be done without risk. Use water spray to keep fire-exposed containers cool.

**Special protective equipment for fire-fighters** : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.

## Section 6. Accidental release measures

### Personal precautions, protective equipment and emergency procedures

**For non-emergency personnel** : Put on appropriate personal protective equipment.

**For emergency responders** : If specialized clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".

## Section 6. Accidental release measures

**Environmental precautions** : Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

### Methods and materials for containment and cleaning up

**Spill** : Stop leak if without risk. Move containers from spill area. Use spark-proof tools and explosion-proof equipment. Approach release from upwind. Prevent entry into sewers, water courses, basements or confined areas. Wash spillages into an effluent treatment plant or proceed as follows. Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations (see Section 13). Dispose of via a licensed waste disposal contractor. Contaminated absorbent material may pose the same hazard as the spilled product. Note: see Section 1 for emergency contact information and Section 13 for waste disposal.

## Section 7. Handling and storage

### Precautions for safe handling

**Protective measures** : Put on appropriate personal protective equipment (see Section 8). Do not swallow. Avoid contact with eyes, skin and clothing. Avoid breathing vapor or mist. Use only with adequate ventilation. Wear appropriate respirator when ventilation is inadequate. Do not enter storage areas and confined spaces unless adequately ventilated. Keep in the original container or an approved alternative made from a compatible material, kept tightly closed when not in use. Store and use away from heat, sparks, open flame or any other ignition source. Use explosion-proof electrical (ventilating, lighting and material handling) equipment. Use only non-sparking tools. Empty containers retain product residue and can be hazardous. Do not reuse container.

**Advice on general occupational hygiene** : Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. See also Section 8 for additional information on hygiene measures.

**Conditions for safe storage, including any incompatibilities** : Store in accordance with local regulations. Store in a segregated and approved area. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Store locked up. Eliminate all ignition sources. Separate from oxidizing materials. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabeled containers. Use appropriate containment to avoid environmental contamination. See Section 10 for incompatible materials before handling or use.

## Section 8. Exposure controls/personal protection

### Control parameters

#### Occupational exposure limits

Ingredient name	Exposure limits
C12-C13 Paraffinic Hydrocarbons, Hydrotreated	None.

**Appropriate engineering controls** : Use only with adequate ventilation. Use process enclosures, local exhaust ventilation or other engineering controls to keep worker exposure to airborne contaminants below any recommended or statutory limits. The engineering controls also need to keep gas, vapor or dust concentrations below any lower explosive limits. Use explosion-proof ventilation equipment.

## Section 8. Exposure controls/personal protection

- Environmental exposure controls** : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation.
- Individual protection measures**
- Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.
- Eye/face protection** : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: safety glasses with side-shields.
- Skin protection**
- Hand protection** : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary. Considering the parameters specified by the glove manufacturer, check during use that the gloves are still retaining their protective properties. It should be noted that the time to breakthrough for any glove material may be different for different glove manufacturers. In the case of mixtures, consisting of several substances, the protection time of the gloves cannot be accurately estimated.
- Body protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Other skin protection** : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Respiratory protection** : Based on the hazard and potential for exposure, select a respirator that meets the appropriate standard or certification. Respirators must be used according to a respiratory protection program to ensure proper fitting, training, and other important aspects of use.

## Section 9. Physical and chemical properties

### Appearance

- Physical state** : Liquid.
- Color** : Clear.
- Odor** : Odorless.
- Odor threshold** : Not available.
- pH** : Not available.
- Melting point** : Not available.
- Boiling point** : 187.78°C (370°F)
- Flash point** : Closed cup: 65.556°C (150°F) [Pensky-Martens.]
- Evaporation rate** : <0.1 (Butyl acetate = 1)
- Flammability (solid, gas)** : Not available.
- Lower and upper explosive (flammable) limits** : Lower: 0.8%  
Upper: 7%
- Vapor pressure** : 0.013 kPa (0.1 mm Hg) [room temperature]
- Vapor density** : >5 [Air = 1]
- Relative density** : 0.77 g/ml

## Section 9. Physical and chemical properties

<b>Solubility</b>	: Insoluble in water.
<b>Partition coefficient: n-octanol/water</b>	: Not available.
<b>Auto-ignition temperature</b>	: 335°C (635°F)
<b>Decomposition temperature</b>	: Not available.
<b>Viscosity</b>	: Not available.
<b>Flow time (ISO 2431)</b>	: Not available.

## Section 10. Stability and reactivity

<b>Reactivity</b>	: The product is non-reactive under recommended conditions of use and storage.
<b>Chemical stability</b>	: The product is stable.
<b>Possibility of hazardous reactions</b>	: Under normal conditions of storage and use, hazardous reactions will not occur.
<b>Conditions to avoid</b>	: Avoid all possible sources of ignition (spark or flame). Do not pressurize, cut, weld, braze, solder, drill, grind or expose containers to heat or sources of ignition. Do not allow vapor to accumulate in low or confined areas.
<b>Incompatible materials</b>	: Reactive or incompatible with the following materials: oxidizing materials.
<b>Hazardous decomposition products</b>	: Under normal conditions of storage and use, hazardous decomposition products should not be produced.

## Section 11. Toxicological information

### Information on toxicological effects

#### Acute toxicity

Product/ingredient name	Result	Species	Dose	Exposure
C12-C13 Paraffinic Hydrocarbons, Hydrotreated	LD50 Oral	Rat	>6 g/kg	-

#### Irritation/Corrosion

There is no data available.

#### Sensitization

There is no data available.

#### Mutagenicity

There is no data available.

#### Carcinogenicity

There is no data available.

#### Reproductive toxicity

There is no data available.

#### Teratogenicity

There is no data available.

#### Specific target organ toxicity (single exposure)

There is no data available.

#### Specific target organ toxicity (repeated exposure)

## Section 11. Toxicological information

There is no data available.

### Aspiration hazard

Name	Result
C12-C13 Paraffinic Hydrocarbons, Hydrotreated	ASPIRATION HAZARD - Category 1

**Information on the likely routes of exposure** : Dermal contact. Eye contact. Inhalation. Ingestion.

### Potential acute health effects

**Eye contact** : No known significant effects or critical hazards.  
**Inhalation** : No known significant effects or critical hazards.  
**Skin contact** : No known significant effects or critical hazards.  
**Ingestion** : Harmful or fatal if swallowed and enters airways.

### Symptoms related to the physical, chemical and toxicological characteristics

**Eye contact** : No known significant effects or critical hazards.  
**Inhalation** : No known significant effects or critical hazards.  
**Skin contact** : No known significant effects or critical hazards.  
**Ingestion** : Adverse symptoms may include the following:  
 nausea or vomiting

### Delayed and immediate effects and also chronic effects from short and long term exposure

#### Short term exposure

**Potential immediate effects** : No known significant effects or critical hazards.  
**Potential delayed effects** : No known significant effects or critical hazards.

#### Long term exposure

**Potential immediate effects** : No known significant effects or critical hazards.  
**Potential delayed effects** : No known significant effects or critical hazards.

#### Potential chronic health effects

**General** : No known significant effects or critical hazards.  
**Carcinogenicity** : No known significant effects or critical hazards.  
**Mutagenicity** : No known significant effects or critical hazards.  
**Teratogenicity** : No known significant effects or critical hazards.  
**Developmental effects** : No known significant effects or critical hazards.  
**Fertility effects** : No known significant effects or critical hazards.

### Numerical measures of toxicity

#### Acute toxicity estimates

There is no data available.

## Section 12. Ecological information

### Toxicity

There is no data available.

### Persistence and degradability

There is no data available.

### Bioaccumulative potential

Product/ingredient name	LogP <sub>ow</sub>	BCF	Potential
C12-C13 Paraffinic Hydrocarbons, Hydrotreated	-	10 to 2500	high

### Mobility in soil

**Soil/water partition coefficient (K<sub>oc</sub>)** : There is no data available.

**Other adverse effects** : No known significant effects or critical hazards.

## Section 13. Disposal considerations

**Disposal methods** : The generation of waste should be avoided or minimized wherever possible. Disposal of this product, solutions and any by-products should comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Care should be taken when handling empty containers that have not been cleaned or rinsed out. Empty containers or liners may retain some product residues. Vapor from product residues may create a highly flammable or explosive atmosphere inside the container. Do not cut, weld or grind used containers unless they have been cleaned thoroughly internally. Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

## Section 14. Transport information

	DOT Classification	IMDG	IATA
<b>UN number</b>	NA1993	Not regulated.	Not regulated.
<b>UN proper shipping name</b>	COMBUSTIBLE LIQUID, N.O.S. (C12-C13 Paraffinic Hydrocarbons, Hydrotreated)	-	-
<b>Transport hazard class(es)</b>	Combustible liquid.	-	-
<b>Packing group</b>	III	-	-
<b>Environmental hazards</b>	No.	No.	No.

**AERG** : 128

## Section 14. Transport information

### Additional information

**DOT Classification** : Non-bulk packages (less than or equal to 119 gal) of combustible liquids are not regulated as hazardous materials.

**Special precautions for user** : **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

## Section 15. Regulatory information

**U.S. Federal regulations** : **TSCA 8(a) CDR Exempt/Partial exemption:** All components are listed or exempted.  
**United States inventory (TSCA 8b):** All components are listed or exempted.

**Clean Air Act Section 112 (b) Hazardous Air Pollutants (HAPs)** : Not listed

**Clean Air Act Section 602 Class I Substances** : Not listed

**Clean Air Act Section 602 Class II Substances** : Not listed

**DEA List I Chemicals (Precursor Chemicals)** : Not listed

**DEA List II Chemicals (Essential Chemicals)** : Not listed

### SARA 302/304

#### Composition/information on ingredients

No products were found.

**SARA 304 RQ** : Not applicable.

### SARA 311/312

**Classification** : FLAMMABLE LIQUIDS - Category 4  
 ASPIRATION HAZARD - Category 1

#### Composition/information on ingredients

Name	Classification
C12-C13 Paraffinic Hydrocarbons, Hydrotreated	FLAMMABLE LIQUIDS - Category 2 ASPIRATION HAZARD - Category 1

### SARA 313

There is no data available.

### State regulations

**Massachusetts** : None of the components are listed.

**New York** : None of the components are listed.

**New Jersey** : None of the components are listed.

**Pennsylvania** : None of the components are listed.

### California Prop. 65

No products were found.

## Section 16. Other information

### Procedure used to derive the classification

Classification	Justification
FLAMMABLE LIQUIDS - Category 4 ASPIRATION HAZARD - Category 1	On basis of test data Calculation method

### History

**Date of issue mm/dd/yyyy** : 07/21/2021  
**Date of previous issue** : 04/15/2017  
**Version** : 2  
**Prepared by** : KMK Regulatory Services Inc.

### Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.