



Project Name: \_\_\_\_\_

Location: \_\_\_\_\_

Item #: \_\_\_\_\_ Qty: \_\_\_\_\_

Model: \_\_\_\_\_

## UNDERCOUNTER FREEZERS

MODEL: ☐ MXCF27UHC ☐ MXCF48UHC ☐ MXCF60UHC ☐ MXCF72UHC



MXCF27UHC



MXCF48UHC



MXCF60UHC



MXCF72UHC


Maxx Cold stainless steel Undercounter Freezers are designed to provide the user with maximum storage, energy savings and cold, accurate temperatures. Our undercounter models allow for easy accessibility, optimum capacity and flexibility for quick and efficient food preparation.

### FEATURES AND CONSTRUCTION

- Durable, easy to clean stainless steel exterior
- Painted aluminum interior
- Easy to grip recessed door handles
- Adjustable heavy-duty wire shelves (1 per section/door)
- Equipped with four (4) 3" swivel casters
- Solid state digital control system
- LED temperature display
- Automatic defrost system
- Equipped with integrated condensate evaporator therefore no drain line connection is needed
- Urethane insulated walls and doors
- Accommodates full-size sheet pans

### ELECTRIC

115V / 60Hz / 1Ph  
(230V / 50-60Hz / 1Ph is available as an option)  
6' (2m) NEMA 5-15P cord set included



NEMA 5-15P

### NET STORAGE CAPACITY

|                 |                    |
|-----------------|--------------------|
| MXCF27UHC ..... | 6.5 Cu Ft (184 L)  |
| MXCF48UHC ..... | 12 Cu Ft (340 L)   |
| MXCF60UHC ..... | 15.5 Cu Ft (439 L) |
| MXCF72UHC ..... | 18 Cu Ft (510 L)   |

### 3RD PARTY APPROVALS



Intertek

Certified to ANSI NSF 7



Intertek

Certified to ANSI UL 471



Zero Ozone Depletion Potential



DOE 2018 Compliant


### TEMPERATURE

Holding temperature ..... -4°F to 10°F (-20°C to -12°C)

- Efficient forced-air refrigeration system

### MAXX COLD WARRANTY (USA / CANADA)

Contact Maxx Cold for warranty statement at  
TechnicalServices@TheLegacyCompanies.com or 877.368.2797



| MODEL     | EXTERNAL DIMENSIONS                             | INTERNAL DIMENSIONS                            | NET CAPACITY          | HOLDING TEMPERATURE RANGE        | AMP DRAW | SHIPPING WEIGHT     | REFRIGERANT AND CHARGE SIZE | DOORS / SHELVES | ELECTRICAL        |
|-----------|-------------------------------------------------|------------------------------------------------|-----------------------|----------------------------------|----------|---------------------|-----------------------------|-----------------|-------------------|
| MXCF27UHC | 27.5" x 30" x 35.5"<br>(699 x 762 x 911 mm)     | 22.9" x 18.8" x 24.5"<br>(602 x 478 x 622 mm)  | 6.5 Cu Ft<br>(184 L)  | -4°F to 10°F<br>(-20°C to -12°C) | 1.9A     | 224 lbs<br>(102 kg) | R-290a<br>3.35 oz (95 g)    | 1 / 1           | 115V / 60Hz / 1Ph |
| MXCF48UHC | 48.3125" x 30" x 35.5"<br>(1227 x 762 x 911 mm) | 43.5" x 18.8" x 24.5"<br>(1104 x 478 x 622 mm) | 12 Cu Ft<br>(340 L)   | -4°F to 10°F<br>(-20°C to -12°C) | 4.0A     | 310 lbs<br>(141 kg) | R-290a<br>3.53 oz (100 g)   | 2 / 2           | 115V / 60Hz / 1Ph |
| MXCF60UHC | 60.375" x 30" x 35.5"<br>(1533 x 762 x 911 mm)  | 56.2" x 18.8" x 24.5"<br>(1428 x 478 x 622 mm) | 15.5 Cu Ft<br>(439 L) | -4°F to 10°F<br>(-20°C to -12°C) | 5.0A     | 362 lbs<br>(166 kg) | R-290a<br>3.53 oz (100 g)   | 2 / 2           | 115V / 60Hz / 1Ph |
| MXCF72UHC | 72.375" x 30" x 35.5"<br>(1839 x 762 x 911 mm)  | 66.9" x 18.8" x 24.5"<br>(1700 x 478 x 622 mm) | 18 Cu Ft<br>(510 L)   | -4°F to 10°F<br>(-20°C to -12°C) | 6.0A     | 442 lbs<br>(203 kg) | R-290a<br>3.88 oz (110 g)   | 3 / 3           | 115V / 60Hz / 1Ph |

## INSTALLATION

- Shorter caster options are available to lower the overall height of the unit to satisfy ADA or other low profile requirements