

FLOOR CARE STRIPPER

SUPER STRIP

Powerful Value Floor Stripper

- Powerful, fast-working, designed for light to medium buildup
- Removes all water-based finishes and sealers, including metal interlocks
- Low odor, phosphate-free, biodegradable formula

Leaves the floors ready for re-application of new floor finish. Minimal contact time and concentrated formula reduce labor and overall costs.

DIRECTIONS FOR USE:

Mix product thoroughly before use. Always test in an inconspicuous area before application. Restrict pedestrian traffic when this product is in use. This product works best with cold to warm water.

Spread stripping solution liberally over the floor and let stand from 10 - 20 minutes. Do not allow the solution to dry on the floor.

Scrub thoroughly with a floor machine to break up the softened film. Pick up the dirty solution with a shop vac or auto scrubber. Detail mop the floor with clean water to remove all residue. Let the clean floor dry completely before refinishing.

RECOMMENDED DILUTIONS:

Average Conditions: Dilute 1:8 16 oz. per gallon of water
Generally, will be effective at: Dilute 1:4 - 1:16 8 - 32 oz. per gallon of water

IMPORTANT SAFETY INFORMATION:



DANGER: Harmful in contact with skin. Causes severe skin burns and eye damage. May cause respiratory irritation.

PRECAUTIONS:

Do not breathe vapors. Wash hands thoroughly after handling. Wear protective gloves, protective clothing, eye protection and face protection. Use only outdoors or in a well-ventilated area. Store locked up. Store in a well-ventilated place. Keep container tightly closed. Dispose of contents and container in accordance with local, regional, national and international regulations.

FIRST AID:

IF ON SKIN (or hair): Remove immediately all contaminated clothing. Rinse skin with water. Wash contaminated clothing before reuse.

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER or physician.

IF INHALED: Remove person to fresh air and keep comfortable for breathing.

IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.

CONTAINS:

2-butoxyethanol (CAS# 111-76-2), 2-aminoethanol (CAS# 141-43-5), Sodium hydroxide (CAS# 1310-73-2), Sodium xylene sulphonate (CAS# 1300-72-7), Nonylphenol ethoxylate NP-9 (CAS# 127087-87-0).



APPLICATIONS

- Nursing homes
- Schools
- Hospitals
- Health care applications

SPECIFICATIONS

Color Clear to straw color
Fragrance Slight solvent
pH Range 12.5 - 13.5
Form Liquid
Dilution Range 8 oz. - 32 oz. per gallon

PACKAGING

4/1 Gallon 100458-500308
5 Gallon Pail 100458-500306

PROP 65 INFO

WARNING: This product can expose you to chemicals including 2,2'-iminodiethanol (111-42-2) which is known to the State of California to cause Cancer. For more information go to www.P65Warnings.ca.gov.



Contact your Account Representative for more information

7373 Rowlett Park Dr., Tampa, FL 33610 | 813.237.6463 | Emergency #800.255.3924 | theochem.com

©2022 Theochem Laboratories Inc. All right reserved. | Made in the USA