



Lined Bottom and Sides with
2 Mesh x .063" Welded Wire
(.437" Openings, 76% Open Area)

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THREE M TOOL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THREE M TOOL IS PROHIBITED.

UNLESS OTHERWISE SPECIFIED:		Rectangular Wire Mesh Basket: 12Lx12Wx12H, 304 SS, 1/4 Rod Frame, Stacking Handles, Mesh: 2 x .063	
DIMENSIONS ARE IN INCHES			
TOLERANCES: FRACTIONAL ± 1/16" ANGULAR: ± 5 DEG. TWO PLACE DECIMAL ±0.03 THREE PLACE DECIMAL ±0.015			
EST WGT	7.0 lbs.	SIZE	DWG. NO.
MATERIAL	304 Stainless Steel	B	TMT-120120120-A02S
FINISH	Natural		
DO NOT SCALE DRAWING		SCALE: 1:6	
			SHEET 1 OF 1