


$\phi \frac{5}{16}$ "
Rod Frame



Lined Bottom and Sides with
2 Mesh x .063" Welded Wire
(.437" Openings, 76% Open Area)

UNLESS OTHERWISE SPECIFIED:	
DIMENSIONS ARE IN INCHES	
TOLERANCES:	
FRACTIONAL $\pm 1/16$ "	
ANGULAR: ± 5 DEG.	
TWO PLACE DECIMAL ± 0.03	
THREE PLACE DECIMAL ± 0.015	
EST WGT	8.9 lbs.
MATERIAL	304 Stainless Steel
FINISH	Natural
DO NOT SCALE DRAWING	

PROPRIETARY AND CONFIDENTIAL
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF THREE M TOOL. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF THREE M TOOL IS PROHIBITED.

Rectangular Wire Mesh Basket:
18Lx18Wx6H, 304 SS, 5/16 Rod Frame,
No Handles, Mesh: 2 x .063

SIZE **B** DWG. NO. TMT-180180060-N02S

SCALE: 1:6

SHEET 1 OF 1