




## LF4-80CW-TR LF4-80WW-TR

### DIMENSIONS:

8-1/2"(H) x 11-7/8"(W) x 4"(D)



## LF4 ARCHITECTURAL SERIES LED FLOOD LIGHT WITH TRUNNION

MODEL	WATTS	VOLTAGE	LUMENS	COLOR TEMP
LF4-80CW-TR	80W	120~277V AC	9500 LM	5000K
LF4-80WW-TR	80W	120~277V AC	9500 LM	3000K

Ideal for general site lighting, alleys, loading docks, doorway, pathway and parking areas. Great for use with motion sensors or other instant on/off controls.

### ELECTRICAL SPECIFICATIONS:

- Voltage: 120-277VAC 50/60Hz
- Wattage: 80W
- Input current: 1A Max
- Other wattages: 100W, 150W
- Power factor: >0.95
- Efficacy: 120LM/W

### HOUSING SPECIFICATIONS:

- Die-cast aluminum with powder coat finish (Dark Bronze)
- Operating temperature: -40°F ~ 104°F
- Lifespan: 50000 Hrs.
- IP rating: IP65, Wet Locations
- High light transmittance, anti-UV & fire resistant PC lens

### CERTIFICATIONS: UL, DLC



### LIGHTING SPECIFICATIONS:

- Dimmable: 0~10V Dimmable
- LED type/brand: Philips Lumileds LEDs / SMD 3030
- Total lumens: 9500LM
- Color temperature: 3000K / 5000K
- Color rendering index: >82
- Beam angle: 90° x 120°

### WARRANTY: 5 years



## LF4-80CW-TR LF4-80WW-TR


### LF4 ARCHITECTURAL SERIES LED FLOOD LIGHT WITH TRUNNION

MODEL	WATTS	VOLTAGE	LUMENS	COLOR TEMP
LF4-80CW-TR	80W	120~277V AC	9500 LM	5000K
LF4-80WW-TR	80W	120~277V AC	9500 LM	3000K

#### CERTIFICATIONS: UL, DLC



#### PHOTOMETRICS:



#### ILLUMINANCE AT A DISTANCE

	Center Beam fc	Beam Width	
17.0ft	12.24 fc	33.0 ft	57.0 ft
34.0ft	3.06 fc	66.0 ft	113.9 ft
51.0ft	1.36 fc	99.1 ft	170.9 ft
68.0ft	0.76 fc	132.1 ft	227.9 ft
85.0ft	0.49 fc	165.1 ft	284.8 ft
102.0ft	0.34 fc	198.1 ft	341.8 ft

■ Vert. Spread: 88.3°  
■ Horiz. Spread: 118.3°

