

This safety data sheet was created pursuant to the requirements of: US OSHA Hazard Communication Standard (29 CFR 1910.1200) and Canada WHMIS 2015 which includes the amended Hazardous Products Act (HPA) and the Hazardous Products Regulation (HPR)

Issuing Date 14-Apr-2020

Revision Date 14-Apr-2020

Revision Number 1

1. Identification

Product identifier

Product Name Wide Range Gear Oil SAE 80W-90

Other means of identification

Product Code(s) 140

Other information Blend Revision ID 2683

Recommended use of the chemical and restrictions on use

Recommended use Lubricant

Restrictions on use No information available.

Details of the supplier of the safety data sheet

Supplier Address

U.S. Lubricants, a Division of U.S. Venture Inc.
425 Better Way
Appleton, WI 54915
800-490-4900

Emergency telephone number

Emergency Telephone 800-490-4900
Chemtrec 1-800-424-9300 (Account# 705487)

2. Hazard(s) identification

Classification

Skin corrosion/irritation	Category 2
Serious eye damage/eye irritation	Category 2A
Skin sensitization	Category 1A

Label elements

Warning

Hazard statements

Causes skin irritation.
Causes serious eye irritation.
May cause an allergic skin reaction.

**Precautionary Statements - Prevention**

Wash face, hands and any exposed skin thoroughly after handling. Avoid breathing dust, fume, gas, mist, vapors and spray. Contaminated work clothing must not be allowed out of the workplace. Wear protective gloves, eye protection and face protection.

Precautionary Statements - Response

Specific treatment (see supplemental first aid instructions on this label).

Eyes

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice and attention.

Skin

IF ON SKIN: Wash with plenty of water and soap. Take off contaminated clothing and wash it before reuse. If skin irritation or rash occurs: Get medical advice and attention.

Precautionary Statements - Disposal

Dispose of contents and container to an approved waste disposal plant.

Other information

Harmful to aquatic life with long lasting effects. Harmful to aquatic life.

3. Composition/information on ingredients

Substance

Not applicable.

Mixture

Chemical name	CAS No	Weight-%	Hazardous Material Information Review Act registry number (HMIRA registry #)	Date HMIRA filed and date exemption granted (if applicable)
Hydrotreated heavy paraffinic petroleum distillate	64742-54-7	1-5	-	-
Petroleum distillates, hydrotreated light paraffinic	64742-55-8	0.5-1	-	-
Amines, C12-14-tert-alkyl	68955-53-3	0.5-1	-	-
Phosphoric acid, mono(2-ethylhexyl) ester	1070-03-7	0.1-0.5	-	-
Phosphoric acid, bis(2-ethylhexyl) ester	298-07-7	0.1-0.5	-	-
Oleylamine	112-90-3	<0.25	-	-

4. First-aid measures

Description of first aid measures**General advice**

Show this safety data sheet to the doctor in attendance.

Inhalation

Remove to fresh air. Get medical attention immediately if symptoms occur.

Eye contact

Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Keep eye wide open while rinsing. Do not rub affected area. Get medical attention if irritation develops and persists.

Skin contact	May cause an allergic skin reaction. In the case of skin irritation or allergic reactions see a physician. Wash off immediately with soap and plenty of water for at least 15 minutes.
Ingestion	Clean mouth with water and drink afterwards plenty of water. Never give anything by mouth to an unconscious person. Do NOT induce vomiting. Call a physician.
Self-protection of the first aider	Avoid contact with skin, eyes or clothing. Wear personal protective clothing (see section 8).

Most important symptoms and effects, both acute and delayed

Symptoms Itching. Rashes. Hives. May cause redness and tearing of the eyes. Burning sensation.

Indication of any immediate medical attention and special treatment needed

Note to physicians May cause sensitization in susceptible persons. Treat symptomatically.

5. Fire-fighting measures

Suitable Extinguishing Media	Dry chemical, CO2, water spray or regular foam.
Unsuitable extinguishing media	None known based on information supplied.
Specific hazards arising from the chemical	May cause sensitization by skin contact. Product is or contains a sensitizer. Thermal decomposition can lead to release of irritating gases and vapors.
Hazardous combustion products	Carbon monoxide, carbon dioxide and unburned hydrocarbons (smoke). Oxides of sulfur. Aldehydes. Ketones and their derivatives.
Explosion data	
Sensitivity to mechanical impact	None.
Sensitivity to static discharge	None.
Special protective equipment for fire-fighters	Firefighters should wear self-contained breathing apparatus and full firefighting turnout gear. Use personal protection equipment. Cool closed containers exposed to fire with water spray.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Personal precautions Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Keep people away from and upwind of spill/leak. Extremely slippery when spilled. Ensure adequate ventilation. Use personal protective equipment as required. See section 8 for more information. Evacuate personnel to safe areas. Avoid contact with skin, eyes or clothing. Remove all sources of ignition. Deny entry to unauthorized and unprotected personnel.

Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Soak up with inert absorbent material. Pick up and transfer to properly labeled containers. Use non-sparking tools.

7. Handling and storage

Precautions for safe handling

Advice on safe handling

Handle in accordance with good industrial hygiene and safety practice. Ensure adequate ventilation. In case of insufficient ventilation, wear suitable respiratory equipment. Use personal protection equipment. Avoid contact with skin, eyes or clothing. Avoid breathing vapors or mists. Wash thoroughly after handling. Do not eat, drink or smoke when using this product. Take off contaminated clothing and wash before reuse.

Conditions for safe storage, including any incompatibilities

Storage Conditions

Keep containers tightly closed in a dry, cool and well-ventilated place. Keep in properly labeled containers. Keep away from heat. Do not reuse empty containers. Keep out of the reach of children.

8. Exposure controls/personal protection

Control parameters

Exposure Limits

Chemical name	ACGIH TLV	OSHA PEL	NIOSH
Hydrotreated heavy paraffinic petroleum distillate 64742-54-7	TWA: 5 mg/m ³ (inhalable fraction)	-	-

Biological occupational exposure limits

This product, as supplied, does not contain any hazardous materials with biological limits established by the region specific regulatory bodies

Appropriate engineering controls

Engineering controls

Showers
Eyewash stations
Ventilation systems.

Individual protection measures, such as personal protective equipment

Eye/face protection

Goggles.

Hand protection

Wear suitable gloves. Impervious gloves.

Skin and body protection

Wear suitable protective clothing. Long sleeved clothing.

Respiratory protection

No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.

General hygiene considerations

Handle in accordance with good industrial hygiene and safety practice. Wash thoroughly after handling. Avoid breathing vapors or mists. Avoid contact with skin, eyes or clothing. Take off contaminated clothing and wash before reuse.

9. Physical and chemical properties

Information on basic physical and chemical properties

Appearance

Physical state	Liquid
Color	Amber
Odor	Mild Petroleum
Odor threshold	No information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	No data available	None known
Melting point / freezing point	No data available	None known
Boiling point / boiling range	No data available	None known
Flash point	173.9 °C / 345 °F	None known
Evaporation rate	No data available	None known
Flammability (solid, gas)	No data available	None known
Flammability Limit in Air		None known
Upper flammability or explosive limits	No data available	
Lower flammability or explosive limits	No data available	
Vapor pressure	No data available	None known
Vapor density	No data available	None known
Relative density	0.900 (7.5 lb/gal)	None known
Water solubility	Insoluble	None known
Solubility(ies)	No data available	None known
Partition coefficient	No data available	None known
Autoignition temperature	No data available	None known
Decomposition temperature	No data available	None known
Kinematic viscosity	131 cSt	None known
Dynamic viscosity	No data available	None known

Other information

Explosive properties	No information available.
Oxidizing properties	No information available.
Softening point	No information available
Molecular weight	No information available
VOC Content (%)	No information available
Liquid Density	No information available
Bulk density	No information available

10. Stability and reactivity

Reactivity	None under normal use conditions.
Chemical stability	Stable under normal conditions.
Possibility of hazardous reactions	None under normal processing.
Conditions to avoid	Excessive heat. Keep away from open flames, hot surfaces and sources of ignition.
Incompatible materials	Strong oxidizing agents.
Hazardous decomposition products	None known based on information supplied.

11. Toxicological information

Information on likely routes of exposure

Product Information .

Inhalation	Specific test data for the substance or mixture is not available. May cause irritation of respiratory tract.
Eye contact	Specific test data for the substance or mixture is not available. Causes serious eye irritation. (based on components). May cause redness, itching, and pain.
Skin contact	Specific test data for the substance or mixture is not available. May cause sensitization by skin contact. Repeated or prolonged skin contact may cause allergic reactions with susceptible persons. (based on components). Causes skin irritation.
Ingestion	Specific test data for the substance or mixture is not available. Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea.

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms Itching. Rashes. Hives. Redness. May cause redness and tearing of the eyes.

Acute toxicity

Numerical measures of toxicity

Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
Hydrotreated heavy paraffinic petroleum distillate	> 15 g/kg (Rat)	> 5000 mg/kg (Rabbit)	-
Petroleum distillates, hydrotreated light paraffinic	-	-	= 3900 mg/m ³ (Rat) 4 h
Amines, C12-14-tert-alkyl	= 300 mg/kg (Rat)	-	-
Phosphoric acid, mono(2-ethylhexyl) ester	= 3450 mg/kg (Rat)	> 4650 mg/kg (Rabbit)	-
Phosphoric acid, bis(2-ethylhexyl) ester	= 1400 mg/kg (Rat)	> 2000 mg/kg (Rabbit)	-
Oleylamine	= 1689 mg/kg (Rat)	-	-

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin corrosion/irritation	Classification based on data available for ingredients. Irritating to skin.
Serious eye damage/eye irritation	Classification based on data available for ingredients. Causes serious eye irritation.
Respiratory or skin sensitization	Classification based on data available for ingredients. May cause sensitization by skin contact.
Germ cell mutagenicity	No information available.
Carcinogenicity	The classification listed below for the petroleum distillates in this product pertains to those that contain more than 3% DMSO extract as measured by IP 346. The petroleum distillates in this product do not meet that criteria to be classified as carcinogens.

The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical name	ACGIH	IARC	NTP	OSHA
Hydrotreated heavy paraffinic petroleum distillate 64742-54-7	A2	Group 1	Known	X
Petroleum distillates,	A2	Group 1	Known	X

hydrotreated light paraffinic 64742-55-8				
---	--	--	--	--

Legend**ACGIH (American Conference of Governmental Industrial Hygienists)**

A2 - Suspected Human Carcinogen

IARC (International Agency for Research on Cancer)

Group 1 - Carcinogenic to Humans

NTP (National Toxicology Program)

Known - Known Carcinogen

OSHA (Occupational Safety and Health Administration of the US Department of Labor)

X - Present

Reproductive toxicity No information available.**STOT - single exposure** No information available.**STOT - repeated exposure** No information available.**Aspiration hazard** No information available.**12. Ecological information****Ecotoxicity** Harmful to aquatic life with long lasting effects.

Chemical name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea
Hydrotreated heavy paraffinic petroleum distillate 64742-54-7	-	LC50: >5000mg/L (96h, Oncorhynchus mykiss)	-	EC50: >1000mg/L (48h, Daphnia magna)
Petroleum distillates, hydrotreated light paraffinic 64742-55-8	-	LC50: >5000mg/L (96h, Oncorhynchus mykiss)	-	EC50: >1000mg/L (48h, Daphnia magna)
Phosphoric acid, bis(2-ethylhexyl) ester 298-07-7	-	LC50: =20mg/L (96h, Oncorhynchus mykiss)	-	-

Persistence and degradability No information available.**Bioaccumulation** No information available.**Mobility in soil** No information available.**Other adverse effects** No information available.**13. Disposal considerations****Waste treatment methods****Waste from residues/unused products** Should not be released into the environment. Dispose of in accordance with local regulations. Dispose of waste in accordance with environmental legislation.**Contaminated packaging** Do not reuse empty containers.

14. Transport information

<u>DOT</u>	Not regulated
<u>TDG</u>	Not regulated
<u>IATA</u>	Not regulated
<u>IMDG</u>	Not regulated

15. Regulatory information

Safety, health and environmental regulations/legislation specific for the substance or mixture

International Regulations

The Montreal Protocol on Substances that Deplete the Ozone Layer Not applicable

The Stockholm Convention on Persistent Organic Pollutants Not applicable

The Rotterdam Convention Not applicable

International Inventories

TSCA Contact supplier for inventory compliance status.

DSL/NDSL Contact supplier for inventory compliance status.

Legend:

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

US Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372.

SARA 311/312 Hazard Categories

Should this product meet EPCRA 311/312 Tier reporting criteria at 40 CFR 370, refer to Section 2 of this SDS for appropriate classifications.

CWA (Clean Water Act)

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42).

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material.

US State Regulations

California Proposition 65

This product does not contain any Proposition 65 chemicals.

U.S. State Right-to-Know Regulations

Chemical name	New Jersey	Massachusetts	Pennsylvania
Petroleum distillates, hydrotreated light paraffinic 64742-55-8	-	X	-
Phosphoric acid, bis(2-ethylhexyl) ester 298-07-7	X	-	-

U.S. EPA Label Information

EPA Pesticide Registration Number Not applicable

16. Other information

NFPA	Health hazards 2	Flammability 1	Instability 0	Physical and chemical properties -
HMIS	Health hazards 2	Flammability 1	Physical hazards 0	Personal protection X

Key or legend to abbreviations and acronyms used in the safety data sheetLegend Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

TWA	TWA (time-weighted average)	STEL	STEL (Short Term Exposure Limit)
Ceiling	Maximum limit value	*	Skin designation

Key literature references and sources for data used to compile the SDS

U.S. Environmental Protection Agency ChemView Database
 European Food Safety Authority (EFSA)
 EPA (Environmental Protection Agency)
 Acute Exposure Guideline Level(s) (AEGL(s))
 U.S. Environmental Protection Agency Federal Insecticide, Fungicide, and Rodenticide Act
 U.S. Environmental Protection Agency High Production Volume Chemicals
 Food Research Journal
 Hazardous Substance Database
 International Uniform Chemical Information Database (IUCLID)
 Japan GHS Classification
 Australia National Industrial Chemicals Notification and Assessment Scheme (NICNAS)
 NIOSH (National Institute for Occupational Safety and Health)
 National Library of Medicine's ChemID Plus (NLM CIP)
 National Toxicology Program (NTP)
 New Zealand's Chemical Classification and Information Database (CCID)
 Organization for Economic Co-operation and Development Environment, Health, and Safety Publications
 Organization for Economic Co-operation and Development High Production Volume Chemicals Program
 Organization for Economic Co-operation and Development Screening Information Data Set
 World Health Organization

Issuing Date 14-Apr-2020

Revision Date 14-Apr-2020

Revision Note Initial Release.

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet