

SAFETY DATA SHEET

PRODUCT NAME: Rainguard™ Microseal™ Densifier LS
Product Codes: CR-0801, CR-0805

SECTION 1 - IDENTIFICATION

MANUFACTURER: Weatherman Products, Inc
21622 Surveyor Circle
Huntington Beach, CA 92646
United States of America

PHONE: (949) 515-8800
(866)989-5159
EMAIL: info@rainguard.com
WEB SITE: rainguardpro.com

DATE PRINTED: October 27, 2018

SECTION 2- HAZARDS IDENTIFICATION

INHALATION HEALTH RISKS AND SYMPTOMS OF EXPOSURE:

Inhalation exposure may cause dizziness, headaches and even unconsciousness.

SKIN AND EYE CONTACT HEALTH RISKS AND SYMPTOMS OF EXPOSURE:

Prolonged skin contact will cause drying and/or defatting of skin tissues leading to irritation and dermatitis. Eye contact may cause irritation and blurred vision.

SKIN ABSORPTION HEALTH RISKS AND SYMPTOMS OF EXPOSURE:

Drying and/or defatting of skin.

INGESTION HEALTH RISKS AND SYMPTOMS OF EXPOSURE:

Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhea.

HEALTH HAZARDS (ACUTE AND CHRONIC):

The proper use of this paint product does not present any serious health hazards known to the manufacturer.

SECTION 3 - COMPOSITION

| <u>Chemical Name</u> | <u>CAS-No.</u> | <u>Weight% Range</u> |
|----------------------|----------------|----------------------|
|----------------------|----------------|----------------------|

THIS PRODUCT DOES NOT CONTAIN ANY SUBSTANCES KNOWN TO THE STATE OF CALIFORNIA TO CAUSE CANCER OR REPRODUCTIVE HARM.

There are no chemicals subject to the reporting requirements of Section 313 (SARA Title III) and of 40 CFR 372

SECTION 4 -FIRST AID MEASURES

Get immediate medical attention for any significant overexposure

INHALATION: Move victim to fresh air. If victim has difficulty breathing, administer oxygen. If breathing has stopped, initiate CPR. Seek immediate medical attention.

SAFETY DATA SHEET

PRODUCT NAME: Rainguard™ Microseal™ Densifier LS
Product Codes: CR-0801, CR-0805

INGESTION: Never give an unconscious person anything to drink. If conscious, treat for shock. Seek immediate medical assistance or nearest poison control center. If conscious, induce vomiting. If unconscious and vomiting, turn the victim on their side to avoid choking.

SKIN CONTACT: Wash exposed areas with soap and water. Remove contaminated clothing and shoes. Wash contaminated clothing before reuse.

EYES: Flush eyes with running water for at least 15 minutes. Hold eyelids apart to insure rinsing of the entire surface of the eye and lids with water. Seek immediate medical attention.

| | | |
|------------------|------------------|----|
| CARCINOGENICITY: | NTP: | No |
| | IARC Monographs: | No |
| | OSHA Regulated: | No |

SECTION 5 - FIRE-FIGHTING MEASURES

| | |
|--|--|
| FLASH POINT: | None |
| METHOD | Not applicable |
| LOWER EXPLOSION LIMIT: | Not available |
| UPPER EXPLOSION LIMIT: | Not available |
| AUTOIGNITION TEMPERATURE: | Not available |
| EXTINGUISHING MEDIA: | CO ₂ , dry chemical or water fog. |
| HAZARDOUS COMBUSTION PRODUCTS: | Carbon monoxide and carbon dioxide can form. Smoke, fumes |
| PROTECTIVE EQUIPMENT FOR FIREFIGHTERS: | Use accepted fire fighting techniques. Wear full firefighting protective clothing, including self-contained breathing apparatus (SCBA). If water is used, fog nozzles are preferable. Use water to cool closed containers. |
| FIRE AND EXPLOSION CONDITIONS: | This product not expected to ignite under normal conditions of use. |

SECTION 6 - ACCIDENTAL RELEASE MEASURES

Remove and eliminate all ignition sources. Control the source of the spill. Ventilate confined spaces. Avoid breathing vapors or mist. Dike and soak up spill with absorbent material such as sand or Fuller's Earth. Recover free liquid and absorbent material from spill area and shovel or broom into appropriate chemical waste containers for proper disposal. Persons performing clean up should wear adequate personal protective equipment and clothing. Keep out of storm drains, sewers and waterways. Observe all local, state and federal laws and regulations regarding spills, clean-up, removal, discharge and disposal.

SAFETY DATA SHEET

PRODUCT NAME: Rainguard™ Microseal™ Densifier LS
Product Codes: CR-0801, CR-0805

SECTION 7 - HANDLING AND STORAGE

Handling: Avoid contact with eyes, skin and clothing. Avoid breathing spray mist. Keep container closed. Promptly clean residue from closures with cloth dampened with water. Promptly clean up spills.

Storage: Keep containers closed. Store in clean plastic containers. Separate from acids, reactive metals, and ammonium salts. Storage temperature 0-95°C. Loading temperature 45-95°C. Do not store in aluminum, steel, fiber glass, copper, brass, zinc, or galvanized containers.

SECTION 8 - EXPOSURE CONTROLS/PERSONAL PROTECTION

The recommendations described in this section are provided as general guidance for minimizing exposure when handling this product. Because use conditions will vary depending upon customer applications, specific safe handling procedures should be developed by a person knowledgeable of the intended use, working conditions and equipment.

Engineering Controls: Use with adequate ventilation. Keep containers closed. Safety shower and eyewash fountain should be within direct access.

RESPIRATORY PROTECTION: Use in a well ventilated and/or open area. Use appropriate NOISH approved organic vapor cartridge respirator equipment when occupational exposure limits are exceeded.

VENTILATION: Local exhaust and or mechanical ventilation in confined or poorly ventilated spaces are recommended.

PROTECTIVE GLOVES: Wear Neoprene or non-soluble plastic gloves.

EYE PROTECTION: Wear chemical goggles.

PROTECTIVE CLOTHING: Wear body-covering protective clothing and gloves

INDUSTRIAL HYGIENE: Before eating or smoking, wash hands and face to remove residual contamination.

EXPOSURE LIMITS:

| <u>Chemical name</u> | <u>CAS Number</u> | <u>Regulation</u> | <u>Limit</u> | <u>Form</u> |
|----------------------|-------------------|-------------------|--------------|-------------|
|----------------------|-------------------|-------------------|--------------|-------------|

SAFETY DATA SHEET

PRODUCT NAME: Rainguard™ Microseal™ Densifier LS
Product Codes: CR-0801, CR-0805

SECTION 9 - PHYSICAL AND CHEMICAL PROPERTIES

| | |
|-----------------------------------|-----------------------------------|
| BOILING POINT: 212° F | SPECIFIC GRAVITY (H2O = 1): 1.075 |
| VAPOR DENSITY (AIR =1): NA | EVAPORATION RATE (ETHER = 1): NA |
| FLAMMABILITY/EXPLOSIVE LIMITS: NA | VISCOCITY: 65 KU |
| Ph: 6 | MELTING/FREEZING POINT: 32° F |
| MATERIAL V.O.C.: 0g/L | SOLUBILITY IN WATER: Dispersible |

APPEARANCE & ODOR: Clear liquid with mild odor VAPOR PRESSURE (mm HG):

SECTION 10 - STABILITY and REACTIVITY

SUBSTANCES TO AVOID: Do not mix with other chemicals.

STABILITY: Stable.

HAZARDOUS POLYMERIZATION: Will not occur.

HAZARDOUS DECOMPOSITION OR THERMAL BYPRODUCTS: Carbon dioxide and carbon monoxide

SECTION 11 - TOXICOLOGICAL INFORMATION

No Data Available

SECTION 12 - ECOLOGICAL INFORMATION

No Data Available

SECTION 13 - DISPOSAL CONSIDERATIONS

Do not allow material to contaminate or cause to be discharged into any storm drain, lake, stream, pond, underground water supplies or any body of water. Incinerate and or bury waste and containers at an approved facility. Dispose of waste materials and containers in accordance with all federal, state and local health, safety and environmental regulations.

SECTION 14- TRANSPORTATION/SHIPPING DATA

REGULATED BY:

United States DOT: Not Regulated

Canada (TDG): Not Regulated

DOT Proper Shipping Name: N/A

UN / NA Number: N/A

Hazard Class: N/A

Packing Group: N/A

SAFETY DATA SHEET

PRODUCT NAME: Rainguard™ Microseal™ Densifier LS
Product Codes: CR-0801, CR-0805

SECTION 15 - REGULATORY INFORMATION

NORTH AMERICAN INVENTORIES: All components listed or exempt from the TSCA inventory.
This product or its components are listed on, or exempt from
the Canadian Domestic Substances List.

CANADIAN REGULATIONS:

WHMIS Classification: D2A
This is a "controlled product" under the Canadian Workplace
Hazardous Materials Information System (WHMIS)

This product has been classified in accordance with the hazard criteria of the Controlled Products
Regulations (CPR) and the SDS contains all of the information required by the CPR.

OTHER REGULATIONS: Regulatory VOC (less water and exempt solvent) <15 g/L

SECTION 16 - OTHER INFORMATION

HMIS RATING:

0 = Minimum
1 = Slight
2 = Moderate
3 = Serious
4 = Severe

| | |
|---------------------|----------|
| HEALTH | 1 |
| FLAMMABILITY | 0 |
| REACTIVITY | 0 |
| PPE | A |

LEGEND

ACGIH - American Conference of Governmental Hygienists
OSHA - Occupational Safety and Health Administration
DOT - Department of Transportation
PEL - Permissible Exposure Limit
DSL - Domestic Substance List
RCRA - Resource Conservation and Recovery Act
EPA - Environmental Protection Agency
STEL - Short Term Exposure Limit
HMIS - Hazardous Materials Information System
TLV - Threshold Limit Value
IARC - International Agency for Research on Cancer

TSCA - Toxic Substances Control Act
MSHA - Mine Safety Health Administration
TWA - Time Weighted Average
NDSL - Non-Domestic Substance List
V - Volume
NIOSH - National Institute for Occupational Safety Health
VOC - Volatile Organic Compound
NTP - National Toxicology Program
WHMIS - Workplace Hazardous Materials Information
System

The information contained in the document relates to the specific material designated and may not be valid for such material used in combination with any other material or in any process. Such information is to the best of our knowledge and belief accurate and reliable as of the date compiled. However no representation, warranty or guarantee, is made as to its accuracy reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability and completeness of such information for their own particular use. We do not accept liability for any loss or damage that may occur from the use or reliance upon this information.

<<END>>