



Revision Number: 003.0

Issue date: 02/16/2018

**1. PRODUCT AND COMPANY IDENTIFICATION**

**Product name:** LOCTITE SF 7601 EQUIPMENT FLUSH SOLVENT known as EQUIPMENT FLUSHING SOLVENT Sol **IDH number:** 135238

**Product type:** Cleaner **Item number:** 12121

**Restriction of Use:** None identified **Region:** Canada

**Company address:** Henkel Canada Corporation  
Meadowpine Boulevard 2515  
Mississauga, Ontario L5N 6C3

**Contact information:**  
Telephone: +1 (905) 814-6511  
MEDICAL EMERGENCY Phone: Poison Control Center  
1-877-671-4608 (toll free) or 1-303-592-1711  
TRANSPORT EMERGENCY Phone: CHEMTREC  
1-800-424-9300 (toll free) or 1-703-527-3887  
Internet: www.henkelna.com

**2. HAZARDS IDENTIFICATION**

**EMERGENCY OVERVIEW**

**DANGER:** CAUSES SKIN IRRITATION.  
CAUSES SERIOUS EYE IRRITATION.  
MAY CAUSE DROWSINESS OR DIZZINESS.  
MAY CAUSE GENETIC DEFECTS.  
MAY CAUSE CANCER.  
MAY CAUSE DAMAGE TO ORGANS THROUGH PROLONGED OR REPEATED EXPOSURE.

HAZARD CLASS	HAZARD CATEGORY
SKIN IRRITATION	2
EYE IRRITATION	2A
GERM CELL MUTAGENICITY	1B
CARCINOGENICITY	1B
SPECIFIC TARGET ORGAN TOXICITY - SINGLE EXPOSURE	3
SPECIFIC TARGET ORGAN TOXICITY - REPEATED EXPOSURE	2

**PICTOGRAM(S)**



**Precautionary Statements**

**Prevention:** Obtain special instructions before use. Do not handle until all safety precautions have been read and understood. Do not breathe vapors, mist, or spray. Wash affected area thoroughly after handling. Use only outdoors or in a well-ventilated area. Wear protective gloves, clothing, eye and face protection.

**Response:** IF ON SKIN: Wash with plenty of water. IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing. Call a POISON CENTER or physician if you feel unwell. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. IF exposed or concerned: Get medical attention. If

IDH number: 135238

Product name: LOCTITE SF 7601 EQUIPMENT FLUSH SOLVENT known as EQUIPMENT FLUSHING SOLVENT Sol

**Storage:**  
**Disposal:**

skin irritation occurs: Get medical attention. If eye irritation persists: Get medical attention. Take off contaminated clothing.  
Store in a well-ventilated place. Keep container tightly closed. Store locked up.  
Dispose of contents and/or container according to Federal, State/Provincial and local governmental regulations.

Classification complies with Canadian Hazardous Products Regulations (WHMIS 2015) and is consistent with the provision of the United Nations Globally Harmonized System of Classification and Labeling of Chemicals (GHS).

See Section 11 for additional toxicological information.

### 3. COMPOSITION / INFORMATION ON INGREDIENTS

Hazardous Component(s)	CAS Number	Weight %*
Methylene chloride	75-09-2	90 - 100
Propylene oxide	75-56-9	0.1 - 1

\* Exact percentages may vary or are trade secret. Concentration range is provided to assist users in providing appropriate protections.

### 4. FIRST AID MEASURES

<b>Inhalation:</b>	Move to fresh air. If breathing is difficult, give oxygen. If not breathing, give artificial respiration. Get medical attention.
<b>Skin contact:</b>	Remove contaminated clothing and footwear. Immediately flush skin with plenty of water (using soap, if available). If symptoms develop and persist, get medical attention. Wash clothing before reuse.
<b>Eye contact:</b>	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Get medical attention.
<b>Ingestion:</b>	Do not induce vomiting. Never give anything by mouth to an unconscious person. Get medical attention.
<b>Symptoms:</b>	See Section 11.

### 5. FIRE FIGHTING MEASURES

<b>Extinguishing media:</b>	Water spray (fog), foam, dry chemical or carbon dioxide.
<b>Special firefighting procedures:</b>	Wear a self-contained breathing apparatus with a full face piece operated in pressure-demand or other positive pressure mode.
<b>Unusual fire or explosion hazards:</b>	Closed containers may rupture (due to build up of pressure) when exposed to extreme heat.
<b>Hazardous combustion products:</b>	Oxides of carbon. Hydrochloric acid. Phosgene. Toxic and irritating vapors.

### 6. ACCIDENTAL RELEASE MEASURES

Use personal protection recommended in Section 8, isolate the hazard area and deny entry to unnecessary and unprotected personnel.

<b>Environmental precautions:</b>	Do not allow product to enter sewer or waterways.
<b>Clean-up methods:</b>	Ensure adequate ventilation. Isolate area. Keep unnecessary personnel away. Soak up with inert absorbent. Store in a closed container until ready for disposal. Refer to Section 8 "Exposure Controls / Personal Protection" prior to clean up.

## 7. HANDLING AND STORAGE

- Handling:** Use only with adequate ventilation. Prevent contact with eyes, skin and clothing. Do not breathe vapor and mist. Wash thoroughly after handling. Refer to Section 8.
- Storage:** Keep in a cool, well ventilated area away from heat, sparks and open flame. Keep container tightly closed until ready for use.

**Shelf Life Statement:** Not available.

## 8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Employers should complete an assessment of all workplaces to determine the need for, and selection of, proper exposure controls and protective equipment for each task performed.

Hazardous Component(s)	ACGIH TLV	OSHA PEL	AIHA WEEL	OTHER
Methylene chloride	50 ppm TWA	12.5 ppm OSHA_ACT 25 ppm TWA 125 ppm STEL	None	None
Propylene oxide	2 ppm TWA (Dermal sensitization)	100 ppm (240 mg/m3) PEL	None	None

- Engineering controls:** Ensure adequate ventilation. Local exhaust ventilation is recommended when general ventilation is not sufficient to control airborne contamination below occupational exposure limits.
- Respiratory protection:** Use NIOSH approved respirator if there is potential to exceed exposure limit(s).
- Eye/face protection:** Safety goggles or safety glasses with side shields. Full face protection should be used if the potential for splashing or spraying of product exists. Safety showers and eye wash stations should be available.
- Skin protection:** Use impermeable gloves and protective clothing as necessary to prevent skin contact. Viton gloves. Nitrile gloves.

## 9. PHYSICAL AND CHEMICAL PROPERTIES

- Physical state:** Liquid
- Color:** Clear colorless
- Odor:** Sweet, Solvent
- Odor threshold:** Not available.
- pH:** Not available.
- Vapor pressure:** 350 mbar (20 °C (68°F))
- Boiling point/range:** Not available.
- Melting point/ range:** Not available.
- Specific gravity:** 1.31 at 25 °C (77°F)
- Vapor density:** 2.93
- Flash point:** No flash point up to 200 °C
- Flammable/Explosive limits - lower:** Not available.
- Flammable/Explosive limits - upper:** Not available.
- Autoignition temperature:** 556.00 °C (1,032.8 °F)
- Flammability:** Not applicable
- Evaporation rate:** Not available.
- Solubility in water:** Slightly soluble
- Partition coefficient (n-octanol/water):** Not available.
- VOC content:** < 1 %; < 10 g/l
- Viscosity:** Not available.
- Decomposition temperature:** Not available.

## 10. STABILITY AND REACTIVITY

<b>Stability:</b>	Stable under normal conditions of storage and use.
<b>Hazardous reactions:</b>	None under normal processing.
<b>Hazardous decomposition products:</b>	Oxides of carbon. Irritating and toxic gases or fumes may be released during a fire. Hydrogen chloride. Phosgene. Irritating organic fragments.
<b>Incompatible materials:</b>	Acids and bases. Oxidizing agents.
<b>Reactivity:</b>	Not available.
<b>Conditions to avoid:</b>	Avoid excessive heat and ignition sources. Store away from incompatible materials.

## 11. TOXICOLOGICAL INFORMATION

**Relevant routes of exposure:** Skin, Inhalation, Eyes, Ingestion

**Potential Health Effects/Symptoms**

<b>Inhalation:</b>	Exposure to high doses may cause central nervous system depression. Such doses may also cause adverse effects in the liver, kidneys, and lungs. The solvent vapors can be harmful and cause headache, nausea, and intoxication. Carboxyhemoglobin levels can be elevated in persons exposed to methylene chloride and can cause substantial stress on the cardiovascular system. This elevation can be additive to the increase caused by smoking and other carbon monoxide sources.
<b>Skin contact:</b>	Causes skin irritation. Prolonged single exposure can result in progressively severe burning sensation and redness.
<b>Eye contact:</b>	Causes serious eye irritation.
<b>Ingestion:</b>	Harmful if swallowed. May cause gastrointestinal tract irritation if swallowed.

Hazardous Component(s)	LD50s and LC50s	Immediate and Delayed Health Effects
Methylene chloride	Oral LD50 (Rat) = 1,600 mg/kg	Blood, Cardiac, Central nervous system, Corrosive, Irritant, Kidney, Liver, Some evidence of carcinogenicity
Propylene oxide	Oral LD50 (Rat) = 380 mg/kg Dermal LD50 (Rabbit) = 1,245 mg/kg Inhalation LC50 (Rat, 4 h) = 4000 ppm	Corrosive, Irritant, Mutagen, Nervous System, Some evidence of carcinogenicity

Hazardous Component(s)	NTP Carcinogen	IARC Carcinogen	OSHA Carcinogen (Specifically Regulated)
Methylene chloride	Reasonably Anticipated to be a Human Carcinogen.	Group 2A	Yes
Propylene oxide	Reasonably Anticipated to be a Human Carcinogen.	Group 2B	No

## 12. ECOLOGICAL INFORMATION

**Ecological information:** Not available.

### 13. DISPOSAL CONSIDERATIONS

Information provided is for unused product only.

**Recommended method of disposal:** Follow all local, state, federal and provincial regulations for disposal.

### 14. TRANSPORT INFORMATION

The transport information provided in this section only applies to the material/formulation itself, and is not specific to any package/configuration.

#### Canada Transportation of Dangerous Goods - Ground

**Proper shipping name:** DICHLOROMETHANE  
**Hazard class or division:** 6.1  
**Identification number:** UN 1593  
**Packing group:** III

#### International Air Transportation (ICAO/IATA)

**Proper shipping name:** Dichloromethane  
**Hazard class or division:** 6.1  
**Identification number:** UN 1593  
**Packing group:** III

#### Water Transportation (IMO/IMDG)

**Proper shipping name:** DICHLOROMETHANE  
**Hazard class or division:** 6.1  
**Identification number:** UN 1593  
**Packing group:** III

### 15. REGULATORY INFORMATION

#### Canada Regulatory Information

**CEPA DSL/NDSL Status:** All components are listed on or are exempt from listing on the Canadian Domestic Substances List.

#### United States Regulatory Information

**TSCA 8 (b) Inventory Status:** All components are listed or are exempt from listing on the Toxic Substances Control Act Inventory.

### 16. OTHER INFORMATION

**This safety data sheet contains changes from the previous version in sections:** New Safety Data Sheet format.

**Prepared by:** Product Safety and Regulatory Affairs

**Issue date:** 02/16/2018

**DISCLAIMER:** The data contained herein are furnished for information only and are believed to be reliable. However, Henkel Corporation and its affiliates ("Henkel") does not assume responsibility for any results obtained by persons over whose methods Henkel has no control. It is the user's responsibility to determine the suitability of Henkel's products or any production methods mentioned herein for a particular purpose, and to adopt such precautions as may be advisable for the protection of property and persons against any hazards that may be involved in the handling and use of any Henkel's products. In light of the foregoing, Henkel specifically disclaims all warranties, express or implied, including warranties of merchantability and fitness for a particular purpose, arising from sale or use of Henkel's products. Henkel further disclaims any liability for consequential or incidental damages of any kind, including lost profits.