

Stucco Sealer™

Vertical & Horizontal Stucco Surfaces

TECHNICAL DATA SHEET

Silane / Siloxane water repellent provides protection from mold, mildew, and efflorescence. Clear long lasting formula designed to seal stucco surfaces.



Product Codes

| | LC | | |
|--------------|------------|---------|--|
| Ready to Use | 1Q → 2 Gal | SP-7002 | |
| | 1Q → 5 Gal | SP-7003 | |
| | 16 Oz | SP-7006 | |
| | 1 Gal | SP-7004 | |
| | 5 Gal | SP-7005 | |
| | | | |

Description

Stucco Sealer is a solvent-free, 100% active solid, silane/ siloxane repellent. Stucco Sealer self-emulsifies to form a high-performance and deep-penetrating, alkali-resistant water-repellent emulsion. When applied, Stucco Sealer forms a long chain water-repellent barrier deep within the stucco surface. This hydrophobic barrier repels water, yet remains highly vapor-permeable and allows moisture to escape. Stucco Sealer performance is not affected by weathering, UV light, or wind-driven rain.

Stucco Sealer uses MICRO-LOK to create a micro-molecular chemical and mechanical bond between the water-repellent chemicals and the substrate. Stucco Sealer penetrates deep into porous stucco surfaces to provide long-lasting and virtually indestructible water-repellent protection that is not affected by weather or sunlight. It helps prevent spalling, and cracking caused by freeze/thaw cycles. Helps prevent chloride ion intrusion and efflorescence.

Features

- Freeze/thaw damage resistant
- Mold and mildew inhibitor
- Protects against weathering and UV light
- Single or multiple coat application
- V.O.C. compliant
- Contains no known carcinogens
- Breathable – does not trap moisture
- Can be used in cold temperature applications
- Will NOT yellow or turn cloudy

Benefits

- Penetrates deep – Perfect for use on sidewalks, driveways and garages
- Stain resistant to oil, gas and anti-freeze
- Easy to use – Same day, one coat application
- Apply in cold weather down to 40°F
- Easy clean up – Simple rinse w/ soap & water
- Low VOC and low odor
- Won't harm pets or plants

Test Panel

Always apply material to a mock wall or test panel. Test wall or actual surface area to determine acceptable color, surface porosity, application rates and methods before starting application.

Coverage Rates* (Theoretical)

| Substrate | Sq Ft / Gallon |
|-----------|----------------|
| Stucco | 100-150 |

**Extremely porous stucco may require multiple coats*

Satisfaction Guarantee

We guarantee that you will be satisfied with our products. If you are unsatisfied, we will be happy to replace the product or issue a refund. See Rainguard.com for details.

Dilution

Add clean water to concentrate ONLY
If product is Ready To Use - DO NOT DILUTE

Rainguard® Stucco Sealer™





Rainguard® Stucco Sealer™

How to Apply

1. Stucco Sealer should be applied using a hand pumped garden sprayer (do not atomize) or low-pressure airless spray equipment.
2. If using airless spray equipment we recommend a spray tip size of .035 to .051. Spray head should be held 8 to 12 inches from the surface so that the flood coat runs down the wall approximately 6-12 inches below the point of application.
3. Avoid application in windy weather.
4. Trigger gun off at the end of each pass to avoid using excessive materials. Stop all applications only at corners, joints, seams, or edges.
5. Multiple coats may be applied. Whiting or yellowing will not occur.

and mold and mildew, etc. All cracks should be pointed or caulked. All voids, beeholes, masonry surface defects and openings such as conduits, pipes, drains, door frames, vents, air conditioner openings, electrical openings, control joints, or any dissimilar materials should be repaired using urethane or other approved patching.

Do not apply to stucco if moisture content is greater than 15% as measured with an electronic moisture meter. Do not apply materials in climates where freezing temperatures have existed prior to application. Allow adequate time for surfaces to thaw. Establish that air, surface, and material temperatures are above 40°F (4.4°C) and at least 5°F above the dew point prior to painting. Do not apply at temperatures below 40°F when temperatures are expected to drop below 40°F within 48 hours of application. Do not apply if rain, snow, or lower temperatures are expected within 48 hours. Do not apply if relative humidity is greater than 90%.

Store materials in a well-protected area at 45°-90°F. Avoid freezing temperatures, direct sunlight, & moisture. Keep away from heat sources.

Precautions & Limitations

All stucco to be coated should be clean of any dirt and grime, efflorescence, lime run, form oils and release agents, grease, mud, excess mortar,

Test Data

| | |
|----------------------------------|--|
| Wind Driven Rain | ASTM E-514-86., 98.7% Leak Red |
| Water Pen Fed Spec | SS-W-110C, 75% Min Req, 96.8 Leak Red Chloride Ion Intr |
| Salt Pounding NCHRP | No. 244 Series IV - 95% Red No. 244 Series II - 83% Red |
| Water Abs CMU ASTM C140-75 | 98.6% Effective |
| Water Vapor Trans ASTM D-1653-71 | 100% Vapor Perm |
| Water Repellency ASTM C67-87 | 98.6% Effective |
| Weathering ASTM G-53 | 3,500 Hours - No Change |
| Surface Burning ASTM E84 | Flame Spread 0, Smoke Development 0 |

Technical Data

| | |
|--------------------|--------------------------------|
| Material Type | Silane/Siloxane |
| Active Content | 100% |
| Volume Solids | 40 or 80%(Depends on Dilution) |
| Color of Material | Milky White |
| Odor | Slight Odor |
| V.O.C. | 20 g/L V.O.C. Compliant |
| Flash Point | Non-Flammable |
| pH Value | 6 |
| Viscosity | 9.6 Seconds No. 4 Ford Cup |
| Weight | Approximately 8.7 lbs./Gal. |
| Surface Dry/Recoat | Approx 1 Hour |
| Full Chemical Cure | 5 to 7 days |

