



1. Identification

Product name : SikaFast®-3511 Part A

Supplier : Sika Corporation
201 Polito Avenue
Lyndhurst, NJ 07071
USA
www.sikausa.com

Telephone : (201) 933-8800

Telefax : (201) 804-1076

E-mail address : ehs@sika-corp.com

Emergency telephone : CHEMTREC: 800-424-9300
INTERNATIONAL: 703-527-3887

Recommended use of the chemical and restrictions on use : For further information, refer to product data sheet.

2. Hazards identification

GHS Classification

Flammable liquids, Category 2	H225: Highly flammable liquid and vapor.
Skin irritation, Category 2	H315: Causes skin irritation.
Eye irritation, Category 2A	H319: Causes serious eye irritation.
Skin sensitization, Category 1	H317: May cause an allergic skin reaction.
Specific target organ systemic toxicity - single exposure, Category 3, Respiratory system	H335: May cause respiratory irritation.
Specific target organ systemic toxicity - repeated exposure, Category 2	H373: May cause damage to organs through prolonged or repeated exposure.

GHS label elements

Hazard pictograms : 

Signal Word : Danger

Hazard Statements : H225 Highly flammable liquid and vapor.
H315 Causes skin irritation.
H317 May cause an allergic skin reaction.
H319 Causes serious eye irritation.
H335 May cause respiratory irritation.
H373 May cause damage to organs through prolonged or repeated exposure.



Precautionary Statements : **Prevention:**
 P210 Keep away from heat/sparks/open flames/hot surfaces.
 No smoking.
 P233 Keep container tightly closed.
 P240 Ground/bond container and receiving equipment.
 P241 Use explosion-proof electrical/ ventilating/ lighting/ equipment.
 P242 Use only non-sparking tools.
 P243 Take precautionary measures against static discharge.
 P260 Do not breathe dust/ fume/ gas/ mist/ vapors/ spray.
 P264 Wash skin thoroughly after handling.
 P271 Use only outdoors or in a well-ventilated area.
 P272 Contaminated work clothing must not be allowed out of the workplace.
 P280 Wear protective gloves/ eye protection/ face protection.
Response:
 P303 + P361 + P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.
 P304 + P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.
 P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
 P314 Get medical advice/ attention if you feel unwell.
 P333 + P313 If skin irritation or rash occurs: Get medical advice/ attention.
 P337 + P313 If eye irritation persists: Get medical advice/ attention.
 P362 Take off contaminated clothing and wash before reuse.
 P370 + P378 In case of fire: Use dry sand, dry chemical or alcohol-resistant foam to extinguish.
Storage:
 P403 + P233 Store in a well-ventilated place. Keep container tightly closed.
 P403 + P235 Store in a well-ventilated place. Keep cool.
 P405 Store locked up.
Disposal:
 P501 Dispose of contents/ container to an approved waste disposal plant.

Warning : Reports have associated repeated and prolonged exposure to some of the chemicals in this product with permanent brain,liver, kidney and nervous system damage. Intentional misuse by deliberate concentration and inhalation of vapors may be harmful or fatal.

See Section 11 for more detailed information on health effects and symptoms.
 There are no hazards not otherwise classified that have been identified during the classification process.
 There are no ingredients with unknown acute toxicity used in a mixture at a concentration $\geq 1\%$.

3. Composition/information on ingredients

**Hazardous ingredients**

Chemical name	CAS-No.	Concentration (%)
methyl methacrylate	80-62-6	> 45 - < 65 %
Ethene, homopolymer, chlorinated, chlorosulfonated	68037-39-8	> 25 - < 45 %
Methacrylic acid	79-41-4	> 1 - < 3 %

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

4. First aid measures

- If inhaled : Move to fresh air.
Consult a physician after significant exposure.
- In case of skin contact : Take off contaminated clothing and shoes immediately.
Wash off with soap and plenty of water.
If symptoms persist, call a physician.
- In case of eye contact : Immediately flush eye(s) with plenty of water.
Remove contact lenses.
Keep eye wide open while rinsing.
If eye irritation persists, consult a specialist.
- If swallowed : Clean mouth with water and drink afterwards plenty of water.
Do not induce vomiting without medical advice.
Do not give milk or alcoholic beverages.
Never give anything by mouth to an unconscious person.
Obtain medical attention.
- Most important symptoms and effects, both acute and delayed : irritant effects
sensitizing effects

Cough
Respiratory disorder
Allergic reactions
Excessive lachrymation
Erythema
Dermatitis
See Section 11 for more detailed information on health effects and symptoms.

Causes skin irritation.
May cause an allergic skin reaction.
Causes serious eye irritation.
May cause respiratory irritation.
May cause damage to organs through prolonged or repeated exposure.
- Protection of first-aiders : Move out of dangerous area.
Consult a physician.
Show this material safety data sheet to the doctor in attendance.



Notes to physician : Treat symptomatically.

5. Fire-fighting measures

- Suitable extinguishing media : Alcohol-resistant foam
Carbon dioxide (CO₂)
Dry chemical
- Unsuitable extinguishing media : Water
High volume water jet
- Specific hazards during fire fighting : Do not use a solid water stream as it may scatter and spread fire.
- Specific extinguishing methods : Use water spray to cool unopened containers.
Collect contaminated fire extinguishing water separately. This must not be discharged into drains.
Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.
- Special protective equipment for fire-fighters : In the event of fire, wear self-contained breathing apparatus.

6. Accidental release measures

- Personal precautions, protective equipment and emergency procedures : Use personal protective equipment.
Remove all sources of ignition.
Deny access to unprotected persons.
Beware of vapors accumulating to form explosive concentrations. Vapors can accumulate in low areas.
- Environmental precautions : Prevent product from entering drains.
If the product contaminates rivers and lakes or drains inform respective authorities.
Local authorities should be advised if significant spillages cannot be contained.
- Methods and materials for containment and cleaning up : Contain spillage, and then collect with non-combustible absorbent material, (e.g. sand, earth, diatomaceous earth, vermiculite) and place in container for disposal according to local / national regulations (see section 13).

7. Handling and storage

- Advice on safe handling : Do not breathe vapors or spray mist.
Avoid exceeding the given occupational exposure limits (see section 8).
Do not get in eyes, on skin, or on clothing.
For personal protection see section 8.
Persons with a history of skin sensitization problems or



asthma, allergies, chronic or recurrent respiratory disease should not be employed in any process in which this mixture is being used.

Smoking, eating and drinking should be prohibited in the application area.

Take precautionary measures against static discharge.

Open drum carefully as content may be under pressure.

Take necessary action to avoid static electricity discharge (which might cause ignition of organic vapors).

Follow standard hygiene measures when handling chemical products.

Conditions for safe storage : Store in original container.
Store in cool place.
Keep in a well-ventilated place.
Containers which are opened must be carefully resealed and kept upright to prevent leakage.
Observe label precautions.
Store in accordance with local regulations.

Materials to avoid : No data available

8. Exposure controls/personal protection

Component	CAS-No.	Basis **	Value	Exposure limit(s)* / Form of exposure
methyl methacrylate	80-62-6	ACGIH	TWA	50 ppm
		ACGIH	STEL	100 ppm
		OSHA Z-1	TWA	100 ppm 410 mg/m3
		OSHA P0	TWA	100 ppm 410 mg/m3
		CAL PEL	PEL	50 ppm 205 mg/m3
		CAL PEL	STEL	100 ppm 410 mg/m3
Methacrylic acid	79-41-4	ACGIH	TWA	20 ppm
		OSHA P0	TWA	20 ppm 70 mg/m3
		CAL PEL	PEL	20 ppm 70 mg/m3



*The above mentioned values are in accordance with the legislation in effect at the date of the release of this safety data sheet.

****Basis**

ACGIH. Threshold Limit Values (TLV)

OSHA P0. Table Z-1, Limit for Air Contaminant (1989 Vacated Values)

OSHA P1. Permissible Exposure Limits (PEL), Table Z-1, Limit for Air Contaminant

OSHA P2. Permissible Exposure Limits (PEL), Table Z-2

OSHA Z3. Table Z-3, Mineral Dust

Engineering measures : Use of adequate ventilation should be sufficient to control worker exposure to airborne contaminants. If the use of this product generates dust, fumes, gas, vapor or mist, use process enclosures, local exhaust ventilation or other engineering controls to keep worker exposure below any recommended or statutory limits.
The engineering controls also need to keep gas, vapor or dust concentrations below any lower explosive limits.

Personal protective equipment

Respiratory protection : Use a properly fitted NIOSH approved air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary.

The filter class for the respirator must be suitable for the maximum expected contaminant concentration (gas/vapor/aerosol/particulates) that may arise when handling the product. If this concentration is exceeded, self-contained breathing apparatus must be used.

Hand protection
Remarks : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

Eye protection : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary.

Skin and body protection : Choose body protection in relation to its type, to the concentration and amount of dangerous substances, and to the specific work-place.

Hygiene measures : Avoid contact with skin, eyes and clothing.
Wash hands before breaks and immediately after handling the product.
Remove respiratory and skin/eye protection only after vapors have been cleared from the area.
Remove contaminated clothing and protective equipment before entering eating areas.
Wash thoroughly after handling.

**9. Physical and chemical properties**

Appearance	: viscous liquid
Color	: off-white
Odor	: characteristic
Odor Threshold	: No data available
Flash point	: 50 °F (10 °C)
Ignition temperature	: 154 °F (68 °C)
Decomposition temperature	: No data available
Lower explosion limit (Vol%)	: No data available
Upper explosion limit (Vol%)	: No data available
Flammability (solid, gas)	: No data available
Oxidizing properties	: No data available
pH	: Note: not determined
Melting point/range / Freezing point	: No data available
Boiling point/boiling range	: 212 °F (100 °C)
Vapor pressure	: 30 mmHg (40 hpa)
Density	: 1.02 g/cm3
Water solubility	: Note: negligible
Partition coefficient: n- octanol/water	: No data available
Viscosity, dynamic	: No data available
Viscosity, kinematic	: > 20.5 mm2/s at 104 °F (40 °C)
Relative vapor density	: No data available
Evaporation rate	: No data available
Burning rate	: No data available
Volatile organic compounds (VOC) content	: 62 g/l A+B Combined

10. Stability and reactivity



Reactivity	: No dangerous reaction known under conditions of normal use.
Chemical stability	: The product is chemically stable.
Possibility of hazardous reactions	: Stable under recommended storage conditions. Vapors may form explosive mixture with air.
Conditions to avoid	: Heat, flames and sparks.
Incompatible materials	: No data available

11. Toxicological information

Not classified based on available information.

Skin corrosion/irritation

Causes skin irritation.

Serious eye damage/eye irritation

Causes serious eye irritation.

Respiratory or skin sensitization

Skin sensitization: May cause an allergic skin reaction.

Respiratory sensitization: Not classified based on available information.

Germ cell mutagenicity

Not classified based on available information.

Carcinogenicity

Not classified based on available information.

IARC

Not applicable

NTP

Not applicable

Reproductive toxicity

Not classified based on available information.

STOT-single exposure

May cause respiratory irritation.

STOT-repeated exposure

May cause damage to organs through prolonged or repeated exposure.

Reports have associated repeated and prolonged exposure to some of the chemicals in this product with permanent brain, liver, kidney and nervous system damage. Intentional misuse by deliberate concentration and inhalation of vapors may be harmful or fatal.

Once sensitized, a severe allergic reaction may occur when subsequently exposed to very low levels.

Aspiration toxicity

Not classified based on available information.

12. Ecological information

Other information	Do not empty into drains; dispose of this material and its
-------------------	--



container in a safe way.
Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

13. Disposal considerations**Disposal methods**

- Waste from residues : Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements.
- Contaminated packaging : Empty containers should be taken to an approved waste handling site for recycling or disposal.

14. Transport information**DOT**

UN number	1133
Description of the goods	Adhesives
Class	3
Packing group	II
Labels	3
Emergency Response	128
Guidebook Number	

IATA

UN number	1133
Description of the goods	Adhesives
Class	3
Packing group	II
Labels	3
Packing instruction (cargo aircraft)	364
Packing instruction (passenger aircraft)	353
Packing instruction (passenger aircraft)	Y341

IMDG

UN number	1133
Description of the goods	ADHESIVES
Class	3
Packing group	II
Labels	3
EmS Number 1	F-E
EmS Number 2	S-D
Marine pollutant	no



DOT: For Limited Quantity exceptions reference 49 CFR 173.150 (b)
IMDG: For Limited Quantity special provisions reference IMDG Code Chapter 3.4

Special precautions for user

No data available

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable

15. Regulatory information

TSCA list : All chemical substances in this product are either listed on the TSCA Inventory or are in compliance with a TSCA Inventory exemption.

EPCRA - Emergency Planning and Community Right-to-Know**CERCLA Reportable Quantity**

Ingredients	CAS-No.	Component RQ (lbs)
methyl methacrylate	80-62-6	1000

SARA304 Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : Fire Hazard
Acute Health Hazard
Chronic Health Hazard

SARA 302 : No chemicals in this material are subject to the reporting requirements of SARA Title III, Section 302.

SARA 313 : The following components are subject to reporting levels established by SARA Title III, Section 313:
methyl methacrylate 80-62-6 45 - 65 %

Clean Air Act**Ozone-Depletion Potential**

This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

The following chemical(s) are listed as HAP under the U.S. Clean Air Act, Section 12 (40 CFR 61):

methyl methacrylate 80-62-6 45 - 65 %

This product does not contain any chemicals listed under the U.S. Clean Air Act Section 112(r) for Accidental Release Prevention (40 CFR 68.130, Subpart F).

California Prop 65 This product does not contain any chemicals known to the State



of California to cause cancer, birth, or any other reproductive defects.

16. Other information

HMIS Classification

Health	*	2
Flammability		3
Physical Hazard		0
Personal Protection		X

Caution: HMIS® rating is based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. Although HMIS® rating is not required on SDSs under 29 CFR 1910.1200, the preparer may choose to provide them. HMIS® rating is to be used with a fully implemented HMIS® program. HMIS® is a registered mark of the National Paint & Coatings Association (NPCA). Please note HMIS® attempts to convey full health warning information to all employees.

Notes to Reader

The information contained in this Safety Data Sheet applies only to the actual Sika Corporation ("Sika") product identified and described herein. This information is not intended to address, nor does it address the use or application of the identified Sika product in combination with any other material, product or process. All of the information set forth herein is based on technical data regarding the identified product that Sika believes to be reliable as of the date hereof. Prior to each use of any Sika product, the user must always read and follow the warnings and instructions on the product's current Product Data Sheet, product label and Safety Data Sheet for each Sika product, which are available at web site and/or telephone number listed in Section 1 of this SDS.

SIKA MAKES NO WARRANTIES EXPRESS OR IMPLIED AND ASSUMES NO LIABILITY ARISING FROM THIS INFORMATION OR ITS USE. SIKA SHALL NOT BE LIABLE UNDER ANY LEGAL THEORY FOR SPECIAL OR CONSEQUENTIAL DAMAGES AND SHALL NOT BE RESPONSIBLE FOR THE USE OF THIS PRODUCT IN A MANNER TO INFRINGE ON ANY PATENT OR ANY OTHER INTELLECTUAL PROPERTY RIGHTS HELD BY OTHERS.

All sales of Sika products are subject to its current terms and conditions of sale available at www.sikausa.com or 201-933-8800.

Revision Date 09/23/2016

Material number: 530424