

# SAFETY DATA SHEET

Issuing Date 5/01/2015



The supplier identified below generated this SDS using the UL SDS template. UL did not test, certify, or approve the substance described in this SDS, and all information in this SDS was provided by the supplier or was reproduced from publically available regulatory data sources. UL makes no representations or warranties regarding the completeness or accuracy of the information in this SDS and disclaims all liability in connection with the use of this information or the substance described in this SDS. The layout, appearance and format of this SDS is © 2014 UL LLC. All rights reserved.

## 1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

### Product identifier

**Product Name** Terro Flea Trap Refill Glue Boards

### Other means of identification

**Synonyms** None

### Recommended use of the chemical and restrictions on use

**Recommended Use** Trap and/or Bait Station

**Uses advised against** No information available

### Details of the supplier of the safety data sheet

**Supplier Name** Woodstream Corp.  
**Supplier Address** 69 North Locust St.  
Litz  
PA  
17543  
US  
**Supplier Phone Number** Phone:(717) 626-2125  
Fax:(717) 626-1912  
Contact Phone(717) 626-2125  
**Supplier Email** mandre@woodstream.com  
**Emergency telephone number**

## 2. HAZARDS IDENTIFICATION

### Classification

This chemical is considered hazardous by the 2012 OSHA Hazard Communication Standard (29 CFR 1910.1200)

Skin sensitization	Category 1
--------------------	------------

### GHS Label elements, including precautionary statements

#### Emergency Overview

Signal word	Warning
-------------	---------



**Hazard Statements**

May cause an allergic skin reaction



**Appearance** Solid

**Physical State** Solid

**Odor** Odorless

**Precautionary Statements - Prevention**

Avoid breathing dust/fume/gas/mist/vapors/spray  
 Contaminated work clothing should not be allowed out of the workplace  
 Wear protective gloves

**Precautionary Statements - Response**

Specific treatment (see supplemental first aid instructions on this label)

**Skin**

IF ON SKIN: Wash with plenty of soap and water  
 If skin irritation or rash occurs: Get medical advice/attention  
 Wash contaminated clothing before reuse

**Precautionary Statements - Storage**

None

**Precautionary Statements - Disposal**

Dispose of contents/container to an approved waste disposal plant

**Hazards not otherwise classified (HNOC)**

Not applicable

**Unknown Toxicity**

70% of the mixture consists of ingredient(s) of unknown toxicity

**Other information**

Repeated or prolonged skin contact may cause allergic reactions with susceptible persons

**Interactions with Other Chemicals**

No information available.

**3. COMPOSITION/INFORMATION ON INGREDIENTS**

Chemical Name	CAS No.	Weight-%	Trade Secret
Paraffin oils	8012-95-1	15 - 40	*
Rubber	9006-04-6	10 - 30	*

\*The exact percentage (concentration) of composition has been withheld as a trade secret



## 4. FIRST AID MEASURES

### First aid measures

<b>General Advice</b>	Show this safety data sheet to the doctor in attendance.
<b>Eye Contact</b>	Rinse thoroughly with plenty of water, also under the eyelids. If symptoms persist, call a physician.
<b>Skin Contact</b>	Wash with soap and water. May cause an allergic skin reaction. In the case of skin irritation or allergic reactions see a physician.
<b>Inhalation</b>	Remove to fresh air.
<b>Ingestion</b>	Rinse mouth immediately and drink plenty of water. Never give anything by mouth to an unconscious person.

### Most important symptoms and effects, both acute and delayed

**Most Important Symptoms and Effects** Itching. Rashes. Hives.

### Indication of any immediate medical attention and special treatment needed

**Notes to Physician** May cause sensitization of susceptible persons. Treat symptomatically.

## 5. FIRE-FIGHTING MEASURES

### Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

### Unsuitable extinguishing media

CAUTION: Use of water spray when fighting fire may be inefficient.

### Specific Hazards Arising from the Chemical

Product is or contains a sensitizer. May cause sensitization by skin contact.

**Uniform Fire Code** Sensitizer: Solid

### Hazardous Combustion Products

Carbon oxides.

### Explosion Data

**Sensitivity to Mechanical Impact** No.

**Sensitivity to Static Discharge** No.

### Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

## 6. ACCIDENTAL RELEASE MEASURES

### Personal precautions, protective equipment and emergency procedures

**Personal Precautions**                      Avoid contact with eyes. Use personal protective equipment as required.

**Other Information**                        Refer to protective measures listed in Sections 7 and 8.

### Environmental Precautions

**Environmental Precautions**            Refer to protective measures listed in Sections 7 and 8. Prevent further leakage or spillage if safe to do so.

### Methods and material for containment and cleaning up

**Methods for Containment**                Prevent further leakage or spillage if safe to do so.

**Methods for cleaning up**                Pick up and transfer to properly labeled containers.

## 7. HANDLING AND STORAGE

### Precautions for safe handling

**Handling**                                    Handle in accordance with good industrial hygiene and safety practice. Avoid contact with eyes. Do not eat, drink or smoke when using this product. Take off contaminated clothing and wash before reuse.

### Conditions for safe storage, including any incompatibilities

**Storage**                                      Keep containers tightly closed in a dry, cool and well-ventilated place. Store locked up. Keep out of the reach of children.

**Incompatible Products**                None known based on information supplied.

## 8. EXPOSURE CONTROLS/PERSONAL PROTECTION

### Control parameters

### Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Paraffin oils 8012-95-1	TWA: 5 mg/m <sup>3</sup> inhalable fraction excluding metal working fluids, highly & severely refined TWA: 5 mg/m <sup>3</sup> inhalable fraction excluding metal working fluids	TWA: 5 mg/m <sup>3</sup> (vacated) TWA: 5 mg/m <sup>3</sup>	
Rubber 9006-04-6	TWA: 0.0001 mg/m <sup>3</sup> inhalable allergenic proteins inhalable fraction S*	-	

*ACGIH TLV: American Conference of Governmental Industrial Hygienists - Threshold Limit Value OSHA PEL: Occupational Safety and Health Administration - Permissible Exposure Limits Immediately Dangerous to Life or Health*

**Other Exposure Guidelines**            See section 15 for national exposure control parameters



**Appropriate engineering controls**

**Engineering Measures**                      Showers  
    Eyewash stations  
    Ventilation systems

**Individual protection measures, such as personal protective equipment**

**Eye/Face Protection**                      Wear safety glasses with side shields (or goggles).

**Skin and Body Protection**                Wear protective gloves and protective clothing.

**Respiratory Protection**                 No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.

**Hygiene Measures**                        Handle in accordance with good industrial hygiene and safety practice. Take off contaminated clothing and wash before reuse. Avoid contact with skin, eyes or clothing. Wear suitable gloves and eye/face protection. Do not eat, drink or smoke when using this product.

**9. PHYSICAL AND CHEMICAL PROPERTIES**

**Physical and Chemical Properties**

<b>Physical State</b>	Solid	<b>Odor</b>	Odorless
<b>Appearance</b>	Solid	<b>Odor Threshold</b>	No information available
<b>Color</b>	No information available		

<u>Property</u>	<u>Values</u>	<u>Remarks/ Method</u>
<b>pH</b>	No data available	None known
<b>Melting / freezing point</b>	No data available	None known
<b>Boiling point / boiling range</b>	No data available	None known
<b>Flash Point</b>	No data available	None known
<b>Evaporation Rate</b>	No data available	None known
<b>Flammability (solid, gas)</b>	No data available	None known
<b>Flammability Limit in Air</b>		
<b>Upper flammability limit</b>	No data available	
<b>Lower flammability limit</b>	No data available	
<b>Vapor pressure</b>	No data available	None known
<b>Vapor density</b>	No data available	None known
<b>Specific Gravity</b>	No data available	None known
<b>Water Solubility</b>	Insoluble	None known
<b>Solubility in other solvents</b>	No data available	None known
<b>Partition coefficient: n-octanol/water</b>	No data available	None known
<b>Autoignition temperature</b>	No data available	None known
<b>Decomposition temperature</b>	No data available	None known
<b>Kinematic viscosity</b>	No data available	None known
<b>Dynamic viscosity</b>	No data available	None known
<b>Explosive properties</b>	No data available	
<b>Oxidizing Properties</b>	No data available	

**Other Information**

<b>Softening Point</b>	No data available
<b>VOC Content (%)</b>	No data available
<b>Particle Size</b>	No data available
<b>Particle Size Distribution</b>	





**Carcinogenicity**

The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical Name	ACGIH	IARC	NTP	OSHA
Paraffin oils 8012-95-1	A2	Group 3		X

*ACGIH (American Conference of Governmental Industrial Hygienists)  
 A2 - Suspected Human Carcinogen  
 IARC (International Agency for Research on Cancer)  
 Group 3 - Not Classifiable as to Carcinogenicity in Humans  
 OSHA (Occupational Safety and Health Administration of the US Department of Labor)  
 X - Present*

- Reproductive Toxicity** No information available.
- STOT - single exposure** No information available.
- STOT - repeated exposure** No information available.
- Chronic Toxicity** Repeated contact may cause allergic reactions in very susceptible persons.
- Target Organ Effects** Skin. Respiratory system. Eyes. Lungs.
- Aspiration Hazard** No information available.

**Numerical measures of toxicity Product Information**

The following values are calculated based on chapter 3.1 of the GHS document  
 Not applicable

**12. ECOLOGICAL INFORMATION**

**Ecotoxicity**  
 The environmental impact of this product has not been fully investigated.

**Persistence and Degradability**  
 No information available.

**Bioaccumulation**  
 No information available

**Other adverse effects**  
 No information available.



**13. DISPOSAL CONSIDERATIONS**

**Waste treatment methods**

**Disposal methods** This material, as supplied, is not a hazardous waste according to Federal regulations (40 CFR 261). This material could become a hazardous waste if it is mixed with or otherwise comes in contact with a hazardous waste, if chemical additions are made to this material, or if the material is processed or otherwise altered. Consult 40 CFR 261 to determine whether the altered material is a hazardous waste. Consult the appropriate state, regional, or local regulations for additional requirements.

**Contaminated Packaging** Dispose of contents/containers in accordance with local regulations.

**California Hazardous Waste Codes** 331

**14. TRANSPORT INFORMATION**

**DOT**  
**Proper Shipping Name** NOT REGULATED  
**Hazard Class** NON REGULATED  
 N/A

**TDG** Not regulated

**MEX** Not regulated

**ICAO** Not regulated

**IATA**  
**Proper Shipping Name** Not regulated  
**Hazard Class** NON REGULATED  
 N/A

**IMDG/IMO**  
**Hazard Class** Not regulated  
 N/A

**RID** Not regulated

**ADR** Not regulated

**ADN** Not regulated

**15. REGULATORY INFORMATION**

**International Inventories**

**TSCA** Complies  
**DSL** All components are listed either on the DSL or NDSL.

**TSCA** - United States Toxic Substances Control Act Section 8(b) Inventory  
**DSL/NDSL** - Canadian Domestic Substances List/Non-Domestic Substances List

**US Federal Regulations**



**SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

**SARA 311/312 Hazard Categories**

<b>Acute Health Hazard</b>	Yes
<b>Chronic Health Hazard</b>	No
<b>Fire Hazard</b>	No
<b>Sudden release of pressure hazard</b>	No
<b>Reactive Hazard</b>	No

**CWA (Clean Water Act)**

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

**CERCLA**

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

**US State Regulations**

**California Proposition 65**

This product does not contain any Proposition 65 chemicals.

**U.S. State Right-to-Know Regulations**

Chemical Name	New Jersey	Massachusetts	Pennsylvania	Rhode Island	Illinois
Mineral Oils RR-03885-7	X		X		X

**International Regulations**

**Mexico**

**National occupational exposure limits**

Component	Carcinogen Status	Exposure Limits
Paraffin oils 8012-95-1 ( 15 - 40 )		Mexico: TWA 5 mg/m <sup>3</sup> Mexico: STEL 10 mg/m <sup>3</sup>

*Mexico - Occupational Exposure Limits - Carcinogens*

**Canada**

**WHMIS Hazard Class**

D2B - Toxic materials



**16. OTHER INFORMATION**

<b>NFPA</b>	<b>Health Hazards 2</b>	<b>Flammability 0</b>	<b>Instability 0</b>	<b>Physical and Chemical Hazards - Personal Protection</b>
<b>HMIS</b>	<b>Health Hazards 2</b>	<b>Flammability 0</b>	<b>Physical Hazard 0</b>	

X



<b>Prepared By</b>	Product Stewardship 23 British American Blvd. Latham, NY 12110 1-800-572-6501
<b>Revision Date</b>	17-Sep-2013
<b>Revision Note</b>	No information available

**Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

**End of Safety Data Sheet**