

**1. Identification**

Product name : Sikadur®-42 Grout Pak LE Part B

Supplier : Sika Corporation
201 Polito Avenue
Lyndhurst, NJ 07071
USA
www.sikausa.com

Telephone : (201) 933-8800

Telefax : (201) 804-1076

E-mail address : ehs@sika-corp.com

Emergency telephone : CHEMTREC: 800-424-9300
INTERNATIONAL: 703-527-3887

Recommended use of the chemical and restrictions on use : For further information, refer to product data sheet.

2. Hazards identification**GHS Classification**

Acute toxicity, Category 4 (Oral)
Skin corrosion, Category 1B
Serious eye damage, Category 1
Skin sensitization, Category 1

H302: Harmful if swallowed.
H314: Causes severe skin burns and eye damage.
H318: Causes serious eye damage.
H317: May cause an allergic skin reaction.

GHS label elements

Hazard pictograms :



Signal Word : Danger

Hazard Statements : H302 Harmful if swallowed.
H314 Causes severe skin burns and eye damage.
H317 May cause an allergic skin reaction.

Precautionary Statements : **Prevention:**
P260 Do not breathe dusts or mists.
P270 Do not eat, drink or smoke when using this product.
P272 Contaminated work clothing must not be allowed out of the workplace.
P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
Response:



P301 + P312 IF SWALLOWED: Call a POISON CENTER/doctor if you feel unwell.
P301 + P330 + P331 IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.
P303 + P361 + P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.
P304 + P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.
P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P310 Immediately call a POISON CENTER/doctor.
P333 + P313 If skin irritation or rash occurs: Get medical advice/ attention.
P363 Wash contaminated clothing before reuse.

Storage:

P405 Store locked up.

Disposal:

P501 Dispose of contents/ container to an approved waste disposal plant.

Warning

: Reports have associated repeated and prolonged exposure to some of the chemicals in this product with permanent brain, liver, kidney and nervous system damage. Intentional misuse by deliberate concentration and inhalation of vapors may be harmful or fatal.

See Section 11 for more detailed information on health effects and symptoms.

There are no hazards not otherwise classified that have been identified during the classification process.

There are no ingredients with unknown acute toxicity used in a mixture at a concentration $\geq 1\%$.

3. Composition/information on ingredients**Hazardous ingredients**

Chemical name	CAS-No.	Concentration (%)
Isophoronediamine	2855-13-2	≥ 25 - < 50 %
Tall oil acids, triethylenetetramine condensate	68919-79-9	≥ 25 - < 50 %
Benzyl alcohol	100-51-6	≥ 20 - < 25 %
triethylenetetramine	112-24-3	≥ 3 - < 5 %

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment and hence require reporting in this section.

4. First aid measures

If inhaled

: Move to fresh air.
Consult a physician after significant exposure.



In case of skin contact	: Take off contaminated clothing and shoes immediately. Wash off with soap and plenty of water. Immediate medical treatment is necessary as untreated wounds from corrosion of the skin heal slowly and with difficulty.
In case of eye contact	: Small amounts splashed into eyes can cause irreversible tissue damage and blindness. In the case of contact with eyes, rinse immediately with plenty of water and seek medical advice. Continue rinsing eyes during transport to hospital. Remove contact lenses. Keep eye wide open while rinsing.
If swallowed	: Clean mouth with water and drink afterwards plenty of water. Do not induce vomiting without medical advice. Do not give milk or alcoholic beverages. Never give anything by mouth to an unconscious person. Take victim immediately to hospital.
Most important symptoms and effects, both acute and delayed	: Health injuries may be delayed. corrosive effects sensitizing effects Gastrointestinal discomfort Allergic reactions Dermatitis See Section 11 for more detailed information on health effects and symptoms. Harmful if swallowed. May cause an allergic skin reaction. Causes serious eye damage. Causes severe burns.
Protection of first-aiders	: Move out of dangerous area. Consult a physician. Show this material safety data sheet to the doctor in attendance.
Notes to physician	: Treat symptomatically.

5. Fire-fighting measures

Suitable extinguishing media	: Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Specific extinguishing methods	: Collect contaminated fire extinguishing water separately. This must not be discharged into drains. Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.
Special protective equipment for fire-fighters	: In the event of fire, wear self-contained breathing apparatus.



6. Accidental release measures

- | | | |
|---|---|---|
| Personal precautions,
protective equipment and
emergency procedures | : | Use personal protective equipment.
Deny access to unprotected persons. |
| Environmental precautions | : | Do not flush into surface water or sanitary sewer system.
If the product contaminates rivers and lakes or drains inform
respective authorities.
Local authorities should be advised if significant spillages
cannot be contained. |
| Methods and materials for
containment and cleaning up | : | Soak up with inert absorbent material (e.g. sand, silica gel,
acid binder, universal binder, sawdust).
Keep in suitable, closed containers for disposal. |

7. Handling and storage

- | | | |
|-----------------------------|---|---|
| Advice on safe handling | : | Avoid exceeding the given occupational exposure limits (see
section 8).
Do not get in eyes, on skin, or on clothing.
For personal protection see section 8.
Persons with a history of skin sensitization problems or
asthma, allergies, chronic or recurrent respiratory disease
should not be employed in any process in which this mixture is
being used.
Smoking, eating and drinking should be prohibited in the
application area.
Follow standard hygiene measures when handling chemical
products. |
| Conditions for safe storage | : | Store in original container.
Keep container tightly closed in a dry and well-ventilated
place.
Containers which are opened must be carefully resealed and
kept upright to prevent leakage.
Observe label precautions.
Store in accordance with local regulations. |
| Materials to avoid | : | No data available |

8. Exposure controls/personal protection

Contains no substances with occupational exposure limit values.

- | | | |
|-----------------------------|---|---|
| Engineering measures | : | Use of adequate ventilation should be sufficient to control
worker exposure to airborne contaminants. If the use of this
product generates dust, fumes, gas, vapor or mist, use
process enclosures, local exhaust ventilation or other
engineering controls to keep worker exposure below any
recommended or statutory limits. |
|-----------------------------|---|---|

Personal protective equipment



Respiratory protection	: Use a properly fitted NIOSH approved air-purifying or air-fed respirator complying with an approved standard if a risk assessment indicates this is necessary. The filter class for the respirator must be suitable for the maximum expected contaminant concentration (gas/vapor/aerosol/particulates) that may arise when handling the product. If this concentration is exceeded, self-contained breathing apparatus must be used.
Hand protection Remarks	: Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.
Eye protection	: Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary.
Skin and body protection	: Choose body protection in relation to its type, to the concentration and amount of dangerous substances, and to the specific work-place.
Hygiene measures	: Avoid contact with skin, eyes and clothing. Wash hands before breaks and immediately after handling the product. Remove contaminated clothing and protective equipment before entering eating areas. Wash thoroughly after handling.

9. Physical and chemical properties

Appearance	: liquid
Color	: amber
Odor	: amine-like
Odor Threshold	: No data available
Flash point	: > 212 °F (> 100 °C)
Ignition temperature	: No data available
Decomposition temperature	: No data available
Lower explosion limit (Vol%)	: No data available
Upper explosion limit (Vol%)	: No data available
Flammability (solid, gas)	: No data available
Oxidizing properties	: No data available
pH	: No data available

**Sikadur®-42 Grout Pak LE Part B**

Revision Date 08/31/2017

Print Date 08/31/2017

Melting point/range /	:	No data available
Freezing point	:	
Boiling point/boiling range	:	No data available
Vapor pressure	:	0.05 mmHg (0.07 hpa)
Density	:	ca.0.98 g/cm ³ at 73 °F (23 °C)
Water solubility	:	Note: soluble
Partition coefficient: n- octanol/water	:	No data available
Viscosity, dynamic	:	No data available
Viscosity, kinematic	:	> 20.5 mm ² /s at 104 °F (40 °C)
Relative vapor density	:	No data available
Evaporation rate	:	No data available
Burning rate	:	No data available
Volatile organic compounds (VOC) content	:	22 g/l A+B+C Combined

10. Stability and reactivity

Reactivity	:	No dangerous reaction known under conditions of normal use.
Chemical stability	:	The product is chemically stable.
Possibility of hazardous reactions	:	Stable under recommended storage conditions.
Conditions to avoid	:	No data available
Incompatible materials	:	No data available

11. Toxicological information**Acute toxicity**

Harmful if swallowed.

Ingredients:**Isophoronediamine:**

Acute oral toxicity : LD50 Oral (Rat): 1,030 mg/kg

Acute inhalation toxicity : LC50 (Rat): > 5.01 mg/l
Exposure time: 4 h
Test atmosphere: dust/mist



Acute dermal toxicity : LD50 Dermal (Rabbit): > 2,000 mg/kg

Benzyl alcohol:

Acute oral toxicity : LD50 Oral (Rat): 1,620 mg/kg

Acute inhalation toxicity : LC50 (Rat): > 4.178 mg/l
Exposure time: 4 h
Test atmosphere: dust/mist

triethylenetetramine:

Acute oral toxicity : LD50 Oral (Rat): 1,716 mg/kg

Acute dermal toxicity : LD50 Dermal (Rabbit): 1,465 mg/kg

Skin corrosion/irritation

Causes severe burns.

Serious eye damage/eye irritation

Causes serious eye damage.

Respiratory or skin sensitization

Skin sensitization: May cause an allergic skin reaction.

Respiratory sensitization: Not classified based on available information.

Ingredients:

Isophoronediamine:

Assessment: The product is a skin sensitizer, sub-category 1A.

Result: The product is a skin sensitizer, sub-category 1A.

Germ cell mutagenicity

Not classified based on available information.

Reproductive toxicity

Not classified based on available information.

STOT-single exposure

Not classified based on available information.

STOT-repeated exposure

Once sensitized, a severe allergic reaction may occur when subsequently exposed to very low levels.

Reports have associated repeated and prolonged exposure to some of the chemicals in this product with permanent brain, liver, kidney and nervous system damage. Intentional misuse by deliberate concentration and inhalation of vapors may be harmful or fatal.

Aspiration toxicity

Not classified based on available information.

Carcinogenicity

Not classified based on available information.

IARC Not applicable

NTP Not applicable



12. Ecological information

Other information Do not empty into drains; dispose of this material and its container in a safe way.
Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

Component:

Isophoronediamine	2855-13-2	<u>Toxicity to algae:</u> ErC50 Species: Desmodesmus subspicatus (green algae) Dose: > 10 - 100 mg/l Exposure time: 72 h
Benzyl alcohol	100-51-6	<u>Toxicity to fish:</u> LC50 Species: Fish Dose: > 100 mg/l Exposure time: 96 h <u>Toxicity to daphnia and other aquatic invertebrates:</u> EC50 Species: Daphnia magna (Water flea) Dose: > 100 mg/l Exposure time: 48 h
triethylenetetramine	112-24-3	<u>Toxicity to fish:</u> LC50 Species: Pimephales promelas (fathead minnow) Dose: > 100 mg/l Exposure time: 96 h <u>Toxicity to daphnia and other aquatic invertebrates:</u> EC50 Species: Daphnia Dose: 10 - 100 mg/l Exposure time: 48 h <u>Toxicity to algae:</u> EC50 Species: Pseudokirchneriella subcapitata (green algae) Dose: 10 - 100 mg/l Exposure time: 72 h

13. Disposal considerations

Disposal methods

- Waste from residues : Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements.
- Contaminated packaging : Empty containers should be taken to an approved waste handling site for recycling or disposal.



14. Transport information**DOT**

UN number	3267
Description of the goods	Corrosive liquid, basic, organic, n.o.s. (Isophoronediamine, 3,6-diazaoctanethylenediamin)
Class	8
Packing group	II
Labels	8
Emergency Response	153
Guidebook Number	

IATA

UN number	3267
Description of the goods	Corrosive liquid, basic, organic, n.o.s. (Isophoronediamine, 3,6-diazaoctanethylenediamin)
Class	8
Packing group	II
Labels	8
Packing instruction (cargo aircraft)	855
Packing instruction (passenger aircraft)	851
Packing instruction (passenger aircraft)	Y840

IMDG

UN number	3267
Description of the goods	CORROSIVE LIQUID, BASIC, ORGANIC, N.O.S. (Isophoronediamine, 3,6-diazaoctanethylenediamin)
Class	8
Packing group	II
Labels	8
EmS Number 1	F-A
EmS Number 2	S-B
Marine pollutant	no

IMDG: For Limited Quantity special provisions reference IMDG Code Chapter 3.4

DOT: For Limited Quantity exceptions reference 49 CFR 173.154 (b)

Special precautions for user

No data available

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable

15. Regulatory information



TSCA list : All chemical substances in this product are either listed on the TSCA Inventory or are in compliance with a TSCA Inventory exemption.

EPCRA - Emergency Planning and Community Right-to-Know

CERCLA Reportable Quantity

This material does not contain any components with a CERCLA RQ.

SARA304 Reportable Quantity

This material does not contain any components with a section 304 EHS RQ.

SARA 311/312 Hazards : Chronic Health Hazard
Acute toxicity (any route of exposure)
Skin corrosion or irritation
Serious eye damage or eye irritation
Respiratory or skin sensitization

SARA 302 : This material does not contain any components with a section 302 EHS TPQ.

SARA 313 : This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

Clean Air Act

Ozone-Depletion Potential

This product neither contains, nor was manufactured with a Class I or Class II ODS as defined by the U.S. Clean Air Act Section 602 (40 CFR 82, Subpt. A, App.A + B).

This product does not contain any hazardous air pollutants (HAP), as defined by the U.S. Clean Air Act Section 112 (40 CFR 61).

This product does not contain any chemicals listed under the U.S. Clean Air Act Section 112(r) for Accidental Release Prevention (40 CFR 68.130, Subpart F).

California Prop 65 This product does not contain any chemicals known to the State of California to cause cancer, birth, or any other reproductive defects.

16. Other information

HMIS Classification

Health	*	3
Flammability		1
Physical Hazard		0
Personal Protection		X

Sikadur®-42 Grout Pak LE Part B



Revision Date 08/31/2017

Print Date 08/31/2017

Caution: HMIS® rating is based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. Although HMIS® rating is not required on SDSs under 29 CFR 1910.1200, the preparer may choose to provide them. HMIS® rating is to be used with a fully implemented HMIS® program. HMIS® is a registered mark of the National Paint & Coatings Association (NPCA). Please note HMIS® attempts to convey full health warning information to all employees.

Notes to Reader

The information contained in this Safety Data Sheet applies only to the actual Sika Corporation ("Sika") product identified and described herein. This information is not intended to address, nor does it address the use or application of the identified Sika product in combination with any other material, product or process. All of the information set forth herein is based on technical data regarding the identified product that Sika believes to be reliable as of the date hereof. Prior to each use of any Sika product, the user must always read and follow the warnings and instructions on the product's current Product Data Sheet, product label and Safety Data Sheet for each Sika product, which are available at web site and/or telephone number listed in Section 1 of this SDS.

SIKA MAKES NO WARRANTIES EXPRESS OR IMPLIED AND ASSUMES NO LIABILITY ARISING FROM THIS INFORMATION OR ITS USE. SIKA SHALL NOT BE LIABLE UNDER ANY LEGAL THEORY FOR SPECIAL OR CONSEQUENTIAL DAMAGES AND SHALL NOT BE RESPONSIBLE FOR THE USE OF THIS PRODUCT IN A MANNER TO INFRINGE ON ANY PATENT OR ANY OTHER INTELLECTUAL PROPERTY RIGHTS HELD BY OTHERS.

All sales of Sika products are subject to its current terms and conditions of sale available at www.sikausa.com or 201-933-8800.

Revision Date 08/31/2017

Material number: 506207