

MasterEmaco P 130 PART A

Version 1.0 Revision Date: 09/03/2020 SDS Number: 000000261566 Date of last issue: -
Date of first issue: 09/03/2020

SECTION 1. IDENTIFICATION

Product name : MasterEmaco P 130 PART A
Product code : 000000000051687178 000000000051687178

Manufacturer or supplier's details

Company name of supplier : Master Builders-Construction Systems
US, LLC
Address : 23700 CHAGRIN BLVD
Beachwood OH 44122
Emergency telephone : ChemTel: +1-813-248-0585

Recommended use of the chemical and restrictions on use

Recommended use : Product for construction chemicals
Restrictions on use : Reserved for industrial and professional use.

SECTION 2. HAZARDS IDENTIFICATION**GHS classification in accordance with 29 CFR 1910.1200**

Skin corrosion/irritation : 2
Serious eye damage/eye irritation : Category 2A
Skin sensitization : Category 1
Short-term (acute) aquatic hazard : 2
Long-term (chronic) aquatic hazard : 2

GHS label elements

Hazard pictograms : 

Signal Word : Warning

Hazard Statements : H319 Causes serious eye irritation.
H315 Causes skin irritation.
H317 May cause an allergic skin reaction.
H401 Toxic to aquatic life.
H411 Toxic to aquatic life with long lasting effects.

MasterEmaco P 130 PART A

Version 1.0 Revision Date: 09/03/2020 SDS Number: 000000261566 Date of last issue: -
Date of first issue: 09/03/2020

Precautionary Statements : **Prevention:**
 P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.
 P261 Avoid breathing dust/ fume/ gas/ mist/ vapours/ spray.
 P273 Avoid release to the environment.
 P272 Contaminated work clothing should not be allowed out of the workplace.
 P264 Wash face, hands and any exposed skin thoroughly after handling.

Response:
 P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
 P303 + P352 IF ON SKIN (or hair): Wash with plenty of soap and water.
 P333 + P311 If skin irritation or rash occurs: Call a POISON CENTER or doctor/physician.
 P332 + P313 If skin irritation occurs: Get medical advice/ attention.
 P362 + P364 Take off contaminated clothing and wash it before reuse.
 P391 Collect spillage.
 P337 + P311 If eye irritation persists: Call a POISON CENTER or doctor/physician.

Disposal:
 P501 Dispose of contents/container to appropriate hazardous waste collection point.

Other hazards

No data available.

SECTION 3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical nature : No data available.

Components

Chemical name	CAS-No.	Concentration (% w/w)
Oxirane, [[[2-ethylhexyl)oxy]methyl]-	2461-15-6	>= 10 - < 15
Reaction product: bisphenol-A-(epichlorhydrin)-Epoxy resin (number average molecular weight <= 700)	25068-38-6	>= 75 - <= 100

SECTION 4. FIRST AID MEASURES

General advice : Remove contaminated clothing.

Move out of dangerous area.
 Show this material safety data sheet to the doctor in attendance.
 Do not leave the victim unattended.

MasterEmaco P 130 PART A

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	09/03/2020	000000261566	Date of first issue: 09/03/2020

- If inhaled : Keep patient calm, remove to fresh air, seek medical attention.
If unconscious, place in recovery position and seek medical advice.
If symptoms persist, call a physician.
- In case of skin contact : Wash thoroughly with soap and water
If skin irritation persists, call a physician.
If on skin, rinse well with water.
If on clothes, remove clothes.
- In case of eye contact : Wash affected eyes for at least 15 minutes under running water with eyelids held open, consult an eye specialist.
Immediately flush eye(s) with plenty of water.
Remove contact lenses.
Protect unharmed eye.
Keep eye wide open while rinsing.
If eye irritation persists, consult a specialist.
- If swallowed : Immediately rinse mouth and then drink 200-300 ml of water, seek medical attention.
Keep respiratory tract clear.
Do not give milk or alcoholic beverages.
Never give anything by mouth to an unconscious person.
If symptoms persist, call a physician.
- Most important symptoms and effects, both acute and delayed : Causes skin irritation.
May cause an allergic skin reaction.
Causes serious eye irritation.
- Notes to physician : Treat symptomatically.

SECTION 5. FIRE-FIGHTING MEASURES

- Suitable extinguishing media : Water spray
Foam
Dry powder
Carbon dioxide (CO₂)
- Unsuitable extinguishing media : High volume water jet
- Specific hazards during fire fighting : Do not allow run-off from fire fighting to enter drains or water courses.
- Further information : Collect contaminated fire extinguishing water separately. This must not be discharged into drains.
Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.

MasterEmaco P 130 PART A

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	09/03/2020	000000261566	Date of first issue: 09/03/2020

Special protective equipment for fire-fighters : Wear self-contained breathing apparatus for firefighting if necessary.

SECTION 6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures : Use personal protective equipment.

Environmental precautions : Prevent product from entering drains. Prevent further leakage or spillage if safe to do so. If the product contaminates rivers and lakes or drains inform respective authorities.

Methods and materials for containment and cleaning up : Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust). Keep in suitable, closed containers for disposal.

SECTION 7. HANDLING AND STORAGE

Advice on protection against fire and explosion : Product is not explosive.

Normal measures for preventive fire protection.

Advice on safe handling : Do not breathe vapors/dust. Avoid exposure - obtain special instructions before use. Avoid contact with skin and eyes. For personal protection see section 8. Smoking, eating and drinking should be prohibited in the application area. Dispose of rinse water in accordance with local and national regulations. Persons susceptible to skin sensitization problems or asthma, allergies, chronic or recurrent respiratory disease should not be employed in any process in which this mixture is being used.

Conditions for safe storage : Keep container tightly closed in a dry and well-ventilated place. Containers which are opened must be carefully resealed and kept upright to prevent leakage. Electrical installations / working materials must comply with the technological safety standards.

Further information on storage conditions : Keep only in the original container in a cool, dry, well-ventilated place away from ignition sources, heat or flame. Protect from direct sunlight.

Materials to avoid : Observe VCI storage rules.

Recommended storage temperature : 41 °F / 5 °C

MasterEmaco P 130 PART A

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	09/03/2020	000000261566	Date of first issue: 09/03/2020

perature

Further information on storage stability : Minimum storage temperature:

SECTION 8. EXPOSURE CONTROLS/PERSONAL PROTECTION
Ingredients with workplace control parameters

Contains no substances with occupational exposure limit values.

Engineering measures : No applicable information available.

Personal protective equipment

Respiratory protection : No applicable information available.

Hand protection

Remarks : No applicable information available.
The suitability for a specific workplace should be discussed with the producers of the protective gloves.

Eye protection : No applicable information available.
Eye wash bottle with pure water
Tightly fitting safety goggles
Wear face-shield and protective suit for abnormal processing problems.

Skin and body protection : No applicable information available.
Impervious clothing
Choose body protection according to the amount and concentration of the dangerous substance at the work place.

Protective measures : Do not inhale gases/vapours/aerosols.
Avoid contact with the skin, eyes and clothing.
Avoid exposure - obtain special instructions before use.
Handle in accordance with good building materials hygiene and safety practice.
Wearing of closed work clothing is recommended.

Hygiene measures : When using do not eat or drink.
When using do not smoke.
Wash hands before breaks and at the end of workday.

SECTION 9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance : liquid

Color : No data available.

MasterEmaco P 130 PART A

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	09/03/2020	000000261566	Date of first issue: 09/03/2020

Odor	:	product specific
Odor Threshold	:	No data available
pH	:	neutral to slightly alkaline
Melting point	:	No applicable information available.
Boiling point	:	No data available
Flash point	:	> 200.01 °F / > 93.34 °C > 200 °F / > 93 °C
Evaporation rate	:	No applicable information available.
Flammability (solid, gas)	:	not highly flammable Method: derived from flash point
Upper explosion limit / Upper flammability limit	:	No applicable information available.
Lower explosion limit / Lower flammability limit	:	No applicable information available.
Relative vapor density	:	No applicable information available.
Relative density	:	No applicable information available.
Density	:	1.15 g/cm ³ (68 °F / 20 °C)
Bulk density	:	not applicable
Solubility(ies)		
Water solubility	:	No data available
Solubility in other solvents	:	No applicable information available.
Partition coefficient: n-octanol/water	:	No applicable information available.
Autoignition temperature	:	No data available
Decomposition temperature	:	No decomposition if stored and handled as prescribed/indicated.
Viscosity		
Viscosity, dynamic	:	No applicable information available.
Viscosity, kinematic	:	No applicable information available.
Explosive properties	:	Not explosive Not explosive

MasterEmaco P 130 PART A

Version 1.0 Revision Date: 09/03/2020 SDS Number: 000000261566 Date of last issue: -
Date of first issue: 09/03/2020

Oxidizing properties : Based on its structural properties the product is not classified as oxidizing.

Sublimation point : No applicable information available.

Molecular weight : No data available

SECTION 10. STABILITY AND REACTIVITY

Reactivity : No decomposition if stored and applied as directed.

Chemical stability : No decomposition if stored and applied as directed.

Possibility of hazardous reactions : No decomposition if stored and applied as directed.

Conditions to avoid : See SDS section 7 - Handling and storage.

Incompatible materials : Strong acids
Strong bases
Strong oxidizing agents
Strong reducing agents

Hazardous decomposition products : No hazardous decomposition products if stored and handled as prescribed/indicated.

SECTION 11. TOXICOLOGICAL INFORMATION**Acute toxicity**

Not classified based on available information.

Product:

Acute oral toxicity : ATE: > 5,000 mg/kg

Acute inhalation toxicity : Remarks: No data available.

Acute dermal toxicity : ATE: > 5,000 mg/kg

Skin corrosion/irritation

Causes skin irritation.

Product:

Remarks : May cause skin irritation and/or dermatitis.

Serious eye damage/eye irritation

Causes serious eye irritation.

Product:

Remarks : May cause irreversible eye damage.

MasterEmaco P 130 PART A

Version 1.0 Revision Date: 09/03/2020 SDS Number: 000000261566 Date of last issue: -
Date of first issue: 09/03/2020

Respiratory or skin sensitization**Skin sensitization**

May cause an allergic skin reaction.

Respiratory sensitization

Not classified based on available information.

Product:

Remarks : Causes sensitization.

Germ cell mutagenicity

Not classified based on available information.

Carcinogenicity

Not classified based on available information.

Reproductive toxicity

Not classified based on available information.

STOT-single exposure

Not classified based on available information.

STOT-repeated exposure

Not classified based on available information.

Aspiration toxicity

Not classified based on available information.

Product:

No aspiration hazard expected.

Further information**Product:**

Remarks : The product has not been tested. The statement has been derived from the properties of the individual components.

Remarks : No data available

SECTION 12. ECOLOGICAL INFORMATION**Ecotoxicity**

No data available

Persistence and degradability

No data available

Bioaccumulative potential

No data available

Mobility in soil

No data available

MasterEmaco P 130 PART A

Version 1.0 Revision Date: 09/03/2020 SDS Number: 000000261566 Date of last issue: -
Date of first issue: 09/03/2020

Other adverse effects**Product:**

Additional ecological information : An environmental hazard cannot be excluded in the event of unprofessional handling or disposal.
Toxic to aquatic life.
Toxic to aquatic life with long lasting effects.

SECTION 13. DISPOSAL CONSIDERATIONS**Disposal methods**

Waste from residues : Do not contaminate ponds, waterways or ditches with chemical or used container.
Dispose of in accordance with national, state and local regulations.
Do not discharge into drains/surface waters/groundwater.

Contaminated packaging : Contaminated packaging should be emptied as far as possible and disposed of in the same manner as the substance/product.

SECTION 14. TRANSPORT INFORMATION**International Regulations****UNRTDG**

Not regulated as a dangerous good

IATA-DGR

Not regulated as a dangerous good

IMDG-Code

Not regulated as a dangerous good

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable for product as supplied.

Domestic regulation**49 CFR**

Not regulated as a dangerous good

SECTION 15. REGULATORY INFORMATION**California Prop. 65**

WARNING: This product can expose you to chemicals including 1-chloro-2,3-epoxypropane, which is/are known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

The ingredients of this product are reported in the following inventories:

TSCA : On the inventory, or in compliance with the inventory


MasterEmaco P 130 PART A

Version 1.0 Revision Date: 09/03/2020 SDS Number: 000000261566 Date of last issue: -
 Date of first issue: 09/03/2020

SECTION 16. OTHER INFORMATION

Further information

NFPA 704:



HMIS® IV:

HEALTH		
FLAMMABILITY		
PHYSICAL HAZARD		

HMIS® ratings are based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. The "*" represents a chronic hazard, while the "/" represents the absence of a chronic hazard.

Full text of other abbreviations

AICS - Australian Inventory of Chemical Substances; ASTM - American Society for the Testing of Materials; bw - Body weight; CERCLA - Comprehensive Environmental Response, Compensation, and Liability Act; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DOT - Department of Transportation; DSL - Domestic Substances List (Canada); ECx - Concentration associated with x% response; EHS - Extremely Hazardous Substance; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; ERG - Emergency Response Guide; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; HMIS - Hazardous Materials Identification System; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; MSHA - Mine Safety and Health Administration; n.o.s. - Not Otherwise Specified; NFPA - National Fire Protection Association; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NTP - National Toxicology Program; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; RCRA - Resource Conservation and Recovery Act; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the

MasterEmaco P 130 PART A

Version	Revision Date:	SDS Number:	Date of last issue: -
1.0	09/03/2020	000000261566	Date of first issue: 09/03/2020

Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RQ - Reportable Quantity; SADT - Self-Accelerating Decomposition Temperature; SARA - Superfund Amendments and Reauthorization Act; SDS - Safety Data Sheet; TCSI - Taiwan Chemical Substance Inventory; TSCA - Toxic Substances Control Act (United States); UN - United Nations; UNRTDG - United Nations Recommendations on the Transport of Dangerous Goods; vPvB - Very Persistent and Very Bioaccumulative

Revision Date : 09/03/2020

We support worldwide Responsible Care® initiatives. We value the health and safety of our employees, customers, suppliers and neighbors, and the protection of the environment. Our commitment to Responsible Care is integral to conducting our business and operating our facilities in a safe and environmentally responsible fashion, supporting our customers and suppliers in ensuring the safe and environmentally sound handling of our products, and minimizing the impact of our operations on society and the environment during production, storage, transport, use and disposal of our products.

IMPORTANT: WHILE THE DESCRIPTIONS, DESIGNS, DATA AND INFORMATION CONTAINED HEREIN ARE PRESENTED IN GOOD FAITH AND BELIEVED TO BE ACCURATE, IT IS PROVIDED FOR YOUR GUIDANCE ONLY. BECAUSE MANY FACTORS MAY AFFECT PROCESSING OR APPLICATION/USE, WE RECOMMEND THAT YOU MAKE TESTS TO DETERMINE THE SUITABILITY OF A PRODUCT FOR YOUR PARTICULAR PURPOSE PRIOR TO USE. NO WARRANTIES OF ANY KIND, EITHER EXPRESSED OR IMPLIED, INCLUDING WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE, ARE MADE REGARDING PRODUCTS DESCRIBED OR DESIGNS, DATA OR INFORMATION SET FORTH, OR THAT THE PRODUCTS, DESIGNS, DATA OR INFORMATION MAY BE USED WITHOUT INFRINGING THE INTELLECTUAL PROPERTY RIGHTS OF OTHERS. IN NO CASE SHALL THE DESCRIPTIONS, INFORMATION, DATA OR DESIGNS PROVIDED BE CONSIDERED A PART OF OUR TERMS AND CONDITIONS OF SALE. FURTHER, YOU EXPRESSLY UNDERSTAND AND AGREE THAT THE DESCRIPTIONS, DESIGNS, DATA, AND INFORMATION FURNISHED BY OUR COMPANY HEREUNDER ARE GIVEN GRATIS AND WE ASSUME NO OBLIGATION OR LIABILITY FOR THE DESCRIPTION, DESIGNS, DATA AND INFORMATION GIVEN OR RESULTS OBTAINED, ALL SUCH BEING GIVEN AND ACCEPTED AT YOUR RISK.

US / EN