
ADJUSTABLE ALUMINUM GANTRY CRANE - AHA-15-12-8-PNU

APPROX WEIGHT: 297 lbs.

DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE *** ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES MODEL NUMBER IS AHA-15-12-8-PNU

CAPACITY IS 1,500 LBS.

BASE WIDTH IS 53 3/4"

MAX OVERALL HEIGHT IS 112 1/4"

I-BEAM HEIGHT IS 8"

I-BEAM FLANGE WIDTH IS 4"

OVERALL I-BEAM LENGTH IS 144"

USABLE I-BEAM LENGTH IS 120 1/4"

ADJUSTABLE UNDER I-BEAM HEIGHT

74 1/4" MIN

104 1/4" MAX

HEIGHT IS ADJUSTABLE IN 6" INCREMENTS

CASTERS: (4) Ø12" X 3 1/2" WIDE PNEUMATIC SWIVEL CASTERS WITH FOUR LOCKING POSITIONS

CRANE MAY BE TAKEN APART AND BUNDLED WITH (2) INCLUDED STRAPS FOR EASY TRANSPORT

ALUMINUM CONSTRUCTION

SPECIAL FEATURES

| DIMENSION TOLERANCE ± 1/4" | | | |
|-----------------------------------|--|-----------------------|--------------------------|
| A P P R O V A | CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS. UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE | | |
| L | Signed: | | _Date: |
| | Printed Name: | PON RECEIPT OF SIGNED | APPROVAL DRAWING |
| DISTRIBUTOR'S NAME: P.O.# X | | | P.O.# X |
| VESTIL MANUFACTURING | | | W.O.# X |
| DRAWN BY: ND | | DATE: 07/11/13 | SALES: X |
| REFERENCE: X QUOTED LEAD TIME: X | | SCALE: 1:32 | FILE NAME: 28-007-291 |