

RDHC-110



Remove unwanted moisture from the air by using the Royal Sovereign 110-Pint Commercial Dehumidifier.



Highlights

- **Comfort:** Adjustable humidistat with the ability to adjust from 20-90% RH.
- **Convenient Maintenance:** Air filter is removable and washable.
- **Drainage Options:** Choose between manual or continuous drainage.
- **User-Friendly:** Digital controls to manage air quality.
- **Portability:** Includes pneumatic wheels and easy grip handle.
- **Eco-Friendly:** Uses R410A refrigerant and is cETLus certified.

Perfect solution for a drier, more comfortable environment!

RDHC-110



INDUSTRIAL
DESIGN

1,200 sq. ft.
RANGE

24 HOUR
TIMER



SPECIFICATIONS

Dehumidifying Capacity	70 pints/day @ 80°F, 60% RH 110 pints/day @ 86°F, 80% RH 127 pints/day @ 90°F, 90% RH	Individual Carton Dimensions	20.5"W x 22.2"D x 28.7"H 520 mm x 565 mm x 730 mm
Air Circulation	450 m3/hr	Individual Carton Weight	87 lbs. / 39.5 kgs
Temperature Range	41°F-100°F (5°C-38°C)	Individual Carton UPC Code	849023080596
Bucket Size	1.45 Gal. / 5.5 L	Master Carton Dimensions	16.77"W x 13.19"D x 25.98"H 426 mm x 335 mm x 660 mm
Direct Drain Option	Yes (Drainage Hose: 16.4 ft.)	Master Carton Weight	51.3 lbs. / 23.32 kgs
Refrigerant	R410A	Master Carton Count	1
Certification	cETLus	Master Carton UPC Code	50849023080591
Dimensions	17"W x 20.3"D x 32.5"H 430 mm x 515 mm x 825 mm		
Weight	79.3 lbs. / 36 kgs		

1 Year Warranty