


4.5'-6' DUAL-LEG INTERNAL SHOCK-ABSORBING ELASTIC LANYARD WITH REBAR HOOKS



Part Number: FAP30399(6)/6-SK

Our **Dingo Core™** series of single and dual-leg lanyards provide an economical solution for Non-SRL applications and are available in multiple hook and shock pack configurations.



SPECIFICATIONS	
Design	<ul style="list-style-type: none"> ▶ 4.5-6-foot internal shock-absorbing elastic lanyard ▶ Dual legs equipped with a steel snap hook (PN 146) at the single end and steel rebar hooks at the double end (PN 167)
Webbing	<ul style="list-style-type: none"> ▶ Material: polyester ▶ Width: 1.57 in. ± 0.04 in. (30mm ± 1 mm) ▶ Breaking strength: 6,000 lbs. (Minimum)
Stitching Thread	▶ Material: high-tenacity polyester
Metal Components	<ul style="list-style-type: none"> ▶ Material: alloy steel ▶ Plating: zinc plated ▶ Finish: shot-blasted ▶ Breaking strength: 5,000 lbs.
Weight	▶ 6.06 lbs. ± 0.02 lbs.
Applicable Standards	▶ Meets or exceeds ANSI Z359.13-2013

Safe Keeper Fall Protection is committed to providing high-quality fall protection equipment and systems to create a safer work environment and ultimately save lives in the workforce. We use today's cutting-edge manufacturing processes and experts, applying real-world practical knowledge to engineer effective yet affordable solution-focused products.

