
ADJUSTABLE STEEL CRANE - KNOCKDOWN - AHSN-2-10-16

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE *** ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



STANDARD FEATURES

MODEL NUMBER IS AHSN-2-10-16 CAPACITY IS 2,000 LBS.

BASE WIDTH IS 91 1/2"

MAX OVERALL HEIGHT IS 197 7/16"

I-BEAM HEIGHT IS 6"

I-BEAM FLANGE WIDTH IS 4"

OVERALL I-BEAM LENGTH IS 119 3/4"

USABLE I-BEAM LENGTH IS 89 3/4"

ADJUSTABLE UNDER I-BEAM HEIGHT 191 7/16" MAX

125 7/16" MIN

HEIGHT IS ADJUSTABLE IN 6" INCREMENTS CASTERS: (4) Ø8" X 2" WIDE GLASS FILLED

NYLON SWIVEL CASTERS WITH FOUR LOCKING POSITIONS **DURABLE LIQUID PAINT BLUE FINISH**

SPECIAL FEATURES **NONE**

I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.

UNITS REQUIRING APPROVAL DRAWINGS OR

MODIFIED ARE NON-RETURNABLE [] As drawn [] As marked

Signed:

Printed Name: LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING

DISTRIBUTOR'S NAME:

VESTIL MANUFACTURING

DRAWN BY: C.CLEMENS

DATE: 06/30/14

SALES: X

W.O.# X

SCALE: 1:52 FILE NAME: Quoted lead time: $_{\mathbf{Y}}$ QUOTE # 28-007-300