

Project Name

Location

Prepared By



SATCO S11731

17T8/LED/48-CCT/BB/BP

Notes

[www] 05-15-2024 04:42:54

General

Status	Active
Watts	17W
Incandescent Equivalent	90W
Fluorescent Equivalent	32W
Volts	120V-277V
Ballast Type	Type B
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
Nominal Length	48
Finish	White
CCT (Kelvin)	3500K/4000K/5000K
CRI	83
Lumens	2100L/2300L/2200L
Beam Spread	140
Hours Rated	50000
Product Category	Linear
Technology	LED

Electrical

Ballasting Requirements	Ballast Bypass
Operating Frequency	60Hz
Power Factor	0.9
THD	<25%
Operating Temperature	-20C (-4F) to +45C (+113F)

Physical

MOL	47.78
MOD	1.13
Material	Aluminum
Lens Finish	Frost
Lens Material	Polycarbonate (PC)
Housing Color	White
Weight (lb.)	0.99

Additional Information

Additional Info	5 Watts and 700 Lumens in Emergency Mode
Shatter-Proof Type	Yes
Tube Guard Use	No
Installation Notes	Not for use in vapor tight fixtures. Maximum Mounting Height: 13 Feet
Specification Note	Height at switch: 1.30 Inches; Work time after power failure: 90 Minutes; Battery Recharge Time is 24 hours
Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - T8 LED Bulbs - Ballast Bypass

Compliance

Safety Listing	cULus - Classified; cETLus - Listed; cRUus - Recognized Component
----------------	---

Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	S-MASCZT
CA T20 / T24 Rationale	Exempt - Base Not Regulated
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
NSF Approved	Yes
SDS Sheet	LED_Lamp

