AIR PNEUMATIC CART -AIR-2000-PSS

APPROX WEIGHT: 441 LBS

DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE



ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON

DIMENSION TOLERANCE ± 1/4"

STANDARD FEATURES

MODEL NUMBER IS AIR-2000-PSS CAPACITY IS 2,000 LBS PLATFORM WIDTH IS 24" PLATFORM LENGTH IS 471/4" PLATFORM RAISED HEIGHT IS 39 1/2" PLATFORM LOWERED HEIGHT IS 15" CASTER DIAMETER IS 6" CASTER WIDTH IS 1 1/2" AIR INLET IS 3/8" PSI RECOMMENDED 80-100 OPERATION: PNEUMATIC STAINLESS STEEL CONSTRUCTION

SPECIAL FEATURES

NONE

A P P R O V A	REPRESENTED REQUIREMENTS CONFIRM COMPLIANCE AND LOCA UNITS REQU MODIF	D SATISFIES DESIGN I ALSO ACKNON M PRODUCT AND WITH ALL APPLICA L REGULATIONS A IRING APPRO	ABLE FEDERAL, STATE AND STANDARDS. VAL DRAWINGS OR RETURNABLE	
L	Signed:		Date:	
	Printed Name:			
		RT UPON RECEIPT C	DF SIGNED APPROVAL DRAWIN	IG
DISTRIBUTOR'S NAME:			P.O.# X	
VESTIL MANUFACTURING			w.o.# X	
DRAV	^{VN BY:} NBE	DATE: 3/16/2		
	ENCE: X		ALE: 1:48 ^{FILE NAME:}	
QUOTED LEAD TIME: X		QUOTE # V	X	