

# TOP & BOTTOM DRIVING CARTON SEALER

MODEL CS-6050

sealersales



Conveyors and Casters  
Included

Value Unit - Excellent for Taller Cartons

- Simple to use
- Quick manual adjustment for various box sizes
- Side pressure rollers to close box top
- Two top and two bottom belts for positive feed
- Plug and Play - Includes conveyors and casters
- Optional 3" tape head available



Unlock seamless carton sealing with our **CS-6050** featuring four belt (top and bottom) drive belt design. The operator simply folds the top flaps of the corrugated carton and feeds it into the machine. The CS-6050 applies a single tape to both the top and bottom of the box simultaneously. The CS-6050 can easily be adjusted to process a different size carton. Excellent for taller, heavier boxes.

Experience thoughtful design with carton sealers – tailored for your convenience. The sealer comes complete with infeed/exit conveyors, casters, and power cord, providing you a plug and play system. Enjoy flexibility with your box sizes – easily adjust for different box widths in seconds. Elevate your packaging process with the features of our carton sealers, designed to make sealing cartons a breeze.



## SPECIFICATIONS

CARTON SIZE (LENGTH)	6" TO INFINITE
CARTON SIZE (WIDTH)	7" - 19.7" (2" TAPE HEAD) 7.9" - 19.7" (3" TAPE HEAD)
CARTON SIZE (HEIGHT)	5.1" - 23.6"
MACHINE SIZE	69"L X 32"W X (38"-63")H
MACHINE SPEED	65.6FT/MINUTE - UP TO 15 CARTONS/MIN
ELECTRICAL	110V, 1 PHASE, 10 AMPS
MAX BOX WEIGHT	55-LBS
TAPE HEAD SPECS	2" (48MM) WIDE - 1,000 OR 1,500 YARD ROLL
WEIGHT	330-LBS (NET) 385-LBS (GROSS)

# TOP & BOTTOM DRIVING CARTON SEALER

Model: CS-6050

sealersales



**Infeed & Exit Conveyors  
Included**



**Quickly & Easily Adjust  
for Box Widths**



**Casters for Flexibility**