

PORTABLE DIRECT HEAT

Model No. FKR-400

sealersales



Value Unit - Lightweight for Sealing Thicker Materials

- Lightweight and easy to operate
- PTFE coated jaws for cleaning ease
- Equipped with adjustable heat control
- Seal width: 10mm (0.39")
- Seal length: 400mm (15.7")
- Seal style: serrated

Introducing our **FKR-400 Portable Direct Heat Sealers**— designed for convenience and ease of use in various settings. This lightweight sealer is perfect for sealing irregular or long packages. We recommend this unit for sealing materials such as cellophane, coated aluminum foil, Kraft paper and other thicker materials. Please note this unit cannot seal polyethylene material.

The FKR-400 comes equipped with an adjustable temperature controller, enabling users to tailor the heat level according to the specific material being sealed. Allow a 5-10 minute warm-up time for the sealer to attain the optimal temperature before use. Please do not touch the jaws of the sealer until the unit has been turned off and allowed to cool down.

To achieve best results, follow these simple steps. Turn the temperature to the desired setting and allow 5-10 minutes for the sealer warm up. Insert the material between the jaws. Close the jaws and release the jaw after a couple of seconds. Fine tune the timing as needed until you achieve a satisfactory seal.

SPECIFICATIONS	FKR-400
SEALING	DIRECT
POWER	110V / 500W
SEAL WIDTH	10MM (0.39")
SEAL LENGTH	400MM (15.7")
SEAL STYLE	SERRATED ==
TEMPERATURE	UP TO 390°F (200°C)
DIMENSIONS (L x W x H)	16" x 10" x 4-1/2"
WEIGHT	4-LBS

8820 Baird Avenue • Northridge, CA 91324 • T: 818-718-8818
contact@sealersales.com • www.sealersales.com