

HEAT IMPULSE SEALER FOOT OPERATED

KF-SERIES

sealersales



Easy to operate - no warm up time

- Ideal for high volume sealing
- Plug-in electronic timer for various material thicknesses
- Seal length: 8" (200mm), 12" (300mm), 18" (450mm)
- Seal width: 2.5mm / 5mm
- ETL Listed (2.5mm units)
- Option: standing height operation



Our **KF-Series Heat Impulse Foot Sealers** are ideal for high volume poly bag and other thermoplastic sealing. The sealers are capable of sealing 15-20 bags per minute, these sealers allow for quick and accurate sealing with both hands free. These machines are also equipped with a plug-in timer. The timer controls the sealing time needed for various material thicknesses. Once the timer is set, the sealer will provide a consistently flat seal. The timer light will turn off once sealing process has been completed.

Our KF-Series sealers are available in 12", 18", and 24" sealing lengths with either a 2.5mm or 5mm wide seal. Depending on the sealer model, materials up to 24" wide and 16mil total thickness can be sealed. The sealers include a 26" pedestal, a 2" base and an adjustable worktable. The worktable measures 12" x 6-1/2" and can adjust from 3-1/2" - 9" from the sealing base. The manufacturer's kit includes two heating elements and one fuse. The 2mm seal width units are ETL Listed.

Easy to operate: Set the timer. Insert the bag between the two sealing bars and press down on the foot board to activate sealing. Hold down the foot board for an additional 2-3 seconds after timer light goes off to set the seal.

SPECIFICATIONS	KF-300F*	KF-305F	KF-450F*	KF-455F	KF-600F*	KF-605F
SEALING LENGTH	12"	12"	18"	18"	24"	24"
SEAL WIDTH	2.5MM	5MM	2.5MM	5MM	2.5MM	5MM
POWER	400W	600W	600W	900W	800W	1200W
MAX. SEAL THICKNESS	10MIL	16MIL	10MIL	16MIL	10MIL	16MIL
DIMENSIONS	15"x14"x35"	15"x14"x35"	21"x15"x35"	21"x15"x35"	28"x16"x35"	28"x16"x35"
WEIGHT	45-LBS	46-LBS	47-LBS	48-LBS	50-LBS	51-LBS



Seal Width
2.5mm (1/8")



Seal Width
5mm (1/4")

