


BOOM CARRIAGE MOUNT - LM-CM2-EBT-4

APPROX WEIGHT: 354 lbs.
 DOES NOT INCLUDE WEIGHT OF POWER OR PACKAGING!!!

*** ANY ADDITIONS, DELETIONS, OR OMISSIONS MUST BE CORRECTED ON THIS DRAWING AS THIS DRAWING WILL BE CONSIDERED ALL INCLUSIVE ***

ALL GRAPHICS PROVIDED ARE FOR REFERENCE ONLY. IF CERTAIN DIMENSIONS ARE CRITICAL PLEASE VERIFY THOSE DIMENSIONS WITH YOUR SALESPERSON



MAXIMUM SINGLE HOOK CAPACITIES

DISTANCE	36"	48"	60"	72"	84"	96"	108"	120"	132"	144"
CAPACITY	4000	3750	3500	3250	3000	2750	2500	2250	2000	1750

STANDARD FEATURES

MODEL NUMBER IS LM-CM2-EBT-4
 OVERALL WIDTH IS 11 1/2"
 OVERALL LENGTH IS 145 7/8"
 USABLE LENGTH IS 144"
 OVERALL HEIGHT IS 23 5/8"
 MAX CAPACITY IS 4,000 LBS
 TOUGH BAKED IN POWDER COATED
 BLUE BASE FRAME W/ YELLOW EXTENSION

SPECIAL FEATURES

NONE
 APPROX. WEIGHT / LOST LOAD = 354
 MINIMUM EFFECTIVE THICKNESS = <1"
 VERTICAL CENTER OF GRAVITY = 14 13/16"
 HORIZONTAL CENTER OF GRAVITY = 5 3/4"

NEVER EXCEED LOAD CENTER
 RATING PER FORKTRUCK
 MANUFACTURERS GUIDELINES.
 DO NOT USE THIS FORK TRUCK
 ATTACHMENT IF LOAD WILL EXCEED
 FORK TRUCK MANUFACTURER'S
 LOAD CENTER RATING

DIMENSION TOLERANCE ± 1/4"

APPROVAL	I, THE UNDERSIGNED, AGREE THAT THE PRODUCT AS REPRESENTED SATISFIES DESIGN AND DIMENSION REQUIREMENTS. I ALSO ACKNOWLEDGE MY DUTY TO CONFIRM PRODUCT AND INSTALLATION COMPLIANCE WITH ALL APPLICABLE FEDERAL, STATE AND LOCAL REGULATIONS AND STANDARDS.	
	UNITS REQUIRING APPROVAL DRAWINGS OR MODIFIED ARE NON-RETURNABLE	
	[] As drawn [] As marked	
	Signed: _____ Date: _____	
Printed Name: _____		
LEAD TIME WILL START UPON RECEIPT OF SIGNED APPROVAL DRAWING		

DISTRIBUTOR'S NAME:		P.O.#
VESTIL MANUFACTURING		X
		W.O.#
DRAWN BY: TJH		X
DATE: 5/23/22		SALES:
REFERENCE: X		SCALE: 1:48
QUOTED LEAD TIME: X		FILE NAME:
QUOTE # X		08-007-485