

STRETCH PALLET WRAPPER

MODEL SPW-1000B

sealersales



Efficiency Unleashed: 250% Power Stretch w Ramp

- Semi-automatic or manual operation
- Simplified control panel for easy operation
- ALHS (Auto Load-Height Sensor) photo eye
- 250% power pre-stretch
- Soft start/stop turntable
- Manual pallet jack ramp included



Unveiling our latest addition to our line of pallet wrappers: the **SPW-1000B** stretch wrap marvel – a robust, savings-driven machine engineered for day-long operations. Save money on film with the 250% powered pre-stretch. The 1000B takes a standard 5,000 ft. machine roll and catapults it to an astounding 12,500 ft! With a 3,500 lbs. maximum load capacity, the SPW-1000B boasts a resilient chain-driven turntable and film carriage, all powered by a 1/2 HP turntable motor achieving speeds of up to 12 RPM.

The SPW-1000B flaunts an easy to use analog control panel, and a photo eye for hands-free wrapping convenience. For enhanced functionality, optional scales can be seamlessly integrated into any SPW-1000B model upon request. Please note: the included photo eye does not recognize loads with black-colored products, metal drums or unusual voids

Our SPW-1000B is backed by a solid 3-year warranty on parts!

SPECIFICATIONS	SPW-1000B
PRODUCTION RATE	30-40 LPH
POWER REQUIREMENTS	110V, 60 HZ
MAXIMUM LOAD SIZE	50”L X 50”W X 85”H
MAXIMUM LOAD	3,500-LBS
TURNTABLE	59” DIAMETER
MACHINE DIMENSIONS	96.5”L X 59”W X 95”H
SHIPPING WEIGHT	1,100-LBS
FILM CAPACITY	ALL COMMERCIAL 20” WIDE FILM
WARRANTY	3 YEAR LIMITED WARRANTY